



## Non-Metallic Conduits

### • HG-DC Double Slit

Double slit corrugated conduit for retrofitting.

#### Features and Benefits

- Can be opened and closed repeatedly
- Cables can be inserted laterally
- Abrasion resistant
- Free of halogen, sulphur and phosphorus
- Colour: black (UV resistant)

#### Application

Control panels, machine building, plant construction and wherever retrofitting is a requirement.



*HelaGuard HG-DC double slit conduit is ideal for retrofitting.*

#### Material Data

|                       |                          |
|-----------------------|--------------------------|
| Material              | <b>Polyamide 6 (PA6)</b> |
| Operating Temperature | <b>-40 °C to +110 °C</b> |
| Flammability          | <b>UL94 V2</b>           |



#### Technical Table

| Article-No. | Type           | Nominal Ø | Outside Ø | Ø D  | Bending Radius | Weight (g/m) | Reel Length (m) | Colour     |
|-------------|----------------|-----------|-----------|------|----------------|--------------|-----------------|------------|
| 166-11800   | <b>HG-DC11</b> | 11        | 11.2      | 6.7  | 45             | 23           | 50              | Black (BK) |
| 166-11801   | <b>HG-DC13</b> | 13        | 12.9      | 7.9  | 55             | 37           | 50              | Black (BK) |
| 166-11802   | <b>HG-DC16</b> | 16        | 15.8      | 10.5 | 60             | 41           | 50              | Black (BK) |
| 166-11803   | <b>HG-DC21</b> | 21        | 21.0      | 13.9 | 90             | 63           | 50              | Black (BK) |
| 166-11804   | <b>HG-DC28</b> | 28        | 28.3      | 20.5 | 105            | 94           | 50              | Black (BK) |
| 166-11805   | <b>HG-DC34</b> | 34        | 34.5      | 27.0 | 150            | 118          | 25              | Black (BK) |
| 166-11806   | <b>HG-DC42</b> | 42        | 42.5      | 34.8 | 170            | 193          | 25              | Black (BK) |
| 166-11807   | <b>HG-DC54</b> | 54        | 54.5      | 45.3 | 170            | 263          | 25              | Black (BK) |

All dimensions in mm. Subject to technical changes.

Other reel lengths available on request.