


C-CD-205-01

100

- STUD SIZES: (+, .005)

"UL" LISTING *E32244
"CSA" LISTING *18689



MWID = MAXIMUM WIRE
 INSULATION DIAMETER
 WIRE SIZE: 12 - 10 AWG
 4.0 - 6.0 MM²

ALL DIMENSIONS = $\frac{\text{INCHES}}{\text{MM}}$

PART NUMBER	"W" ±.010	"C" MIN.	"L" MAX.	"D" ±.005	AVAILABLE STUD SIZES	TITLE:	DWG. NO.	A	CUSTOMER DWG.
C-2196-	$\frac{.290}{7.37}$	$\frac{.305}{7.75}$	$\frac{1.097}{27.86}$	$\frac{.111}{2.82}$	06X	SNAP SPADE TONGUE TERMINAL INSULKRIMP 200-SERIES			
C-2197-	$\frac{.320}{8.13}$	$\frac{.305}{7.75}$	$\frac{1.125}{28.58}$	$\frac{.137}{3.48}$	08X				
C-2198-	$\frac{.320}{8.13}$	$\frac{.305}{7.75}$	$\frac{1.145}{29.08}$	$\frac{.163}{4.14}$	10X				
C-2199-	$\frac{.415}{10.54}$	$\frac{.375}{9.53}$	$\frac{1.271}{32.28}$	$\frac{.223}{5.66}$	14X				
DIMENSIONAL TOLERANCES UNLESS OTHERWISE SPECIFIED		REFERENCE	SCALE:	NTS	DATE				
FRAC.	DEC.	ANG.							
±	±	±							