



## SCG-16B-LS

### Specifications

|                       |                 |
|-----------------------|-----------------|
| SPL (0.3W/10CM)       | 92.5dB +/- 3dB  |
| Nominal Input         | 0.3W (1.55Vrms) |
| Impedance             | 8 +/- 1.2Ω      |
| Resonance Frequency   | 780 +/- 100Hz   |
| Operating Temperature | 030~ +70°C      |
| Weight                | 1.2 Grams       |



