

Leopard Network Camera

Model:LNC-Q00xxx-M034



LEOPARD IMAGING INC.

High Definition Embedded Camera Leader

LNC-Q00xxx-M034 is an HD network camera and it supports H.264, MPEG4 and MJPEG video format outputs with high definition video (1080 x 720p 30 frames/s).

The image process module supports noise filters (NS), wide dynamic range (WDR), auto-enhancement and lens distortion correct (LDC). All of the features provide high quality images even in dark and shake environments.

Embedded motions detect, face detects, face recognition and privacy area mask provide an advanced surveillance system.

LNC-Q00xxx-M034 is compatible with PSIA and can easily be integrated with other systems.



Features

- 30 frames per second @720P
- single/double/triple media combo output
- video stabilization
- face detect, face recognition
- motion detect, motion alarm
- image enhance, digital WDR
- compatible with PSIA standard
- optional PoE support
- optional Wi-Fi module
- optional Day/Night IR cutting auto-switch
- Low light sensitivity




Wide Dynamic Range

This HD camera provides clear images in both extreme brightness and darkness simultaneously in the field.



Face Recognition

The Leopard Network Camera can accommodate 30 frames per second to provide prompt results for locating and recognizing the human face.



Feature List

Image Input

Sensor	Aptina 1/3" CMOS
Day/Night	Auto switch (Optional Feature)
WDR	Sensor WDR
Active pixels	1080x720
e-shoot	1/2 to 1/10,000
Enhance	Auto Enhance
Exposure	Auto Exposure
White Balance	Auto WB
Noise Filter	Configurable Enable/Disable
Video Stabilization	Configurable Enable/Disable
Lens	Fix focus, IRIS support, C/CS mount lens support

Image Process

Resolution	1280x720,D1,SXVGA
Format	H.264, MPEG-4, JPEG
Frame Rate	H264/MPEG-4: 30f/s

Smart Imaging

Motion Detect	Yes
Face Detect	Yes
Face Recognition	Yes

Audio

Format	G.711
--------	-------

Network

Protocols	TCP/IP, HTTP, FTP (client/server), SMTP, DHCP, DNS, NTP, RTP/RTCP
Wireless	Yes (Optional Feature)
IP Protocol	PSIA
Authentication	IEEE802.1X
UPnP	Yes
Zero-config	Yes

Interfaces

Network	10BASE-T/100BASE-TX (RJ-45)
Serial Port	RS-485 (PELCO-D protocol)
Extention Storage	SD card x1
USB	MiniB USB
Alarm In/Out	One channel Input,one channel Output
Audio Input	3.5MM Input
Audio Output	3.5MM Output

Work Environment

Weight	348 gram
Size	136mm*63mm*56mm
Power Supply	PoE(Optional) or DC12V
Power Consuming	<3w
Temperature	-20°C ~ 45°C
Humidity	10% ~ 80% no condense

Survellian Software

OS	Microsoft Windows 98/2000/XP/Vista/Win7
Browser	Internet Explorer6.0 or above
Record Software	Milestone xprotect (3rd software)

System Architecture



Product Size



Leopard Imaging Inc.

1130 Cadillac Ct
 Milpitas, CA 95035,USA
 Phone: +1-408-263-0988
 Fax: +1-408-217-1960
 Email:sales@leopardimaging.com
 Website: www.leopardimaging.com

上海嘉骏信息科技有限公司

上海市闵行区沪闵路 7250 号友谊商城 802 室
 电话: +86-21-54887300
 传真: +86-21-54887300-804
 邮箱: sales@jiajuntech.com
 网站: www.jiajuntech.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Leopard Imaging:](#)

[LNC-M00-M034](#) [LNC-Q00-M034](#)