


722-0960



Bulletin 700-CF

- AC and DC Operating Coils
- Positive-Guided (Mechanically Linked) Main and Auxiliary Contacts
- Ideal for Use in Safety Circuits
- Front- and Side-Mounted Auxiliary Contacts
- Guarded Terminals with Backed-Out Terminal Screws
- Electronic and Pneumatic Timing Modules
- Environmentally Friendly Materials
- Space-Saving Coil Modules
- Common accessories with Bulletin 100-C Contactors

TABLE OF CONTENTS

Description	Page	Description	Page
Product Selection	8-19	Specifications	8-25
4-Pole Control Relays, AC Operated	8-19	Technical Data	8-25
6- and 8-Pole Control Relays, AC Operated	8-20	Shipping Weights	8-25
4-Pole Control Relays, DC Operated	8-19	Approximate Dimensions	8-28
Accessories	8-21		
Auxiliary Contacts	8-21		
Control Modules	8-22		
Marking Systems	8-24		
Renewal Parts	8-24		

Description

The Bulletin 700-CF range of 4-pole relays combined with its adder decks, timers and accessories provides a highly flexible line of devices acceptable worldwide.

Conformity to Standards

IEC 947-5-1

EN 50011, EN 50005, EN 50022

UL 508

VDE 0660

CSA C22.2 Part 14

Approvals

CE Certified

CSA Certified

UL Listed, File E14840, Guide NKCR

SUVA Third Party Certified

Your order must include:

- Cat. No. of the relays required, complete with coil suffix.
- Cat. No. of adder decks, timers and accessories required.
- If required, the part number of replacement coils.

Type CF Control Relays — 4-Pole AC Voltage

2

2



Cat. No.

AC-1		
I_b [A]		
40°C	60°C	24/48V
25	20	16

⊗ Voltage Suffix Code
The Cat. No. as listed is in
becomes Cat. No. 700-CF

Voltage	12	24	32	36	42	4
50 Hz	R	K	V	W	X	
60 Hz	Q	J	—	V	—	
50/60 Hz	—	KJ	—	—	—	K

Type CF Control Rela


General

Aux./


Aux./

Approximate Dimensions

Dimensions are shown in millimetres (inches). Dimensions are not intended for manufacturing purposes.




Mounting Position



Front View

Side View



DC Control Relay

Relay

Type	a	b	c	c1	c2	Ød	d1	d2
700-CF	45 (1-25/32)	81 (3-3/16)	80.5 (3-11/64)	75.5 (3-3/32)	6 (1/4)	2 screws 4.5 (3/16)	60 (2-23/64)	35 (1-25/64)
700-CF Z	45 (1-25/32)	81 (3-3/16)	106.5 (4-2/16)	101.5 (4)	6 (1/4)	2 screws 4.5	60 (2-23/64)	35 (1-25/64)