



General ordering data

Order No.	1690050000
Part designation	ZDK 2.5/D/5
Version	Component terminal, 2.5 mm ² , Tension clamp connection, Wemid, dark beige, TS 35
EAN	4008190898885
Qty.	50 pc(s).

Product notes

Note, ordering data	Soldered diode: Type 1N 4007, reverse voltage 1000V, current 1 A; current of continuous busbar = 10 A
Note, technical data	2.5 mm ² flexible conductors with wire end ferrules are crimped with the Weidmüller PZ 6/5 crimping tool.
Product description	Z-series standard ranges provide solutions for conductor cross-sections from 0.05 to 35 mm ² .

Additional technical data

Colour of insulating material	dark beige
Connection direction	top
Electronic component	Diode
End plate required	Yes
Explosion-tested version "Ex e"	Yes
Installation advice	TS 35
Insulating material	Wemid
Levels cross-connected internally	No
No. of levels	2
No. of terminal strips per level	2
Open sides	right
Operating temperature range	- 50 °C, + 120 °C
Product family	Z-series
Type of connection	Plugged
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	V-0

Additional technical data

Version Feed-through terminal with electronic components

CSA rating data

Voltage (CSA)	300 V
CSA current	10 A
Min. cross-section (CSA)	AWG 26
Max. cross-section (CSA)	AWG 12

Conductors for clamping (additional connection)

Type of connection	Tension clamp connection
Flexible with ferrule, min. (DIN 46228 pt 1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228 pt 1)	2.5 mm ²

Conductors for clamping (rated connection)

Clamping range, min.	0.05 mm ²
Clamping range, max.	2.5 mm ²
Type of connection	Tension clamp connection
2nd type of connection	clamped
Connection direction	top
No. of connections	4
Stripping length	10 mm
Blade size	0.6 x 3.5 mm
Gauge to IEC 60947-1	A2
Solid, min.	0.5 mm ²
Solid, max.	2.5 mm ²
Flexible, min.	0.5 mm ²
Flexible, max.	2.5 mm ²
Flexible with ferrule, min. (DIN 46228/1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228/1)	1.5 mm ²
Flexible, min., ferrule with plastic collar (DIN 46228 pt 4)	0.5 mm ²
Flexible, max., ferrule with plastic collar (DIN 46228 pt 4)	1.5 mm ²
Twin wire-end ferrule, min.	0.14 mm ²
Twin wire-end ferrule, max.	0.34 mm ²
AWG conductor size, min.	AWG 30
AWG conductor size, min.	0.13 mm ²
AWG conductor size, max.	2.5 mm ²

Dimensions

Width	5.1 mm
Height of lowest version	54 mm
Length	79.1 mm
TS 35 offset	39 mm

Rating data

Rated cross-section	2.5 mm ²
Rated voltage	500 V
Rated impulse voltage	6 kV
Rated current	10 A

Rating data

Standards	IEC 60947-7-1
Pollution severity	3

UL rating data

Voltage (UL)	300 V
Current (UL)	10 A
Min. cross-section (UL)	AWG 30
Max. cross-section (UL)	AWG 14

Approvals

Approvals institutes



Downloads

STEP	1690050000_24219_ZDK_2.5-1.5-D-5_STP.stp
------	--

Classifications

eClass 4.1	27-14-11-27
eClass 5.0	27-14-11-27
eClass 5.1	27-14-11-27

Similar products

Order No.	Part designation	Version
1690020000	ZDK 2.5/D/1	Component terminal, 2.5 mm ² , Tension clamp connection, Wemid, dark beige, TS 35
1690030000	ZDK 2.5/D/2	Component terminal, 2.5 mm ² , Tension clamp connection, Wemid, dark beige, TS 35
1690040000	ZDK 2.5/D/4	Component terminal, 2.5 mm ² , Tension clamp connection, Wemid, dark beige, TS 35
1690060000	ZDK 2.5/D/6	Component terminal, 2.5 mm ² , Tension clamp connection, Wemid, dark beige, TS 35