

Product Description

Protection against dust; Abrasion protection; Cut into length without frizzle on the conduit's end; Simple, fast cable bundling; Can be cut without the need for a thermo-cutting tool



Application range

- Easy cable protection
- Additional insulation
- Bundling and guiding of cables and wires
- Low rodent-protection

Benefits

- Protection against dust
- Abrasion protection
- Cut into length without frizzle on the conduit's end
- Simple, fast cable bundling
- Can be cut without the need for a thermo-cutting tool

Design

- Polyamide 6.6 - halogen-free

Product features

- Abrasion-resistant
- Flexible
- Can be cut at cold temperatures

Technical Data

Upon request

Bulk containers on rolls

Note

Halogen and cadmium-free

Self-extinguishing according to DIN

75200/FMVSS302 and DIN5510

Colour delivered

Black (RAL 9005), UV-resistant

Material

Polyamide 6.6 - halogen-free

Temperature range

-55°C to +125°C

Article List

Part number	Clamping range (mm)	PU (m)
SILVYN BRAID PA6		
61721260	4 - 10	20
61721261	10 - 14	15
61721262	14 - 24	15
61721263	14 - 24	10
61721264	18 - 26	10
61721265	32 - 44	5

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.