

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0210200249](#)
Status: **Active - Custom**
Overview:
Description: 0.50mm (.020") Pitch Premo-Flex™ FFC Jumper, Same Side Contacts (Type A), 24 Circuits, 0.03m (1.18") Length


Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Cable
Series [21020](#)
Comments Contacts on the same side, Type A
Geographic Area Americas
Overview Premo-Flex™;
Product Name Premo-Flex™ FFC Jumper

Physical
Cable Length 0.03m (1.18")
Circuits (Loaded) 24
Packaging Type Bag
Pitch - Term. Interface (in) 0.020 In
Pitch - Term. Interface (mm) 0.50 mm
Temperature Range - Operating -40°C to +80°C
Wire Size AWG N/A
Wire/Cable Type Flat Flex Cable

Electrical
Current - Maximum 0.5A
Voltage - Maximum 30V

Material Info



Series image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?
Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

Duration at Max. 30
Process Temperature (seconds)
Max. Cycles at Max. 1
Process Temperature
Process Temperature 250 max. C

Search Parts in this Series
[21020 Series](#)

Use With
Any 0.50mm (.020") Pitch Molex FFC/FPC connector

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION