


DC0041/01/PC99-0.06

Die Cut PCM Resistor Pad



Features

Low thermal resistance
Natural tack

Applications

Resistor Pad

Properties

- REACH Compliant
- RoHS Compliant

Property	PC99	Unit	Tolerance	Test Method
Colour	Yellow	-	-	Visual
Thickness	0.06	mm	-	ASTM D374
Phase Change Softening Point	52	°C	-	-
Specific Gravity	2.35	g/cm ³	±0.2	ASTM D792
Working Temperature	-40 to 200	°C	-	-
Surface Resistance	>10 ¹²	Ohm-cm	-	ASTM D257
Elongation	5	%	±13	ASTM D412
Tensile Strength	0.1	Kgf/cm ²		ASTM D412
Standard Shape	-	Sheets 320-320mm	-	-
Thermal Resistance 30psi	0.1	°c-cm ² /w	-	-

Dimensions / mm							Ordering part number
A	B	C	D	E	F	G	
19	20.3	14.30	15.9	10.8	2.4	2.4	DC0041/01 - XXX - T
27	27.4	18.30	19.8	14	4.4	3.2	DC0041/02 - XXX - T
50.00	29	39.6	21.3	16	5.1	3.2	DC0041/03 - XXX - T
88.9	71.4	69.9	57.1	46	9.7	4.8	DC0041/04 - XXX - T