


Lamp Specification

Wamco Part No.	Envelope Size	Base Type	Rating	Filament Shape
WL-1315	G-5	BA15s	2.5V 1.00A	C-6

Test Volts	Current (A)			Light Output (MSCP)			Life Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
2.5	.900	1.00	1.100	1.40	1.75	2.10	20 Hrs

Dimensional Characteristics:

1. L.C.L. = .69" (17.5mm)
2. Base = Nickel-plated Brass Construction.



Title:

**G-5 Single Contact Bayonet Base Lamp
2.5V 1.00A Gas-Filled**

Drawn	7/17/00	CI	Notes: Unless otherwise specified, all dimensions are in inches.
Checked	7/17/00	EB	
Approved	7/17/00	EB	