


MMS-112-02-F-SH



MMS-116-02-L-DV

MMS-108-01-L-SV

MMS SERIES

TIGER CLAW™ SOCKET STRIP

TCMD

IPG@santec.com)

RI[®]
FILE NO. E111594

Note:
Some lengths, styles and options are non-standard, non-returnable.

MMS	1	NO. PINS PER ROW	01	PLATING OPTION	ROW OPTION	OTHER OPTION
02 thru 40			-F = Gold flash on contact, Matte Tin on tail -L = 10 μ" (0.25 μm) Gold contact, Matte Tin on tail	-SV = Single Vertical -SH = Single Horizontal -DV = Double Vertical -DH = Double Horizontal	-“XX” = Polarized Position	
No. of positions x $(2.00) .0787 + (0.56) .022$			-SV	-SH	-DV	-DH

MMS	1	NO. PINS PER ROW	02	PLATING OPTION	ROW OPTION	OTHER OPTION
02 thru 40				-F = Gold flash on contact, Matte Tin on tail -L = 10 μ " (0.25 μ m) Gold contact, Matte Tin on tail	-SV = Single Vertical -SH = Single Horizontal -DV = Double Vertical -DH = Double Horizontal	-“XX” = Polarized Position -K = (5.50 mm) .217" DIA Polyimide Film Pick & Place Pad (-SV & -DV only) (-SV= 3 positions min.) (-DV= 4 positions min.) -M = Metal Pick & Place Pad (4 positions min.) (-DV only) -P = Plastic Pick & Place Pad (4 pos. min., -SV only) (5 pos. min., -DV only) -TR = Tape & Reel Packaging

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.