





Rev	AWO #	Description	Date	Appr
-		RELEASED	9/21/04	

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED
PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: PBT, glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze or Brass

Plating:

Gold Flash over Nickel underplate on contact area, Tin over Copper underplate on tails

Electrical:

Operating voltage: 250 VAC max

Current rating: 1 Amps max

Contact resistance: 30 mohms max.

Insulation resistance: 100 Mohms min.

Dielectric withstanding voltage: 250 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +85°C

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES		Holes		DATE	
.X	± .10	ØX	± .10		
.XX	± .020	ØXX	± .015		
.XXX	± .015	ØXXX	± .010		
APPROVALS		DATE			
DRAWN	SS	9/21/04			
CHECKED					
APPROVED					
TITLE		PART NO.		REV.	
FIRE WIRE CONNECTOR, RIGHT ANGLE		FWC-C-S-RA		-	
PCB		SCALE: NTS		SHEET 1 OF 1	
REF:					

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ADAM TECH:

FWC-C-S-RA