

D

C

B



A

D

C

B

A



- 1

POLYOLEFIN, BLACK.
- 2

NYLON, BLACK.
- 3

NOMINAL WALL THICKNESS, EXPANDED.
- 4

LENGTH OF SEALANT.
- 5

EXPANDED INSIDE DIAMETER.
- 6

9.52[.375] MAXIMUM RECOVERED INSIDE DIAMETER.
- 7

ASSEMBLY WILL PASS 0.0703 KG PER SQ CENTIMETER [ONE POUND PER SQ IN.] WATER PRESSURE TEST.
- 8

121°C [250°F] SHRINK TEMPERATURE.
- 9

-55°C TO 110°C [-67°F TO 230°F] OPERATING TEMPERATURE.
- 10

THIS PART WILL ACCOMMODATE ø10.16 - ø22.22 [ø400 - ø.875] CABLE RANGE.
- 11

ACTUAL SHAPE MAY VARY DUE TO PROCESS VARIANCE.
- 12

SEE P/N CHART FOR MARKING. WHITE CHARACTERS .150 MIN HIGH AND LOCATED ON THE OUTSIDE SURFACE OF THE TUBING.
- 13

OBSOLETE PART.

|            |      |             |
|------------|------|-------------|
| TE 54011-5 | 2.50 | 13 54011-5  |
| NONE       | 4.00 | 54011-4     |
| NONE       | 3.25 | 54011-3     |
| NONE       | 2.50 | 54011-1     |
| MARKING    | A    | PART NUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN  
C.REIFSNYDER  
10 APR 96

CHK  
R.STONE  
15 APR 95

APVD  
T.A.WETZEL  
03 MAY 96

DIMENSIONS:  
INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

|        |   |   |
|--------|---|---|
| 0 PLC  | ± | - |
| 1 PLC  | ± | - |
| 2 PLC  | ± | - |
| 3 PLC  | ± | - |
| 4 PLC  | ± | - |
| ANGLES | ± | - |

MATERIAL

TUBING: 1  
SLEEVE: 2

FINISH  
-

TE Connectivity

STRAIN RELIEF ASSY,  
SHELL SIZE 17, CPC

SIZE  
A2

CAGE CODE  
00779

DRAWING NO  
C=54011

RESTRICTED TO  
-

CUSTOMER DRAWING

SCALE  
2:1

SHEET  
1 of 1

REV  
AC

1471-9 (1/15)

54011