





D



RECOMMENDED HOLE LAYOUT



C



SECTION X-X

- 1 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 2 THE NOTED DIMENSION APPLIES AT THE INTERSECTION OF THE POST AND HOUSING
- 3 POSTS:.000015 GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON SOLDER TAIL, ALL OVER .000050 NICKEL.
- 4 POSTS:.000015 GOLD IN CONTACT AREA, .000100-.000200 MATTE TIN ON SOLDER TAIL, ALL OVER .000050 NICKEL.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

A	4	3.032	2.900	29	60	7-102055-8	
	4	2.732	2.600	26	54	7-102055-5	
	4	2.532	2.400	24	50	7-102055-3	
	4	2.032	1.900	19	40	6-102055-8	
	4	1.732	1.600	16	34	6-102055-5	
	4	1.532	1.400	14	30	6-102055-3	
	4	1.232	1.100	11	24	6-102055-0	
	4	.932	.800	8	18	5-102055-8	
	4	.832	.700	7	16	5-102055-7	
	4	.732	.600	6	14	5-102055-6	
OBSOLETE	4	.632	.500	5	12	5-102055-5	
	4	.532	.400	4	10	5-102055-4	
	4	.432	.300	3	8	5-102055-3	
	4	.332	.200	2	6	5-102055-2	
	4	1.032	.900	9	20	5-102055-1	
	OBSOLETE	4	3.732	3.600	36	74	3-102055-5
	OBSOLETE	4	3.632	3.500	35	72	3-102055-4
	OBSOLETE	4	3.532	3.400	34	70	3-102055-3
	OBSOLETE	4	3.432	3.300	33	68	3-102055-2
	OBSOLETE	4	3.332	3.200	32	66	3-102055-1
A	OBSOLETE	4	3.232	3.100	31	64	3-102055-0
	OBSOLETE	4	3.132	3.000	30	62	2-102055-9
	OBSOLETE	4	3.032	2.900	29	60	2-102055-8
	OBSOLETE	4	2.932	2.800	28	58	2-102055-7
	OBSOLETE	4	2.832	2.700	27	56	2-102055-6
	OBSOLETE	4	2.732	2.600	26	54	2-102055-5
	OBSOLETE	4	2.632	2.500	25	52	2-102055-4
		4	2.532	2.400	24	50	2-102055-3
	OBSOLETE	4	2.432	2.300	23	48	2-102055-2
	OBSOLETE	4	2.332	2.200	22	46	2-102055-1
A	OBSOLETE	4	2.232	2.100	21	44	2-102055-0
	OBSOLETE	4	2.132	2.000	20	42	1-102055-9
	OBSOLETE	4	2.032	1.900	19	40	1-102055-8
	OBSOLETE	4	1.932	1.800	18	38	1-102055-7
	OBSOLETE	4	1.832	1.700	17	36	1-102055-6
		4	1.732	1.600	16	34	1-102055-5
	OBSOLETE	4	1.632	1.500	15	32	1-102055-4
	OBSOLETE	4	1.532	1.400	14	30	1-102055-3
	OBSOLETE	4	1.432	1.300	13	28	1-102055-2
	-103164-1	4	1.332	1.200	12	26	1-102055-1
A	OBSOLETE	4	1.232	1.100	11	24	1-102055-0
	OBSOLETE	4	1.132	1.000	10	22	102055-9
		4	.932	.800	8	18	102055-8
	OBSOLETE	4	.832	.700	7	16	102055-7
		4	.732	.600	6	14	102055-6
		4	.632	.500	5	12	102055-5
	OBSOLETE	4	.532	.400	4	10	102055-4
		4	.432	.300	3	8	102055-3
		4	.332	.200	2	6	102055-2
		4	1.032	.900	9	20	102055-1
	PLATING	C	B	A	NO OF POSN	PART NUMBER	