

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

—, —, —

© COPYRIGHT — BY TYCO ELECTRONICS CORPORATION.

ALL INTERNATIONAL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

Al

—

A2

UL—File entfällt EGD0—0218—03 UL— File removed

20.09.03

SR

SM

A3

REVISED PER ECO—11—002591

11FEB11

HMR

MM

Maßbild

Outline drawing

M3×10

57

63

35.5

27

33

Assembly reference

Pin

19.5 ×

Socket

× Distance for contact max: 21 mm

Kontaktanordnung

Contact arrangement

Ansicht Anschlußseite

view from termination side

36

42

1

7

Montageausschnitt

Panel cut-out for contact insert

bei Verwendung ohne Gehäuse

when used without housing

36

27

20

50

57

65

M3

Notes,

1

Material: insert, PC

2

Finish: contact; Ag, Au

Bemerkungen,

1

Material: Einsatz: PC

2

Oberfläche: Kontakte; Ag, Au

1

Female insert HN.2D.42 Crimp

1

dark gray

1

—

2–3

DESCRIPTION / BENENNUNG

MATERIAL

COLOR / FARBE

ITEM NO. POS.

REMARKS / BEMERKUNGEN

HN.2D.42.Bu.C

ORDERING TEXT / BESTELLTEXT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

GENERAL TOLERANCES

h ISO 8015

p ISO 2768

m DIN 16901

12.0

—E

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

MATERIAL

1

FINISH

2

DWN

10.11.1997

CHK

—

APVD

—

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

56g

CUSTOMER DRAWING

Tyco Electronics

Tyco Electronics Corporation

Harrisburg, Pa 17105—3608

NAME

Female insert

Buchseneinsatz HN.2D.42

—

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1103206

—

SCALE

1:1

SHEET

1 OF 1

REV

A3

1470—19

(1/08)