

CATALOG LISTING
701PB542-RG



PAGE 1 OF 1

REPLACES PR-23325

RELEASE NO. PR-23325

5

ISSUE



- NOTES
- 1 - UNIT INCLUDES "20HM2-1" BASIC SWITCH
 - 2 - RECOMMENDED FOR MANUAL OPERATION ONLY
 - 3 - FOR USE IN TEMPERATURE RANGE -65° F TO 392° F

ANSI Y14.5M-1982 APPLIES

THIRD ANGLE PROJECTION		SCALE FULL		DO NOT SCALE PRINT
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
ELECTRICAL DATA		ONE PLACE (.0)		±.030
CONTACT ARRANGEMENT 2X S P N C		TWO PLACE (.00)		±.015
28 VOLTS DC RATING		THREE PLACE (.000)		±.005
INDUCTIVE ---SEA LEVEL---1/4 AMP 70,000 FT---1/4 AMP		ANGLES		±
RESISTIVE ---SEA LEVEL---1/2 AMP 70,000 FT---1/2 AMP		WEIGHT		
CHARACTERISTICS		OPERATING FORCE --- 2 LBS MAX		
		OVERTRAVEL FORCE --- 2.5 LBS MAX		
		RELEASE FORCE --- 2 OZ MIN		
		PRETRAVEL		
		DIFFERENTIAL TRAVEL --- .031 MAX		
		OVERTRAVEL --- .030 MIN		
		FREE POSITION		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[701PB542-RG](#)