



har-port USB coupler

Advantages

- Compact and well-shaped service interface in a timeless attractive design
- Easy mounting
- Compact and robust design
- Practical accessories

Technical characteristics

Number of ports	2x USB Typ A
Mounting	Screwable to cover plates
Degree of protection	IP 20
Mating cycles	min. 1500
Temperature range	– 25 °C ... + 70 °C
Housing material	Polyamide

Identification


Part number

Drawing

Dimensions in mm


har-port USB 2.0 A-A coupler

09 45 452 1901



har-port USB 3.0 A-A coupler

09 45 452 1902



har-port USB 2.0 A-A coupler with 1.5 m cable

09 45 452 1922

