


## Inner Panels *EP Series*

Eclipse Series Enclosures



### Features

- Larger than standard NEMA panel used in same sized enclosure.
- 12gauge steel construction.
- Larger sizes have 2 or 4 formed flanges for added strength.
- Slotted corner design for easier mounting.
- Finished in white or unpainted galvanized.



| Mild<br>Steel<br>Part No. | Galvanized<br>Part No. | Size  |       | Gauge |
|---------------------------|------------------------|-------|-------|-------|
|                           |                        | D     | E     |       |
| EP1212                    | EPG1212                | 10.20 | 10.20 | 12.00 |
| EP1224                    | EPG1224                | 10.20 | 22.20 | 12.00 |
| EP1612                    | EPG1612                | 14.20 | 10.20 | 12.00 |
| EP1616                    | EPG1616                | 14.20 | 14.20 | 12.00 |
| EP1620                    | EPG1620                | 14.20 | 18.20 | 12.00 |
| EP2012                    | EPG2012                | 18.20 | 10.20 | 12.00 |
| EP2016                    | EPG2016                | 18.20 | 14.20 | 12.00 |
| EP2020                    | EPG2020                | 18.20 | 18.20 | 12.00 |
| EP2024                    | EPG2024                | 18.20 | 22.20 | 12.00 |
| EP2412                    | EPG2412                | 22.20 | 10.20 | 12.00 |
| EP2416                    | EPG2416                | 22.20 | 14.20 | 12.00 |
| EP2420                    | EPG2420                | 22.20 | 18.20 | 12.00 |
| EP2424                    | EPG2424                | 22.20 | 22.20 | 12.00 |
| EP2430                    | EPG2430                | 22.20 | 28.20 | 12.00 |
| EP2442                    | EPG2442                | 22.20 | 40.20 | 12.00 |
| EP2448                    | EPG2448                | 22.20 | 46.20 | 12.00 |
| EP3012                    | EPG3012                | 28.20 | 10.20 | 12.00 |
| EP3016                    | EPG3016                | 28.20 | 14.20 | 12.00 |
| EP3020                    | EPG3020                | 28.20 | 18.20 | 12.00 |
| EP3024                    | EPG3024                | 28.20 | 22.20 | 12.00 |
| EP3030                    | EPG3030                | 28.20 | 28.20 | 12.00 |

| Mild Steel |          | Galvanized |       | Size  |  |
|------------|----------|------------|-------|-------|--|
| Part No.   | Part No. | D          | E     | Gauge |  |
| EP3036     | EPG3036  | 28.20      | 34.20 | 12.00 |  |
| EP3042     | EPG3042  | 28.20      | 40.20 | 12.00 |  |
| EP3048     | EPG3048  | 28.20      | 46.20 | 12.00 |  |
| EP3060     | EPG3060  | 28.20      | 58.20 | 12.00 |  |
| EP3624     | EPG3624  | 34.20      | 22.20 | 12.00 |  |
| EP3630     | EPG3630  | 34.20      | 28.20 | 12.00 |  |
| EP3636     | EPG3636  | 34.20      | 34.20 | 12.00 |  |
| EP3642     | EPG3642  | 34.20      | 40.20 | 12.00 |  |
| EP3648     | EPG3648  | 34.20      | 46.20 | 12.00 |  |
| EP3660     | EPG3660  | 34.20      | 58.20 | 12.00 |  |
| EP4224     | EPG4224  | 40.20      | 22.20 | 12.00 |  |
| EP4230     | EPG4230  | 40.20      | 28.20 | 12.00 |  |
| EP4236     | EPG4236  | 40.20      | 34.20 | 12.00 |  |
| EP4824     | EPG4824  | 46.20      | 22.20 | 12.00 |  |
| EP4830     | EPG4830  | 46.20      | 28.20 | 12.00 |  |
| EP4836     | EPG4836  | 46.20      | 34.20 | 12.00 |  |
| EP4848     | EPG4848  | 46.20      | 46.20 | 12.00 |  |
| EP6036     | EPG6036  | 58.20      | 34.20 | 12.00 |  |
| EP7230     | EPG7230  | 70.20      | 28.20 | 12.00 |  |
| EP7236     | EPG7236  | 70.20      | 34.20 | 12.00 |  |

*Data subject to change without notice*