

Screw connection - WP-GT BRASS M10 - 3241030

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland made from brass with metric thread, rotatable, IP40 protection

Key Commercial Data

Packing unit	1 STK
Minimum order quantity	10 STK
Weight per Piece (excluding packing)	14.0 g
Custom tariff number	74122000
Country of origin	Germany

Technical data

Dimensions

Width (a)	17 mm
Height	32 mm
Wrench size	15.00 mm
Outside diameter	10.00 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 250 °C
Degree of protection	IP40

General

Color	Brass
Type	Rotatable
	Outer thread
Components	Halogen-free
Material	Brass

Screw connection - WP-GT BRASS M10 - 3241030

Classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	21132007
eCl@ss 5.1	21132007
eCl@ss 6.0	21132007
eCl@ss 7.0	27439210
eCl@ss 8.0	27439203

ETIM

ETIM 3.0	EC000519
ETIM 4.0	EC000519
ETIM 5.0	EC001180

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

VDE Zeichengenehmigung

Ex Approvals

Approvals submitted

Approval details

VDE Zeichengenehmigung 
--

Screw connection - WP-GT BRASS M10 - 3241030

Accessories

Accessories

Corrugated pipe

Protective hose - WP-STEEL ZC 10 - 3240697



Protective hose in galvanized steel

Protective hose - WP-STEEL S 10 - 3240686



Protective hose in stainless steel