




SEZ. A-A
(SECT. A-A)



SCALA NON IMPEGNATIVA
(DO NOT SCALE)
DIMENSIONI IN mm
(DIMENSIONS IN mm)

METRIC

PROIEZIONE EUROPEA
(EUROPEAN PROJECTION)

1 NORYL, UL94 V1, COLORE NERO

2 NORYL SE-1 COLORE ROSSO

3 TOLLERANZA NON CUMULATIVA

1 NORYL, UL94 V1, BLACK COLOUR

2 NORYL SE-1 RED COLOUR

3 NON CUMULATIVE TOLERANCE

4	1-280359-0	7.62	10.6	12.2	2
2	1-280358-0	2.54	5.6	7.1	
22	280364-0	53.34	56.4	57.9	1
15	280363-0	35.56	38.6	40.1	
12	280514-0	27.94	31	32.5	
10	280362-0	22.86	25.9	27.4	
9	280512-0	20.32	23.3	24.9	
8	280361-0	17.78	20.8	22.3	
6	280360-0	12.70	15.7	17.3	
4	280359-0	7.62	10.6	12.2	
2	280358-0	2.54	5.6	7.1	
N° POS.	PART NUMBER	DIM. "A"	DIM. "B"	DIM. "C"	MATERIAL (SEE NOTE)

CUSTOMER DRAWING
FOR REFERENCE ONLY

DISEGNO PER CLIENTE
SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED RELEASE FOR PUBLICATION 19

© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING

TOLLERANZE: SE NON
DIVERSAMENTE SPECIFICATO
(TOLERANCES, UNLESS
OTHERWISE SPECIFIED)

DIAM. ISOLANTE
(INS. DIA. RANGE)

RANGO FILO
(WIRE RANGE)

SCALA
(SCALE)

± 0.3

ANGOLI
(ANGLES)

± 2°

AMP

AMP ITALIA S.p.A.
Corso F.lli Cervi, 15
COLLEGNO (TORINO)

Y1 REVISED PER -ECO-10-000445 KK JAN10

Y REVISED NOTE 1 (ET00-0188-97) C.P. 1992

G REVISED AND REDRAWN BY CAD ET00-0092-95 C.P. 1995

F REVISED NOTE 1 C.M. 10-791

E REVISED AND REDRAWN E.B. 86

REV. REVISIONI (REVISION RECORD) DIS. DATA (DATE)

DIS. 11 APRIL '95 (DR.) C.P.A.

CONT. 11 APRIL '95 (CHK) R. CANTORE

APP. DATA (DATE)

DESCRIZIONE (DESCRIPTION) AMPMODU II REC. HSG

SINGLE ROW, CRIMP ON-SNAP IN

LOC. SIZE NUMERO (DWS NO) REV. FOGLIO (SHEET)

I A3 C-280358 Y1 1 D1 (COP) 1