

Power Supply

1U AC Input ATX Power Supply


ACE-818APM

Medical

PFC


Input Type	90 ~ 265 VAC Full Range					
Output Voltage	+3.3 V 16.8 A (0.3 A min)	+5 V 12 A (0.5 A min)	+12 V 12 A (1.5 A min)	-5 V	-12 V 0.8 A	+5 Vsb 2 A
Efficiency	68 %					
Temperature	Operating : 0 °C~ 50 °C , Storage : -20 °C~ 80 °C					
MTBF(hrs)	100,000					
Output Connector	20-pin ATX, 4-pin 12 V CPU, 2 x FDD and 3 x HDD					
Dimensions	190 x 81.5 x 40.5 (mm)					

Dimensions

180W


Ordering Information


Part No.	Description
ACE-818AP-RS	180W AC-DC 1U ATX Power Supply with PFC, meet Medical standard

ACE-4518AP/816A


PFC


Input Type	90 ~ 265VAC Full Range (ACE-4518AP) 95 ~ 132VAC or 181 ~ 264VAC (ACE-816A)					
Output Voltage	+3.3V 16.8A (0.3A min)	+5V 12A (0.3A min)	+12V 10A (1.5A min)	-5V	-12V 0.8A	+5Vsb 2A
ACE-4518AP						
ACE-816A	16A (0.2A min)	15A (1A min)	12A (0.2A min)		0.3A	2A
Efficiency	72% (ACE-816A) , 68% (ACE-4518AP)					
Temperature	Operating : 0 °C~ 50 °C , Storage : -20 °C~ 80 °C					
MTBF(hrs)	100,000					
Output Connector	ACE-4518AP:20-pin ATX, 4-pin 12 V CPU, FDD and 3 x HDD ACE-816A:20-pin ATX, FDD and 3 x HDD					
Dimensions	150 x 81.5 x 40.5 (mm)					

Dimensions

180W


Ordering Information


Part No.	Description
ACE-4518AP-RS	180W AC-DC 1U ATX Power Supply, with PFC
ACE-816A-RS	150W AC-DC 1U ATX Power Supply

ACE-A615A


PFC


Product	ACE-A615A-RS				
Input Type	90~264 VAC Full Range				
Output Voltage	+3.3 V 10 A (0.3 A min.)	+5 V 13 A (0.3 A min.)	+12 V 10 A (1 A min.)	-12 V 0.5 A (0 A min.)	+5 Vsb 2.0 A (0 A min.)
Efficiency	68 %				
Temperature	Operating : 0 °C~ 50 °C , Storage : -20 °C~ 80 °C				
MTBF(hrs)	100,000 hr				
Output Connector	20-pin ATX, 4-pin 12 V CPU, FDD and 3 x HDD				
Dimensions	150 x 81.5 x 40.5 (mm)				

Dimensions

150W


Ordering Information

Part No.	Description
ACE-A615A-RS	150W AC-DC 1U flex ATX Power Supply , with PFC