

(2.54 mm) .100"

SMH SERIES

SMT HORIZONTAL SOCKET

Mates With:

TSW, MTSW, MTLW,
EW, ZW, TSS, ZSS, TSM

SPECIFICATIONS

For complete specifications
and recommended PCB layouts
see www.samtec.com?SMH

Insulator Material:

Black LCP

Contact Material:

Phosphor Bronze

Plating:

Au or Sn over

50 μ " (1.27 μ m) Ni

Operating Temp Range:

-55 °C to +125 °C with Gold

-55 °C to +105 °C with Tin

Insertion Depth:

(3.68 mm) .145" to

(6.35 mm) .250"

Max Cycles:

100 with 10 μ " (0.25 μ m) Au

RoHS Compliant:

Yes

PROCESSING

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.15 mm) .006" max (02-24)

(0.20 mm) .008" max (25-36)*

*(.004" stencil solution

may be available; contact

IPG@samtec.com)

RECOGNITIONS

For complete scope of
recognitions see
www.samtec.com/quality



ALSO AVAILABLE (MOQ Required)



- Other platings

Important Note:

SMH mated to TSM-DH/-SH
not coplanar, SSM-DH/-SH
recommended for coplanar
applications.

Note:

Some lengths, styles and
options are non-standard,
non-returnable.



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.