

Flat gasket - WP-FS HF IP68 PG29 - 3241185

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Flat gasket, Height: 2.5 mm, Diameter: 43 mm, Color: green



Why buy this product

- The Centellen flat sealing rings are used to seal protective hose screw connections on uneven surfaces.
- IP68 degree of protection
- Resistant to oil, seal against dust and water, UV resistant, halogen-free, high mechanical stability

Key Commercial Data

Packing unit	1 STK
Minimum order quantity	25 STK
Custom tariff number	40169300
Country of origin	Germany

Technical data

Dimensions

Height	2.5 mm
Diameter	43 mm
Inner diameter (f)	35 mm

Ambient conditions

Ambient temperature (operation)	-50 °C ... 200 °C
Degree of protection	IP68

General

Color	green
Components	free from silicone and halogen
Material	Centellen

Flat gasket - WP-FS HF IP68 PG29 - 3241185

Classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	21132007
eCl@ss 5.1	27141120
eCl@ss 6.0	21132007
eCl@ss 7.0	27439210
eCl@ss 8.0	27439218
eCl@ss 9.0	27430319

ETIM

ETIM 3.0	EC000519
ETIM 4.0	EC000519
ETIM 5.0	EC001181

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411