


2014



Professional Tech Tools



Complete Tech Tools Program



Wiha Precision Screwdrivers

Description	Page
Precision Slotted Drivers	4-5
Precision Phillips Drivers	5
Precision Pozidriv® Drivers	6
Precision Hex Drivers	6
Precision Ball End Drivers	7
Precision Nut Drivers	8
Precision Torx® Drivers	9
Precision Pentalobe Drivers	9
Precision Chip Lifters	4

Wiha Magnetizer/Demagnetizer

Description	Page
Magnetizer/Demagnetizer	13

Wiha Precision Protturn Drivers

Description	Page
Protturn Drivers & Blade Sets	14
Slotted, Phillips, Torx, Chip Lifter	

Wiha Magnetizer/Demagnetizer

Description	Page
Torque Cable Keys	7
TorqueControl Handle	7

Wiha ESD Safe Precision Handles/Blades

Description	Page
SYSTEM 4 Handles/Blades	15-16
SYSTEM 4 Sets	18-19

Wiha Precision Screwdriver Accessories

Description	Page
Precision Master Tech Set	9
Precision Pocket Clip	4
Precision Stand	4
Precision Pouch	11,13

Wiha ESD Safe Precision Handle & Blades

Description	Page
SYSTEM 4 Drive-Loc Handle & Blades	17
SYSTEM 4 Drive-Loc Set	17


Wiha Precision PicoFinish Drivers

Description	Page
PicoFinish Screwdrivers	10-13
Slotted, Phillips, Torx, TorxPlus, Hex, MagicSpring, Ball End Hex, Chip Lifter & Nut Drivers	

ESD Safe Micro Bit Handles, Bits & Sets

Description	Page
Micro Bits Handles/Bits/Sets	20-22
Micro Bit Storage Handle Sets	21
ESD Safe Micro Bit Sets	23

Precision Electronic Pliers/Cutters

Description	Page
 Electronic Diagonal Cutters Wide Pointed Head	24
 Electronic Diagonal Cutters Wide Shape w/Wire Holding Spring	24
 Electronic Diagonal Cutters Narrow Shape	24
 Electronic Diagonal Cutters Full Flush Cutters w/Wire Trapping Spring	25
 Electronic Diagonal Cutters 48° Front Cutter/Long Nose Pliers	25
 Electronic Diagonal Cutters Oblique 30° Cutting Nippers	25
 Electronic Diagonal Cutters Short Nose Precision Pliers	25
 Electronic Stripping Pliers	25
 Flush Cutting Diagonal Cutters	25

Wiha Stripping Tools

Description	Page
 Self Adj. Cut & Strip Tools	34
 Adjustable Cable Stripper	35
 Adjustable Stripping Tool	35
 CATV/Satellite Stripper	35
 2 Step Stripping Tools	36
 3 Step Stripping Tools	37

Wiha Professional Tweezers

Description	Page
 ESD Safe Tweezers	26-28
 Inspection Mirrors	29

Wiha ESD Safe Tech Tools

ESD Safe Precision Drivers
Slotted/Phillips/Torx®/
TorxPlus®/Hex/Nut Drivers/
Chip Lifter

ESD Safe Ceramic Drivers

ESD Safe SYSTEM 4
Handles/Blades/Sets

ESD Safe Drive-Loc
Handles/Blades/Sets

ESD Safe Pliers & Cutters



Catalog 99945.wo

Stripping & Crimping Tools

Description	Page
 PortaCrimp Frame	30
 PortaCrimp Dies	31-33
 PortaCrimp Sets	30

Rotating cap

for precise turning and control
with fingertip

Precision handle

high quality plastic,
cadmium free

**Molded on
tapered handle**

allows rapid rotation

**High performance
blades**

chrome-vanadium-molybdenum steel,
Hard chrome finished

Tip

precision ground for exact fit,
hard chromed non-slip surface

**Wiha Long Life Precision Series****260 Slotted Screwdriver, With Precision Handle**

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	mm	Inch	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26008	.80	1/32	40	1.6	0.16	.01	120	4.7	.02	10
26010	1.0	.039	40	1.6	0.18	.01	120	4.7	.02	10
26012	1.2	3/64	40	1.6	0.20	.01	120	4.7	.02	10
26015	1.5	1/16	40	1.6	0.25	.01	120	4.7	.02	10
26018	1.8	.070	40	1.6	0.30	.01	120	4.7	.02	10
26020	2.0	5/64	40	1.6	0.40	.02	120	4.7	.02	10
26022	2.0	5/64	50	2.0	0.40	.02	145	5.7	.02	10
26023	2.0	5/64	100	3.9	0.40	.02	180	7.1	.03	10
26025	2.5	3/32	50	2.0	0.40	.02	145	5.7	.03	10
26027	2.5	3/32	100	3.9	0.40	.02	195	7.7	.03	10
26028	2.5	3/32	150	6.0	0.40	.02	245	9.6	.04	10
26030	3.0	1/8	50	2.0	0.50	.02	145	5.7	.03	10
26032	3.0	1/8	60	2.4	0.50	.02	170	6.7	.04	10
26033	3.0	1/8	100	3.9	0.50	.02	210	8.3	.04	10
26034	3.0	1/8	150	5.9	0.50	.02	260	10.2	.05	10
26035	3.5	9/64	60	2.4	0.60	.02	170	6.7	.05	10
26040	4.0	5/32	60	2.4	0.80	.03	170	6.7	.05	10
26041	4.0	5/32	100	3.9	0.80	.03	210	8.3	.06	10
26042	4.0	5/32	150	5.9	0.80	.03	260	10.2	.07	10

*Metric dimensions actual - Inch dimensions approximate

Wiha Precision Chip Lifter & Accessories**26810 Precision Chip Lifter**

Blade chrome-vanadium-molybdenum steel, hardened, chrome-plated.

Precision handle high quality plastic, impact resistant. Standard handle

Item No.	mm	mm	mm	mm	Inch	lbs.	pkg.
26810	1	3.5	50	145	5.7	.07	1

*Metric dimensions actual - Inch dimensions approximate

**26001 Pocket Clip for Precision Screwdrivers**

Tool clips turn Precision Screwdrivers into Pocket Screwdrivers.

Item No.	lbs.	pkg.
26001	Fits all Precision handles .0035	1

**26000 Plastic Precision Tool Rack**

Rack holds 6 precision screwdrivers, can be set on workbench.
Also has holes for hanging. Made from high quality plastic.

Item No.	lbs.	pkg.
26000	Rack for 6 Precision screwdrivers .08	1

**26090 6 Piece Precision Slotted Set**

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished.

Item No.	lbs.
26090	Slotted:
	1.5, 2.0 x 40mm .27
	2.5, 3.0 x 50mm
	3.5, 4.0 x 60mm

**26099 8 Piece Precision Slotted Set**

Blade high alloy chrome-vanadium-molybdenum steel.
Hard chrome finished. In canvas storage pouch

Item No.	lbs.
26099	Slotted: 1.0, 1.2, 1.5, 2.0 x 40mm
	2.5, 3.0 x 50mm, 3.5, 4.0 x 60mm .54

Wiha Precision Slotted/Phillips Drivers



261 Phillips Screwdriver, With Precision Handle

Blade high alloy chrome-vanadium-molybdenum steel.

[SHOP](#)

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26102	000	40	1.6	2.0	.08	120	4.7	.02	10
26100	00	40	1.6	2.0	.08	120	4.7	.02	10
26101	00	75	3.0	2.0	.08	155	6.1	.02	10
26105	0	50	2.0	3.0	.12	145	5.7	.02	10
26108	0	75	3.0	3.0	.12	170	6.7	.03	10
26107	0	100	3.9	3.0	.12	195	7.6	.05	10
26109	0	150	5.9	3.0	.12	245	9.6	.06	10
26110	1	60	2.4	4.0	.16	170	6.7	.05	10
26113	1	80	3.1	4.0	.16	190	7.5	.05	10
26114	1	100	3.9	4.0	.16	210	8.2	.06	10
26115	1	150	5.9	4.0	.16	260	10.2	.07	10

*Metric dimensions actual - Inch dimensions approximate



[SHOP](#)

26092 7 Piece Precision Slotted & Phillips Set

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.		lbs.
26092	Slotted:	
	2.5 x 50mm,	.30
	2.5, 3.0, 4.0 x 100mm	
	3.0, 4.0 x 150mm	
	Phillips:	
	0 x 75mm	



[SHOP](#)

26190 7 Piece Precision Slotted & Phillips Set

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.		lbs.
26190	Slotted:	
	1.5 x 40mm	.31
	2.0, 2.5 x 50mm	
	3.0 x 60mm	
	Phillips:	
	00 x 40mm	
	0 x 50mm, 1 x 60mm	



[SHOP](#)

26194 4 Piece Precision Phillips Set

Blade high alloy chrome-vanadium-molybdenum steel.

Hard chrome finished.

Item No.		lbs.
26194	Phillips: 000, 00 x 40mm	
	0 x 50mm, 1 x 60mm	.18



In canvas storage pouch

[SHOP](#)

26199 8 Piece Precision Slotted/Phillips Set

Blade high alloy CVM steel, hard chrome finished.

Item No.		lbs.
26199	Slotted: 1.0, 2.0 x 40mm,	
	3.0 x 50mm, 4.0 x 60mm	.55
	Phillips: 000, 00 x 40mm,	
	0 x 50mm, 1 x 60mm	



[SHOP](#)

26192 5 Piece Precision Slotted & Phillips Set

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.		lbs.
26192	Slotted:	
	2.5, 3.0, 4.0 x 150mm	.44
	Phillips:	
	0, 1 x 150mm	



Wiha Pozidriv® Precision Series



[SHOP](#)

262 Pozidriv® Screwdriver, With Precision Handle

Blade high alloy chrome-vanadium-molybdenum steel.

Item									
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26205	0	50	2.0	3.0	.12	145	5.7	.03	10
26210	1	60	2.4	4.0	.16	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate

Wiha Hex Metric Precision Series



[SHOP](#)

263 Metric Metric Hex Driver, With Precision Handle

Metric sizes. Blade high alloy chrome-vanadium-molybdenum steel.

Item									
No.	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.	
26307	.7	.028	40	1.6	120	4.7	.02	10	
26309	.9	.035	40	1.6	120	4.7	.02	10	
26313	1.3	.050	40	1.6	120	4.7	.02	10	
26315	1.5	-	50	2.0	145	5.7	.03	10	
26320	2.0	5/64	50	2.0	145	5.7	.03	10	
26325	2.5	-	60	2.4	170	6.7	.04	10	
26330	3.0	-	60	2.4	170	6.7	.04	10	
26340	4.0	-	60	2.4	170	6.7	.05	10	

*Metric dimensions actual - Inch dimensions approximate

Wiha Hex Inch Precision Series



[SHOP](#)

263 Inch Inch Hex Driver, With Precision Handle

Inch sizes. Blade high alloy chrome-vanadium-molybdenum steel.

Item									
No.	Inch	mm	mm	Inch	mm	Inch	lbs.	pkg.	
26307	0.028	0.7	40	1.6	120	4.7	.02	10	
26309	0.035	0.9	40	1.6	120	4.7	.02	10	
26313	0.05	1.3	40	1.6	120	4.7	.02	10	
26316	1/16	-	50	2.0	145	5.7	.03	10	
26320	5/64	2.0	50	2.0	145	5.7	.03	10	
26323	3/32	-	60	2.4	170	6.7	.04	10	
26327	7/64	-	60	2.4	170	6.7	.04	10	
26331	1/8	-	60	2.4	170	6.7	.04	10	
26333	9/64	-	60	2.4	170	6.7	.05	10	
26336	5/32	-	60	2.4	170	6.7	.05	10	

*Metric dimensions actual - Inch dimensions approximate



[SHOP](#)

26391 8 Pc. Precision Hex Driver Set - Inch

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.		
26391	Hex Inch:	lbs.
	.028, .035, .050 x 1.6"	.32
	1/16, 5/64 x 2.0"	
	3/32, 7/64, 1/8 x 2.4"	



[SHOP](#)

26390 7 Pc. Precision Hex Driver Set - Metric

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.		
26390	Hex Metric:	lbs.
	.7, .9, 1.3 x 40mm	.28
	1.5, 2.0 x 50mm	
	2.5, 3.0 x 60mm	



[SHOP](#)


26399 8 Piece Precision Hex Driver Set - Inch

Blade high alloy chrome-vanadium-molybdenum steel.

Hard chrome finished. In canvas storage pouch

Item No.		
26399	Hex Inch:	lbs.
	.028, .035, .050 x 1.6"	
	1/16, 5/64 x 2.0", 3/32, 7/64, 1/8 x 2.4"	.55

Wiha Ball End Precision Series




SHOP

264 Inch Ball End Hex Inch Screwdriver With Precision Handle

Angle entry up to 30°. Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finish.

Item No.	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26413	0.05	40	1.6	120	4.7	.02	10
26416	1/16	50	2.0	145	5.7	.03	10
26419	5/64	50	2.0	145	5.7	.03	10
26423	3/32	50	2.0	145	5.7	.03	10
26427	7/64	60	2.4	170	6.7	.03	10
26431	1/8	60	2.4	170	6.7	.05	10
26436	9/64	60	2.4	170	6.7	.05	10
26439	5/32	60	2.4	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate



SHOP

264 Metric Ball End Hex Metric Screwdriver With Precision Handle

Angle entry up to 30°. Blade high alloy CVM steel.

Item No.	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
26413	1.3	.050	40	1.6	120	4.7	.02	10
26415	1.5	-	50	2.0	145	5.7	.03	10
26420	2.0	-	50	2.0	145	5.7	.03	10
26425	2.5	-	60	2.4	170	6.7	.04	10
26430	3.0	-	60	2.4	170	6.7	.05	10
26440	4.0	-	60	2.4	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate



26491 5 Piece Ball End Hex Driver Set - Metric

Angle entry up to 30°. Blade high alloy chrome-vanadium-molybdenum-steel.

Item No.	Ball End Hex Metric:	lbs.
26491	1.3 x 40mm	.25
	1.5, 2.0 x 50mm	
	2.5, 3.0 x 60mm	

SHOP



26490 8 Piece Ball End Hex Driver Set - Inch

Angle entry up to 30°. Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	Hex Inch:	lbs.
26490	.050 x 1.6, 1/16, 5/64, 3/32 x 2.0, 7/64, 1/8, 9/64, 5/32 x 2.4"	.28

SHOP



In canvas storage pouch

SHOP

26499 8 Piece Ball End Hex Driver Set - Inch

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished.

Item No.	Ball End Hex Inch:	lbs.
26499	.050 x 1.6", 1/16, 5/64, 3/32 x 2.0" 7/64, 1/8, 9/64, 5/32 x 2.4"	.62

Wiha Torque Cable Keys



SHOP

286 Torque Cable Key For Threaded Hex Connectors

For torque controlled fastening of cable plug connectors with Hex heads. Used with Wiha-TorqueControl Screwdrivers.

Item No.	Size	mm	mm	mm	Max Nm	pkg.	lbs.
28620	8mm	4.0	78	218	1.0	1	.06
28622	9mm	4.0	78	218	1.0	1	.06
28624	11mm	4.0	78	218	1.5	1	.06
28626	12mm	4.0	78	218	1.5	1	.06
28627	13mm	4.0	78	218	1.5	1	.06
28629	14mm	4.0	78	218	1.5	1	.06
28632	17mm	4.0	78	218	1.5	1	.06
28633	18mm	4.0	78	218	1.5	1	.06
28637	22mm	4.0	90	233	2.0	1	.10
28638	24mm	4.0	90	233	2.0	1	.10

28644 Torque Cable Key For Threaded Hex Connectors - Inch

Item No.	Size	mm	mm	mm	Max Nm	pkg.	lbs.
28644	1/2"	4.0	78	218	1.5	1	.06

+/-6% accuracy tolerance
Certificate of calibration



SHOP

28552 Adjustable TorqueVario-S Handle - In Newton Meter Scale

EN ISO 6798, BS EN 26789, ASME B107.14M. Ergonomic molded multi-component handle, light and compact. Handle sizes proportioned to optimize torque range. Audible and perceptible click when the torque setting has been attained, automatically resets for next torque cycle.

Item No.	Newton Meter Scale	Increments	mm	lbs.	pkg.
28552	0.8 - 2.0Nm	.10 Nm	126 - 131	.45	1

Wiha Nut Driver Precision Series



265 Metric Metric Nut Driver With Precision Handle

Metric sizes. Blade CVM steel. Hard chrome finished.

[SHOP](#)

Item No.													lbs.	pkg.
	mm	mm	Inch	mm	Inch	mm	mm	mm	mm	mm	mm	mm		
26510	1.5	60	2.4	140	5.5	2.5	3.0						.03	10
26515	1.8	60	2.4	140	5.5	2.9	3.5						.03	10
26520	2.0	60	2.4	140	5.5	3.2	4.0						.04	10
26525	2.5	60	2.4	155	6.1	4.0	4.0						.04	10
26530	3.0	60	2.4	155	6.1	5.0	5.0						.05	10
26532	3.2	60	2.4	155	6.1	5.0	5.0						.05	10
26535	3.5	60	2.4	155	6.1	5.3	6.0						.05	10
26540	4.0	60	2.4	155	6.1	5.5	6.0						.05	10
26545	4.5	60	2.4	155	6.1	6.2	7.0						.05	10
26550	5.0	60	2.4	155	6.1	6.8	7.0						.05	10
26555	5.5	60	2.4	170	6.7	7.6	8.0						.06	10
26560	6.0	60	2.4	170	6.7	8.2	9.0						.06	10
26570	7.0	60	2.4	170	6.7	9.6	10.0						.06	10

*Metric dimensions actual - Inch dimensions approximate



265 Inch Inch Nut Driver With Precision Handle

Inch sizes. Blade CVM steel. Hard chrome finished.

[SHOP](#)

Item No.													lbs.	pkg.
	Inch	mm	Inch	mm	Inch	Inch	Inch	Inch	Inch	Inch	Inch	Inch		
26523	3/32	60	2.4	155	6.1	.16	.16						.04	10
26527	7/64	60	2.4	155	6.1	.20	.20						.05	10
26531	1/8	60	2.4	155	6.1	.20	.20						.05	10
26536	9/64	60	2.4	155	6.1	.21	.24						.05	10
26539	5/32	60	2.4	155	6.1	.22	.24						.05	10
26547	3/16	60	2.4	155	6.1	.25	.28						.05	10
26556	7/32	60	2.4	170	6.7	.30	.32						.06	10
26563	1/4	60	2.4	170	6.7	.34	.36						.06	10

*Metric dimensions actual - Inch dimensions approximate



26591 8 Pc. Precision Nut Driver Set - Inch

Blade CVM steel.

[SHOP](#)

Item No.													lbs.	pkg.
26591	Inch Nut Drivers:													
	3/32, 7/64, 1/8, 9/64, 5/32,													
	3/16, 7/32, 1/4" x 2.4"													



26590 8 Pc. Precision Nut Driver Set - Metric

Blade CVM steel.

[SHOP](#)

Item No.													lbs.	pkg.
26590	Metric Nut Drivers:													
	2.5, 3.0, 3.5, 4.0, 4.5,													
	5.0, 5.5, 6.0 x 60mm													

26592 Set 7 Pcs. Nut Driver Metric

Item No. 26592 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm


[SHOP](#)


26599 8 Pc. Precision Nut Driver Set - Inch

Blade high alloy chrome-vanadium-molybdenum steel.

Hard chrome finished. In canvas storage pouch

Item No.	Inch Nut Drivers:		lbs.
26599	3/32, 7/64, 1/8, 9/64, 5/32,		.72
	3/16, 7/32, 1/4" x 2.4"		

Wiha Precision Screwdriver Set


[SHOP](#)

92191 51 Piece Precision Tool Tray Set

Tool box tray. Equipped with 51 precision drivers.

Item No.	Slotted: .8, 1.0, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0
92191	Phillips: #000, #00, #0, #1
	Torx: T1, T2, T3, T4, T5, T6, T7, T8, T9, T10
lbs. 3.14	Metric Hex: 1.27, 1.5, 2.0, 2.5, 3.0, 4.0
	Inch Hex: .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
	Metric Nut Drivers: 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5
	26810 Chip Lifter

Wiha TORX® Precision Series



267 TORX® Screwdriver, With Precision Handle

Blade high alloy chrome-vanadium-molybdenum steel.

[SHOP](#)

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
26701	T1	40	1.6	120	4.7	.01	10
26702	T2	40	1.6	120	4.7	.02	10
26703	T3	40	1.6	120	4.7	.02	10
26704	T4	40	1.6	120	4.7	.02	10
26705	T5	40	1.6	120	4.7	.02	10
26706	T6	40	1.6	120	4.7	.02	10
26707	T7	40	1.6	120	4.7	.02	10
26708	T8	40	1.6	120	4.7	.03	10
26709	T9	50	2.0	145	5.7	.03	10
26710	T10	50	2.0	145	5.7	.03	10
26715	T15	60	2.4	170	6.7	.05	10
26720	T20	60	2.4	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate



[SHOP](#)

26790 6 Pc. TORX® Screwdriver Set

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.		lbs.
26790	TORX®:	
	T6, T7, T8 x 40mm	.30
	T9, T10 x 50mm	
	T15 x 60mm	

26791 Set 8 Pcs. TORX® Screwdriver Set

Item No. 26791 T1, T2, T3, T4, T5, T6, T7, T8



[SHOP](#)

26799 8 Pc. TORX® Screwdriver Set

Blade high alloy chrome-vanadium-molybdenum steel.

Hard chrome finished. In canvas storage pouch

Item No.		lbs.
26799	TORX®: T3, T4, T5, T6, T7, T8 x 40mm	
	T9 x T10 x 50mm	.50



[SHOP](#)

26792 7 Pc. TORX® Screwdriver Set

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.		lbs.
26792	TORX®:	
	T5, T6, T7, T8 x 40mm	.33
	T9, T10 x 50mm	
	T15 x 60mm	



Wiha Pentalobe IPR Precision Series

Wiha Pentalobe IPR drivers will fit fasteners used in "Apple" brand products including iPhone, Mac Book & Mac Air



- Exact fit precision machined Pentalobe tips
- High performance CRM72 tool steel
- Hard chromed finish blades & tips
- Tapered ergonomic handle
- Easy spin finger tip control cap



267 Pentalobe IPR Screwdriver, With Precision Handle

Blade high alloy chrome-vanadium-molybdenum steel.

[SHOP](#)

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
26761	P1	40	1.6	120	4.7	.01	1
26762	P2	40	1.6	120	4.7	.02	1
26763	P3	40	1.6	120	4.7	.02	1
26764	P4	40	1.6	120	4.7	.02	1
26765	P5	40	1.6	120	4.7	.02	1
26766	P6	40	1.6	120	4.7	.02	1

*Metric dimensions actual - Inch dimensions approximate



[SHOP](#)

26794 6 Pc. Precision Pentalobe IPR Screwdriver Set

Blade high alloy chrome-vanadium-molybdenum steel.

Hard chrome finished. Super hardened best wear resistance long life

Item No.	Pentalobe IPR Drivers:	lbs.
26794	P1, P2, P3, P4, P5, P6	.35

Wiha Precision Screwdriver Set



[SHOP](#)

92190 Master Technicians Bench Top Set

Metal frame. Equipped with 50 precision drivers.

Item No.	Slotted: .8, 1.0, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0
92190	Phillips: #000, #00, #0, #1
	TORX®: T1, T2, T3, T4, T5, T6, T7, T8, T9, T10
lbs. 2.86	Metric Hex: 1.27, 1.5, 2.0, 2.5, 3.0
	Inch Hex: .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
	Metric Nut Drivers: 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5
	26810 Chip Lifter

Wiha Soft Grip PicoFinish Precision Screwdrivers

The Comfortable Precision Screwdriver



Color coded symbols on rotating cap gives easy recognition of individual styles & sizes

CVM tool steel blade, hardened, hard chrome finish



Soft Grip Handle



Ergonomic multi-component handle with rotating cap for maximum user comfort and precise control



260 Slotted Precision Screwdriver, With PicoFinish Handle

Blade CVM steel, hardened, hard chromed.

[SHOP](#)

Item No.	mm	Inch	mm	Inch	mm	Inch	Pkg.
26050	0.8	.03	40	1.6	134	5.3	10
26051	1.0	.04	40	1.6	134	5.3	10
26052	1.2	.05	40	1.6	134	5.3	10
26053	1.5	.06	40	1.6	134	5.3	10
26054	1.5	.06	60	2.4	154	6.1	10
26055	1.8	.07	40	1.6	134	5.3	10
26056	1.8	.07	60	2.4	154	6.1	10
26060	2.0	.08	40	1.6	140	5.5	10
26061	2.0	.08	60	2.4	160	6.3	10
26063	2.0	.08	100	3.9	200	7.9	10
26065	2.5	.09	50	2.0	150	5.9	10
26066	2.5	.09	75	3.0	175	6.9	10
26068	2.5	.09	100	3.9	200	7.9	10
26070	3.0	.13	50	2.0	150	5.9	10
26072	3.0	.13	100	3.9	200	7.9	10
26073	3.0	.13	150	5.9	250	9.8	10
26074	3.5	.14	60	2.4	160	6.3	10
26076	4.0	.16	60	2.4	160	6.3	10
26079	4.0	.16	100	3.9	200	7.9	10
26080	4.0	.16	150	5.9	250	9.8	10

*Metric dimensions actual - Inch dimensions approximate



[SHOP](#)

26093 8 Pc. Slotted Precision Screwdriver Set, With Soft

PicoFinish Handle In storage pouch

Item No.		lbs.
26093	Slotted: .8, 1.2, 1.5, 2.0 x 40mm 2.5, 3.0 x 50mm, 3.5, 4.0 x 60mm	.54



261 Phillips Precision Screwdriver, With Soft PicoFinish

Precision Handle Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished.

[SHOP](#)

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	pkg.
26130	000	40	1.6	2.0	.08	134	5.3	10
26132	00	40	1.6	2.0	.08	134	5.3	10
26133	00	60	2.4	2.0	.08	154	6.1	10
26135	0	50	2.0	3.0	.12	150	5.9	10
26136	0	75	3.0	3.0	.12	175	6.9	10
26140	1	60	2.4	4.0	.16	160	6.3	10
26142	1	80	3.1	4.0	.16	180	7.1	10
26145	1	150	5.9	4.0	.16	250	9.8	10

*Metric dimensions actual - Inch dimensions approximate



[SHOP](#)

26193 8 Pc. Slotted & Phillips Precision Driver Set, With Soft

PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

Item No.		lbs.
26193	Slotted: 1.0, 1.5, 2.0 x 40mm 2.5 x 50mm, 3.5 x 60mm Phillips: 00 x 40mm 0 x 50mm, 1 x 60mm	.55

Wiha Pico Soft Grip TORX®



267 TORX® Screwdriver, With Precision Soft PicoFinish Handle Blade high alloy chrome-vanadium-molybdenum tool steel, hardened, hard chrome finish.

[SHOP](#)

Item No.	Size	mm	Inch	mm	Inch	pkg.
26732	T1	40	1.6	134	5.3	10
26733	T2	40	1.6	134	5.3	10
26735	T3	40	1.6	134	5.3	10
26736	T4	40	1.6	134	5.3	10
26737	T5	40	1.6	134	5.3	10
26739	T6	40	1.6	140	5.5	10
26741	T7	40	1.6	140	5.5	10
26743	T8	40	1.6	140	5.5	10
26745	T9	50	2.0	150	5.9	10
26747	T10	50	2.0	150	5.9	10
26749	T15	60	2.4	160	6.3	10
26751	T20	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate


[SHOP](#)

26793 8 Pc. TORX® Precision Driver Set, With Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

Item No.		lbs.
26793	TORX® : T1, T2, T3, T4, T5, T6, T7, T8 x 40mm	.50


[SHOP](#)

26796 8 Pc. TORX® Precision Driver Set, Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

Item No.		lbs.
26796	TORX® : T5, T6, T7, T8 x 40mm T9, T10 x 50mm, T15, T20 x 60mm	.57

Wiha Pico Soft Grip Screw Holding



267 MagicSpring Screw Holding TORX® Screwdriver, With Wiha-Precision Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. Molded on ergonomic Wiha-PicoFinish precision handle, molded on, soft grips.

[SHOP](#)

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
26721	T6	40	1.6	140	5.5	.03	10
26723	T7	40	1.6	140	5.5	.03	10
26725	T8	40	1.6	140	5.5	.03	10
26727	T9	50	2.0	150	5.9	.04	10
26729	T10	50	2.0	150	5.9	.04	10
26731	T15	60	2.4	160	6.3	.04	10

*Metric dimensions actual - Inch dimensions approximate


[SHOP](#)

26798 6 Pc. MagicSpring Screw Holding TORX® Screwdriver Set, With Wiha-Precision Soft PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. Molded on ergonomic Wiha-PicoFinish precision handle, molded on, soft grips. In storage pouch

Item No.		lbs.
26798	MagicSpring TORX® : T6, T7, T8 x 40mm T9, T10, T15 x 50mm	.45

Pico Soft Grip Precision Chip Lifter


[SHOP](#)

26815 Soft PicoFinish Precision Chip Lifter Blade chrome-vanadium-molybdenum steel, hardened, hard chromed.

Item No.	mm	mm	mm	mm	Inch	lbs.	pkg.
26815	1	3.5	50	150	5.9	.03	1

Standard Soft PicoFinish handle


[SHOP](#)

91118 Rugged Polyester Canvas Storage Pouch Holds 8 Precision Tools up to 170mm in length. Folding pouch. Has security flaps and velcro closer.

Item No.	Size	lbs.	pkg.
91118	14 1/2" W x 7 3/4" L	.13	1

Pico Soft Grip Hex Inch & Metric



[SHOP](#)

263 Hex Inch Screwdriver, With Precision Soft PicoFinish Handle

Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item No.	Inch	mm	Inch	mm	Inch	pkg.
26341	0.028(0.7)	40	1.6	134	5.3	10
26343	0.035(0.9)	40	1.6	134	5.3	10
26345	0.05(1.3)	40	1.6	134	5.3	10
26349	5/64(2.0)	50	2.0	150	5.9	10
26363	1/16	50	2.0	144	5.7	10
26367	3/32	60	2.4	160	6.3	10
26369	7/64	60	2.4	160	6.3	10
26371	1/8	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate



In storage pouch

[SHOP](#)

26392 8 Piece Hex Inch Precision Driver Set, Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed.

Item No.	Hex Inch:	lbs.
26392	.028, .035, .050 x 1.6"	
	5/64, 1/16 x 2.0", 3/32, 7/64, 1/8 x 2.4"	.24



263 Hex Metric Driver, With Precision Soft PicoFinish Handle

Blade high alloy CVM tool steel, hardened, hard chrome finish.

Item No.	mm	mm	Inch	mm	Inch	pkg.
26341	.71(.028)	40	1.6	134	5.3	10
26343	.89(.035)	40	1.6	134	5.3	10
26345	1.27(.050)	40	1.6	134	5.3	10
26347	1.5	50	2.0	144	5.7	10
26349	2.0(5/64)	50	2.0	150	5.9	10
26351	2.5	60	2.4	160	6.3	10
26353	3.0	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate



In storage pouch

[SHOP](#)

26393 7 Piece Hex Metric Precision Driver Set, Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed.

Item No.	Hex Metric:	lbs.
26393	.71, .89, 1.27 x 40mm	
	1.5, 2.0 x 50mm, 2.5, 3.0 x 60mm	.22

Pico Soft Grip Ball End Inch & Metric



[SHOP](#)

264 Ball End Hex Inch Screwdriver, With Precision Soft PicoFinish Handle

Blade high alloy chrome-vanadium-molybdenum tool steel, hardened, hard chrome finish.

Item No.	Inch	Inch	mm	Inch	mm	pkg.
26455	1/16	2.0	50	5.9	150	10
26457	5/64	2.0	50	5.9	150	10
26459	3/32	2.0	50	5.9	150	10
26461	7/64	2.4	60	6.3	160	10
26463	1/8	2.4	60	6.3	160	10
26465	9/64	2.4	60	6.3	160	10
26467	5/32	2.4	60	6.3	160	10

*Metric dimensions actual - Inch dimensions approximate



[SHOP](#)

26493 7 Piece Inch Ball End Hex Precision Driver Set, With Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

Item No.	Ball End Hex Inch:	lbs.
26493	1/16, 5/64, 3/32 x 2.0"	
	7/64, 1/8, 9/64, 5/32 x 2.4"	.27



[SHOP](#)

264 Ball End Hex Metric Screwdriver, With Precision Soft PicoFinish Handle

Blade high alloy chrome-vanadium-molybdenum tool steel, hardened, hard chrome finish.

Item No.	mm	mm	Inch	mm	Inch	pkg.
26441	1.3	40	1.6	134	5.3	10
26443	1.5	50	2.0	150	5.9	10
26445	2.0	50	2.0	150	5.9	10
26447	2.5	60	2.4	160	6.3	10
26449	3.0	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate

Pico Soft Grip Nut Drivers Inch & Metric



SHOP

265 Inch Nut Drivers, With Precision Soft PicoFinish Handle

Blade high alloy chrome-vanadium-molybdenum tool steel, hardened, hard chrome finish.

Item No.	Inch	Inch	mm	Inch	mm	pkg.
26571	3/32	2.4	60	6.3	160	10
26572	7/64	2.4	60	6.3	160	10
26573	1/8	2.4	60	6.3	160	10
26574	9/64	2.4	60	6.3	160	10
26575	5/32	2.4	60	6.3	160	10
26576	3/16	2.4	60	6.3	160	10
26577	7/32	2.4	60	6.3	160	10
26578	1/4	2.4	60	6.3	160	10

*Metric dimensions actual - Inch dimensions approximate



SHOP

26593 8 Piece Inch Nut Driver Set, With Precision Soft PicoFinish Handle

Blade high alloy CVM tool steel, hardened, hard chrome finish. Chrom-Top finish on tip for a perfect fit. In storage pouch

Item No.		lbs.
26593	Inch Nut Drivers: 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32, 1/4" x 2.4"	.72



SHOP

91118 Rugged Polyester Canvas Storage Pouch

Holds 8 Precision Tools up to 170mm in length. Folding pouch. Has security flaps and velcro closer.

Item No.	Size	lbs.	pkg.
91118	14 1/2" W x 7 3/4" L	.13	1



SHOP

265 Metric Nut Drivers, With Precision PicoFinish Handle

Blade high alloy chrome-vanadium-molybdenum tool steel, hardened, hard chrome finish.

Item No.	mm	mm	Inch	mm	Inch	pkg.
26579	1.5	60	2.4	160	6.3	10
26581	2.0	60	2.4	160	6.3	10
26582	2.5	60	2.4	160	6.3	10
26583	3.0	60	2.4	160	6.3	10
26584	3.5	60	2.4	160	6.3	10
26585	4.0	60	2.4	160	6.3	10
26586	4.5	60	2.4	160	6.3	10
26587	5.0	60	2.4	160	6.3	10
26588	5.5	60	2.4	160	6.3	10
26589	6.0	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate



SHOP

26596 8 Piece Metric Nut Driver Set, With Precision Soft PicoFinish Handle

Blade high alloy CVM tool steel, hardened, hard chrome finish. Chrom-Top finish on tip for a perfect fit.

In storage pouch

Item No.		lbs.
26596	Metric Nut Drivers: 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5 x 60mm	.66

Wiha Magnetizer/Demagnetizer

Magnetize or Demagnetize tools and small parts instantly

Shatterproof Box is made from high quality plastic

Uses 2 C8 industrial permanent magnets



(+) to Magnetize

(-) to Demagnetize

40010 Magnetizer and Demagnetizer

To magnetize and demagnetize steel screwdriver blades, tweezers and similar tools. Box high quality plastic, shock-resistant, green, cadmium free.

Application:


To magnetize, lead tool slowly through the (+) opening, to demagnetize guide tool slowly through the (-) opening.

Item No.	Dimensions	lbs.
40010	2.1" x 2.0" x 1.1"	.30

(Parts under 1" Length or 1/8" Diameter may not demagnetize)

SHOP

Wiha Protturn Precision Screwdrivers



[SHOP](#)

95190 6 Piece Slotted/Phillips Protturn Precision Screwdriver Set

Molded on precision handle. Blade high alloy chrome-vanadium-molybdenum tool steel, black finish.

Item No.	Slotted	mm	mm	Phillips	Size	mm	lbs.
95190	Slotted:	1.5mm	40	Phillips:	00	40	.27
		2.5mm	50		0	50	
		3.5mm	60		1	60	



[SHOP](#)

65090 9 Piece Slotted/Phillips Protturn Precision Screwdriver Set

Molded on precision handle. Blade high alloy chrome-vanadium-molybdenum tool steel, black finish.

Item No.	Slotted	mm	mm	mm	mm	Phillips	Size	mm
65090	Slotted:	1.5	40	3.0	60	Phillips:	00	40
		2.0	50	3.5	60		0	50
		2.5	60	4.0	60		1	60



[SHOP](#)

96800 Protturn Precision Chip Lifter

Molded on precision handle. Blade chrome-vanadium-molybdenum tool steel, hardened, black finish.

Item No.	Size	mm	mm	Inch	lbs.	pkg.
96800	1.0	50	145	5.7	.07	1



[SHOP](#)

62990 5 Piece Slotted & Phillips Pocket Pack Set Wiha Protturn precision ball retainer handle & 4 Wiha interchangeable blades.

Set includes the following blades:

- Slotted: 1.5, 2.0, 3.0, 4.0
- Phillips: #000, #00, #0, #1
- lbs. .15




[SHOP](#)

62993 9 Piece Slotted/Phillips/TORX® Work Station Set Wiha Protturn precision ball retainer handle & 8 Wiha interchangeable blades.

Set includes the following blades:

- Slotted: 1.5, 2.0, 3.0, 4.0
- Phillips: #000, #00, #0, #1
- TORX®: T6, T7, T8, T9, T10, T15, T20
- lbs. .64



[SHOP](#)

62995 22 Piece Slotted/Phillips/TORX®/Ball End Hex Inch & Metric Tech Pack Wiha Protturn precision ball retainer handle & 21 Wiha interchangeable blades. Set in canvas storage pouch

Set includes the following blades:

- Slotted: 1.5, 2.0, 3.0, 4.0
- Phillips: #000, #00, #0, #1
- TORX®: T6, T7, T8, T9, T10, T15, T20
- Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0mm
- lbs. .87

62994 14 Piece Inch/Metric Ball End Hex Work Tech Pack

Protturn precision ball retainer handle & 13 Wiha interchangeable blades.

Set includes the following blades:

- Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"
- Hex Metric: 1.5, 2.0, 2.5, 3.0, 4.0mm
- lbs. .66 Set in canvas storage pouch

[SHOP](#)

Wiha SYSTEM 4 Precision Handles and Blades

Rotating Cap
for precise turning & control

Tapered Handle
allows rapid rotation, requires less clearance

Blades
chrome-vanadium-molybdenum steel, hardened, hard chromed. On 4mm Hex shafts

Tips
Exact fit, precision machined

Precision Handle
high quality plastic, cadmium free. ESD Safe or Standard styles

15mm
Collet Lock Handle adjustable blade length from 15 to 95mm/.6" to 3.75"
95mm

28000 ESD Safe Dissipative Precision Handle with rotating control cap. Surface resistant 10^6 - 10^9 Ohms. 4 mm hex retainer for all SYSTEM 4 interchangeable blades. Tapered handle, high quality plastic, impact resistant. Ball retainer hold. 110mm/4.3" OAL

Item	No.	mm	Inch	mm	Inch	lbs.
	28000	4.0	.1574	14.0	.55	.04

[SHOP](#)

28001 ESD Safe Dissipative Precision Adjustable Handle with rotating control cap.

Advantages:

- Use in ESD sensitive applications. Surface resistant 10^6 - 10^9 Ohms.
- Collet lock allows for quick & easy adjustment.
- Holds blade securely in place. Accepts all SYSTEM 4 blades. 110mm/4.3" OAL

Item	No.	mm	Inch	mm	Inch	lbs.
	28001	4.0	.1574	14.0	.55	.04

[SHOP](#)

26900 SYS 4 Standard Precision Handle, with rotating control cap. Accepts all SYSTEM 4 interchangeable blades. Wiha Precision handle, tapered, impact resistant. Ball retainer hold. 110mm/4.3" OAL

Item	No.	mm	Inch	mm	Inch	lbs.
	26900	4.0	.1574	14.0	.55	.04

[SHOP](#)

26901 SYSTEM 4 Standard Precision Adjustable handle with rotating control cap.

Advantages:

- Allows adjustable blade from 15 to 95mm.
- Collet lock allows for quick & easy adjustment.
- Holds blade securely in place. Accepts all SYSTEM 4 blades. 110mm/4.3" OAL

Item	No.	mm	Inch	mm	Inch	lbs.
	26901	4.0	.1574	14.0	.55	.06

[SHOP](#)

269 SYSTEM 4 Combined Slotted/Phillips Reversible Blade High alloy CVM steel, hardened, hard chromed.

Item	No.	mm	Size	mm	Inch	lbs.
	26971	1.5 + 000		120	4.7	.05
	26972	2.0 + 00		120	4.7	.05
	26973	3.0 + 0		120	4.7	.05
	26974	4.0 + 1		120	4.7	.06

[SHOP](#)

269 SYSTEM 4 Pozidriv® Reversible Blade High alloy CVM steel, hardened, hard chromed. Wiha vapor Chrome-Top finish on tips.

Item	No.	Size	Size	mm	Inch	lbs.
	26922	0 + 1		120	4.7	.03

[SHOP](#)

269 SYSTEM 4 Slotted Reversible Blade High alloy CVM steel, hardened, hard chromed. Wiha vapor Chrome-Top finish on tips.

Item	No.	mm	mm	mm	Inch	lbs.
	26903	1.5 + 3.0		120	4.7	.05
	26904	2.0 + 3.5		120	4.7	.05
	26905	2.5 + 4.0		120	4.7	.06

[SHOP](#)

269 SYS 4 TORX® Reversible Blade High alloy CVM steel, hardened, vapor chrome protected, Wiha vapor Chrome-Top finish on tips. 120mm/4.7" OAL.

Item	No.	Size	Size	lbs.
	26951	T6 + T8		.03
	26952	T7 + T9		.03
	26953	T10 + T15		.03
	26954	T15 + T20		.03

[SHOP](#)

269 SYSTEM 4 Phillips Reversible Blade High alloy CVM steel, hardened, hard chromed. Wiha vapor Chrome-Top finish on tips.

Item	No.	Size	Size	mm	Inch	lbs.
	26911	000 + 00		120	4.7	.03
	26912	0 + 1		120	4.7	.03

[SHOP](#)

269 SYSTEM 4 TORX® Interchangeable Blade High alloy CVM steel, hardened, Wiha vapor Chrome-Top finish on tips. 120mm/4.7" OAL

Item	No.	Size	lbs.
	26955	T3	.03
	26956	T4	.03
	26957	T5	.03

[SHOP](#)

Wiha SYSTEM 4 Precision Blades




269 SYSTEM 4 Inch Hex Sizes,

Interchangeable Blade High alloy CVM steel, hardened, corrosion protected.

Item	Hex	Inch	mm	Inch	lbs.
26921	.050	120	4.7	.06	
26923	1/16	120	4.7	.06	
26924	5/64	120	4.7	.06	
26925	3/32	120	4.7	.06	
26926	7/64	120	4.7	.06	
26927	1/8	120	4.7	.06	
26928	9/64	120	4.7	.06	
26929	5/32	120	4.7	.06	

[SHOP](#)



280 SYSTEM 4 Inch Ball End Hex

Interchangeable Blade High alloy tool steel, hardened, corrosion protected. Ball end works at 30° angle entry for easy access to fasteners.

Item	Hex	Inch	mm	Inch	lbs.
28021	.050	120	4.7	.06	
28023	1/16	120	4.7	.06	
28024	5/64	120	4.7	.06	
28025	3/32	120	4.7	.06	
28026	7/64	120	4.7	.06	
28027	1/8	120	4.7	.06	
28028	9/64	120	4.7	.06	
28029	5/32	120	4.7	.06	

[SHOP](#)



269 SYSTEM 4 Metric Hex Sizes,

Interchangeable Blade High alloy CVM steel, hardened, corrosion protected.

Item	Hex	mm	mm	Inch	lbs.
26913	0.7	120	4.7	.06	
26914	0.9	120	4.7	.06	
26915	1.3	120	4.7	.06	
26916	1.5	120	4.7	.06	
26917	2.0	120	4.7	.06	
26918	2.5	120	4.7	.06	
26919	3.0	120	4.7	.06	
26920	4.0	120	4.7	.06	

[SHOP](#)



280 SYSTEM 4 Metric Ball End Hex

Interchangeable Blade High alloy tool steel, hardened, corrosion protected. Ball end works at 30° angle entry for easy access to fasteners.

Item	Hex	mm	mm	Inch	lbs.	pkg.
28033	1.5	120	4.7	.06	1	
28034	2.0	120	4.7	.06	1	
28035	2.5	120	4.7	.06	1	
28036	3.0	120	4.7	.06	1	
28037	4.0	120	4.7	.06	1	

[SHOP](#)



269 SYS 4 Metric Ball End & Standard

Hex, Reversible Blade CVM steel, hardened, hard chromed. Wiha vapor Chrome-Top finish on tips. One side hex, other side ballpoint hex.

Item	Hex	mm	mm	Inch	lbs.
26932	1.3 + 1.3	120	4.7	.05	
26933	1.5 + 1.5	120	4.7	.05	
26934	2.0 + 2.0	120	4.7	.06	
26935	2.5 + 2.5	120	4.7	.06	
26936	3.0 + 3.0	120	4.7	.06	
26937	4.0 + 4.0	120	4.7	.06	

[SHOP](#)



269 SYSTEM 4 Nut Driver Inch,

Interchangeable Blade High alloy chrome-vanadium-molybdenum steel, hardened, corrosion protected. 120mm/4.7" OAL

Item	Nut Driver	Inch	Inch	lbs.
26962	3/32	.16	.16	.04
26963	7/64	.20	.20	.04
26964	1/8	.20	.20	.04
26965	9/64	.21	.24	.04
26966	5/32	.22	.24	.04
26967	3/16	.26	.28	.04
26968	7/32	.30	.32	.04
26969	1/4	1.34	.36	.04

[SHOP](#)



269 SYSTEM 4 Nut Driver Metric,

Interchangeable Blade High alloy chrome-vanadium-molybdenum steel, hardened, corrosion protected. 120mm/4.7" OAL

Item	Nut Driver	mm	mm	Inch	lbs.
26940	1.5 + 1.8	.12	.12	.03	
26941	2.0 + 2.5	.16	.16	.03	
26938	1.5 -	.11	.11	.04	
26939	1.8 -	.12	.12	.04	
26949	2.0 -	.13	.13	.06	
26950	2.5 -	.16	.16	.06	
26942	3.0 -	.20	.20	.06	
26943	3.2 -	.20	.20	.06	
26944	3.5 -	.22	.24	.06	
26945	4.0 -	.22	.24	.06	
26946	4.5 -	.25	.28	.06	
26947	5.0 -	.27	.28	.06	
26948	5.5 -	.30	.32	.06	

[SHOP](#)

Wiha SYSTEM 4 Drive-Loc Precision Locking Tools



26961 ESD Safe Dissipative Precision Drive-Loc Handle

Surface resistant 10^6 - 10^9 Ohms. 4 mm hex retainer for all SYSTEM 4 interchangeable blades. Ball retainer hold. 105mm/4.13" OAL

Item No.	mm	Inch	mm	Inch	lbs.
26961	4.0	.1574	23	.91	.08



269 SYSTEM 4 Slotted Drive-Loc Reversible Locking Blades

On 4mm Hex blades

Item No.	mm	mm	lbs.
26958	1.5 + 3.0		.02
26959	2.0 + 3.5		.02
26960	2.5 + 4.0		.02



269 SYSTEM 4 Phillips Drive-Loc Reversible Locking Blades

On 4mm Hex blades

Item No.	Size	Size	lbs.
26975	000 + 00		.02
26976	0 + 1		.02



269 SYSTEM 4 TORX Drive-Loc Reversible Locking Blades

On 4mm Hex blades

Item No.	Size	Size	lbs.
26977	T1 + T2		.02
26978	T3 + T4		.02
26979	T5 + T6		.02
26980	T6 + T8		.02
26981	T7 + T9		.02
26982	T10 + T15		.02



280 SYSTEM 4 Pozidriv Drive-Loc Reversible Locking Blades

On 4mm Hex blades

Item No.	Size	Size	lbs.
28002	0 + 1		.02



280 SYSTEM 4 Metric Hex Drive-Loc Reversible Locking Blades

On 4mm Hex blades

Item No.	mm	mm	lbs.
28003	1.3 + 1.3		.02
28004	1.5 + 1.5		.02
28005	2.0 + 2.0		.02
28006	2.5 + 2.5		.02
28007	3.0 + 3.0		.02
28008	4.0 + 4.0		.02



280 SYSTEM 4 Metric Nut Drivers Drive-Loc Reversible Locking Blades

On 4mm Hex blades

Item No.	mm	mm	lbs.
28009	1.5 + 1.8		.02
28010	2.0 + 2.5		.02
28011	3.0 + 3.0		.02
28012	3.2 + 3.2		.02
28013	3.5 + 3.5		.02
28014	4.0 + 4.0		.02
28015	4.5 + 4.5		.02
28016	5.0 + 5.0		.02
28017	5.5 + 5.5		.02



26985 12 Piece SYSTEM 4 Precision ESD Drive-Loc Set

In storage pouch

Item No.	
26985	ESD Safe Drive-Loc Handle
	Slotted: 1.5x3.0, 2.0x3.5, 2.5x4.0
lbs. .44	Phillips: 000x00, 0x1
	TORX: T1xT2, T3xT4, T5xT6, T6xT8, T7xT9, T10xT15

Wiha Canvas Pouch Sets



SHOP

Canvas Pouch

26990 4 Piece Slotted & Phillips Precision Interchangeable Blade Set


Wiha ESD Safe precision collet lock handle and 3 Wiha interchangeable blades.

26990 Set includes the following blades:

● **Slotted:** 2.0, 3.0, 4.0mm

⊕ **Phillips:** 00, 0, 1

↔ lbs. .17



SHOP

Canvas Pouch

26991 6 Piece Slotted & Phillips Precision Interchangeable Blade Set


Wiha ESD Safe precision collet lock handle and 5 Wiha interchangeable blades. In canvas pouch.

26991 Set includes the following blades:

● **Slotted:** 1.5, 2.0, 2.5, 3.0, 3.5, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

↔ lbs. .29



SHOP

Canvas Pouch

26992 17 Pc. Slotted, Phillips and Ball End Hex Metric/Inch Precision Interchangeable Blade Set

Wiha ESD Safe precision collet lock handle and 15 Wiha interchangeable blades.

26992 Set include the following blades:

● **Slotted:** 1.5, 2.0, 3.0, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

● **Ball End Hex Inch:** .050, 1/16, 5/64, 7/64, 3/32, 1/8"

● **Ball End Hex Metric:** 1.5, 2.0, 2.5, 3.0, 4.0mm

ESD Safe Precision Chip Lifter

↔ lbs. .63



SHOP

Canvas Pouch

28080 22 Piece Slotted, Phillips, TORX® & Hex Precision Interchangeable Blade Set

Wiha ESD Safe precision collet lock handle and 20 Wiha interchangeable blades.

28080 Set includes the following blades:

● **Slotted:** 1.5, 2.0, 3.0, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

⚙ **TORX®:** T3, T4, T5, T6, T7, T8, T9, T10, T15

● **Hex:** .028, .035


● **Ball Hex:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

ESD Safe Precision Chip Lifter

↔ lbs. .33



ESD Technicians Kit Precision Screwdrivers & Tweezers



SHOP



Canvas Pouch

44590 12 Pc. Slotted, Phillips and TORX® Precision Interchangeable Blade Set

Wiha ESD Safe precision collet lock handle, 7 Wiha interchangeable blades & 4 ESD Safe Tweezers.

44590 Set includes the following blades:

● **Slotted:** 2.0, 3.0, 4.0mm

⊕ **Phillips:** 00, 0, 1

⚙ **TORX®:** T6, T7, T8, T9, T10, T15

ESD Safe Precision Tweezers:


44501 Fine Point - AA SA

44509 Extra Fine Point - 5 SA


44505 Flat and Blunt - 2a SA

44510 Curved Fine Point - 7a SA

↔ lbs. .60



Slotted, Phillips, TORX® Set In Steel Box



SHOP

28094 11 Piece Slotted, Phillips & TORX® Precision Interchangeable Blade Set

Wiha ESD Safe precision collet lock handle and 10 Wiha interchangeable blades.


28094 Set includes the following blades:

● **Slotted:** 1.5, 2.0, 3.0, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

⚙ **TORX®:** T3, T4, T5, T6, T7, T8, T9, T10, T15

↔ lbs. 1.51



SHOP

26993 6 Piece Slotted & Phillips Precision Interchangeable Blade Set

Wiha ESD Safe precision collet lock handle and 5 Wiha interchangeable blades.

26993 Set includes the following blades:


● **Slotted:** 1.5, 2.0, 2.5, 3.0, 3.5, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

↔ lbs. .87



ESD Anti-Static Vinyl Pouch Set



SHOP

28091 6 Piece Slotted & Phillips Precision Interchangeable Blade Set

Wiha-ESD Safe precision collet lock handle and 5 Wiha interchangeable blades.

28091 Set includes the following blades:

↓ **Slotted:** 1.5, 2.0, 2.5, 3.0, 3.5, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

↔ **lbs.** .25

ESD Safe



SHOP

28097 9 Piece Slotted, Phillips and TORX Precision Interchangeable Blade Set

Wiha ESD Safe precision collet lock handle and 8 Wiha Interchangeable blades.

28097 Set includes the following blades:


↓ **Slotted:** 1.5, 2.0, 3.0, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

⊗ **TORX:** T5, T6, T7, T8, T9, T10, T15

↔ **lbs.** .33

ESD Safe



SHOP

28084 13 Piece Slotted, Phillips and Ball End Hex Inch Precision Interchangeable Blade Set

Wiha ESD Safe precision collet lock handle and 12 Wiha interchangeable blades.

28084 Set includes the following blades:

↓ **Slotted:** 1.5, 2.0, 3.0, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

⬢ **Ball End Hex Inch:** .050, 1/16,

5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

↔ **lbs.** .44

ESD Safe



SHOP

28087 8 Piece TORX Precision Interchangeable Blade Set

Wiha-ESD Safe precision collet lock handle and 7 Wiha interchangeable blades.

28087 Set includes the following blades:


⊗ **TORX Sizes on standard blades:** T3, T4, T5

⊗ **TORX Sizes on reversible blades:**

T6, T7, T8, T9, T10, T15, T20

↔ **lbs.** .29

ESD Safe



SHOP

26996 5 Piece Slotted & Phillips Precision Interchangeable Blade Set

Wiha ESD Safe precision collet lock handle and 4 Wiha interchangeable blades.

26996 ⊕ **Phillips:** 000, 00, 0, 1

↓ **Slotted:** 1.5, 2.0, 3.0, 3.5mm

↔ **lbs.** .54



SHOP

26997 9 Pc. Slotted, Phillips and TORX Precision Interchangeable Blade Set

Wiha ESD Safe precision collet lock handle and 8 Wiha Interchangeable blades.

26997 ⊕ **Phillips:** 000, 00, 0, 1

↓ **Slotted:** 1.5, 2.0, 2.5, 3.0, 3.5, 4.0mm

⊗ **TORX:** T6, T7, T8, T9, T10, T15

↔ **lbs.** .64



SHOP

26999 9 Piece Hex Metric Precision Blade Set

Wiha ESD Safe precision collet lock handle and 8 Wiha interchangeable blades.

26999 ⬢ **Hex Metric:** .7, .9, 1.3, 1.5,

2.0, 2.5, 3.0, 4.0mm

↔ **lbs.** .66



SHOP

26989 9 Piece Hex Inch Precision Blade Set

Wiha ESD Safe precision collet lock handle and 8 Wiha interchangeable blades.

26989 ⬢ **Hex Inch:** .050, 1/16, 5/64, 3/32,

7/64, 1/8, 9/64, 5/32"

↔ **lbs.** .64



SHOP

26995 5 Piece TORX Precision Blade Set

Wiha ESD Safe precision collet lock handle and 4 interchangeable blades.

26995 ⊗ **TORX:** T6, T7, T8, T9, T10, T15, T20

↔ **lbs.** .52



SHOP

26987 8 Piece TORX Precision Blade Set

Wiha ESD Safe precision collet lock handle and 7 interchangeable blades.

26987 Set includes the following blades:

⊗ **TORX standard blades:** T3, T4, T5

⊗ **TORX reversible blades:**

T6, T7, T8, T9, T10, T15, T20

↔ **lbs.** .62



Wiha SYSTEM 4 Micro Bits

SYSTEM 4 Handles & Micro Bits

Rotating Cap
for precise
turning and
control

Tips
Exact fit,
precision
machined

Tapered Handle
allows rapid
rotation, requires
less clearance

Bits High alloy
CVM steel, hardened

Use bits directly in handle or with 4" bit extension



75800 SYSTEM 4 Standard Precision Bit

Handle Accepts all SYSTEM 4 Series bits.
110mm/4.3" OAL

Item					
No.	mm	Inch	mm	Inch	lbs.
75800	4.0	.1574	14.0	.55	.06



75801 SYSTEM 4 ESD Safe Dissipative

Precision Bit Handle 110mm/4.3" OAL

Advantages:

- For working in ESD sensitive applications
Surface resistant 10^6 - 10^9 Ohms
- Ball retainer holds bits securely in place
- Accepts all SYSTEM 4 Series bits

Item					
No.	mm	Inch	mm	Inch	lbs.
75801	4.0	.1574	14.0	.55	.06

SYSTEM 4 Micro Bit Extension Blades



75900 Extension Blade For SYS 4 Micro Bits

Shaft CVM steel, hardened, corrosion protected.
Ball retainer bit extension for 4mm bits.

Item					
No.	Size	mm	mm	lbs.	
75900	4.0	100	4.0	.07	



75901 Magnetic Bit Extension Blade For SYS 4 Micro Bits

Shaft CVM steel, hardened, corrosion protected. Magnetic bit holder.

Item					
No.	Size	mm	mm	lbs.	
75901	4.0	100	4.0	.04	



750 SYSTEM 4 Slotted Micro Bits

CVM steel, hardened, on 4 mm hex stock.

Item					
No.	mm	mm	Inch	lbs.	
75008	0.8	28	1.1	.01	
75012	1.2	28	1.1	.01	
75015	1.5	28	1.1	.01	
75018	1.8	28	1.1	.01	
75020	2.0	28	1.1	.01	
75025	2.5	28	1.1	.01	
75030	3.0	28	1.1	.01	
75035	3.5	28	1.1	.01	
75040	4.0	28	1.1	.01	



751 SYSTEM 4 Phillips Micro Bits

CVM steel, hardened, on 4 mm hex stock.

Item					
No.	Size	mm	Inch	lbs.	
75105	000	28	1.1	.01	
75110	00	28	1.1	.01	
75115	0	28	1.1	.01	
75120	1	28	1.1	.01	



753 SYSTEM 4 Hex Metric Micro Bits

CVM steel, hardened, on 4 mm hex stock.

Item					
No.	mm	mm	Inch	lbs.	
75307	.7	28	1.1	.01	
75309	.9	28	1.1	.01	
75313	1.3	28	1.1	.01	
75315	1.5	28	1.1	.01	
75320	2.0	28	1.1	.01	
75325	2.5	28	1.1	.01	
75330	3.0	28	1.1	.01	
75340	4.0	28	1.1	.01	



753 SYSTEM 4 Hex Inch Micro Bits

CVM steel, hardened, on 4 mm hex stock.

Item					
No.	Inch	mm	Inch	lbs.	
75307	.028	28	1.1	.01	
75309	.035	28	1.1	.01	
75313	.050	28	1.1	.01	
75350	1/16	28	1.1	.01	
75352	5/64	28	1.1	.01	
75354	3/32	28	1.1	.01	
75356	7/64	28	1.1	.01	
75358	1/8	28	1.1	.01	
75360	9/64	28	1.1	.01	
75340	5/32	28	1.1	.01	



757 SYSTEM 4 TORX® Micro Bits

CVM steel, hardened, on 4 mm stock.

Item					
No.	Size	mm	Inch	lbs.	
75703	T3	28	1.1	.01	
75704	T4	28	1.1	.01	
75705	T5	28	1.1	.01	
75706	T6	28	1.1	.01	
75707	T7	28	1.1	.01	
75708	T8	28	1.1	.01	
75709	T9	28	1.1	.01	
75710	T10	28	1.1	.01	
75715	T15	28	1.1	.01	
75720	T20	28	1.1	.01	



757 SYSTEM 4 Security TORX® Micro Bits

CVM steel, hardened, on 4 mm stock.

Item					
No.	Size	mm	Inch	lbs.	
75727	T7s	28	1.1	.01	
75728	T8s	28	1.1	.01	
75729	T9s	28	1.1	.01	
75735	T10s	28	1.1	.01	
75739	T15s	28	1.1	.01	
75742	T20s	28	1.1	.01	



753 SYS 4 Metric Security Hex Micro Bits

CVM steel, hardened, on 4 mm hex stock.

Item					
No.	mm	mm	Inch	lbs.	
75322	2.0	28	1.1	.01	
75327	2.5	28	1.1	.01	
75332	3.0	28	1.1	.01	
75342	4.0	28	1.1	.01	

753 SYS 4 Security Hex Inch Micro Bits

Item					
No.	Inch	mm	Inch	lbs.	
75362	5/64	28	1.1	.01	
75364	3/32	28	1.1	.01	
75366	7/64	28	1.1	.01	
75368	1/8	28	1.1	.01	
75370	9/64	28	1.1	.01	
75372	5/32	28	1.1	.01	

Micro Bit 1/4" Drive Power Tool Adapter



75902 Micro Bit 1/4" Drive Power Tool Adapter

Shaft CVM steel, hardened, corrosion protected. For 4mm bits. 2.3" OAL

Item					
No.	Size	mm	mm	lbs.	
75902	4.0	60	4.0	.07	

Wiha SYSTEM 4 Micro Bits



757 SYSTEM 4 Pentalobe IPR Micro Bits

CVM steel, hardened, on 4 mm hex stock.

Item No.	Size	mm	Inch	lbs.	SHOP
75743	P1	28	1.1	.01	
75744	P2	28	1.1	.01	
75745	P3	28	1.1	.01	
75746	P4	28	1.1	.01	
75747	P5	28	1.1	.01	
75748	P6	28	1.1	.01	



758 SYSTEM 4 Metric & Inch Nut Setters

CVM steel, hardened, on 4 mm hex stock.

Item No.	Metric	mm	mm	Inch	lbs.	SHOP
75820	2.0	30	1.2	.01		
75821	2.5	30	1.2	.01		
75822	3.0	30	1.2	.01		
75823	3.5	30	1.2	.01		
75824	4.0	30	1.2	.01		
75825	4.5	30	1.2	.01		
75826	5.0	30	1.2	.01		
75827	5.5	30	1.2	.01		
Inch	mm	mm	Inch	lbs.		
75810	5/64	30	1.2	.01		
75811	3/32	30	1.2	.01		
75812	7/64	30	1.2	.01		
75813	1/8	30	1.2	.01		
75814	9/64	30	1.2	.01		
75815	5/32	30	1.2	.01		
75816	3/16	30	1.2	.01		
75817	7/32	30	1.2	.01		

1/4" Drive Micro Bit Tool Adapters



75802 Micro Bit To 1/4" Drive Insert Bit Adapter

magnets to hold 4mm Micro Bits

Item No.	Size	mm	mm	lbs.	SHOP
75802	4.0	25	4.0	.01	

75803 Long Micro Bit To 1/4" Drive Insert Bit Adapter

Uses spring clip non-magnetic to hold 4mm Micro Bits

Item No.	Size	mm	mm	lbs.	SHOP
75803	4.0	38	4.0	.02	

Micro Bit Handle Storage Sets

Micro precision bits on 4mm hex drive
Storage handle
Bits hardened for extreme durability
Bits of exclusive CRM-72 tool steel



75981 Micro Bit Handle Storage Slotted & Phillips Bit Set, 7 Pcs.

Wiha precision storage handle & 6 Micro Bit interchangeable 4mm bits.

Item No.	Set with Micro Bit Precision Storage Handle
75981	Slotted: 1.2, 1.5, 2.0mm Phillips: 000, 00, 0 lbs. .08



75985 Micro Bit Handle Storage TORX Bit Set, 7 Pcs.

Wiha precision storage handle & 6 Micro Bit interchangeable 4mm bits.

Item No.	Set with Micro Bit Precision Storage Handle
75985	TORX T3, T4, T5, T6, T7, T8 lbs. .08



75983 Micro Bit Handle Storage Hex Inch Bit Set, 7 Pcs.


Wiha precision storage handle & 6 Micro Bit interchangeable 4mm bits.

Item No.	Set with Micro Bit Precision Storage Handle
75983	Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8" lbs. .08

Protturn Precision Power Driver Bit Set

75989 SYSTEM 4 Protturn Precision Power Screwdriver Set With Micro Bits, 40 Pcs. In Storage Box. Includes Wiha precision handle, Protturn Power Screwdriver & 38 interchangeable Micro bits.

Item No.	Set with System 4 Standard Precision Handle
75989	Set includes the following bits: Slotted: 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm Phillips: 000, 00, 0, 1 TORX: T3, T4, T5, T6, T7, T8, T9, T10, T15 Hex Metric: .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm Hex Inch: .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"



Wiha SYS 4 Micro Bits & Compact Bit Sets

75999 SYSTEM 4 Slotted, Phillips, Hex Inch & Metric Precision Interchangeable Bit Set, 26 Pcs. In Compact Fold Out Box. Wiha precision handle, bit extension & 24 interchangeable bits.

Item No. Combination Bit Set

75999 Set with Standard Precision Handle

Set includes the following bits:

↓ **Slotted:** 1.5, 2.0, 3.0, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

⬢ **Hex Metric:** .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm

⬢ **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

○ **100mm Bit Extension**

↔ lbs. .64



26 Pc. Set

75792 SYSTEM 4 TORX® Precision Interchangeable Bit Set, 11 Pcs. In Compact Fold Out Box.

Sets includes Wiha precision handle, bit extension and 9 Wiha interchangeable bits.

Item SYSTEM 4 TORX® Bit Set

No. Set with ESD Safe Precision Handle

75792 and the following bits:

⬢ **TORX®:**

T3, T4, T5, T6, T7, T8, T9, T10, T15

○ **100mm Bit Extension**

↔ lbs. .54



11 Pc. Set

75395 SYSTEM 4 Hex Inch & Metric Precision Interchangeable Bit Set, 18 Pcs. In Compact Fold Out Box. Wiha precision handle, bit extension and 16 Wiha interchangeable bits.

Item No. Combination Bit Set

75395 Set with Standard Precision Handle

Includes the following bits:

⬢ **Hex Metric:** .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm

⬢ **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

○ **100mm Bit Extension**

↔ lbs. .58



18 Pc. Set

759 sets SYSTEM 4 Slotted/Phillips/Hex Inch/TORX® Precision Interchangeable Bit Set, 27 Pcs. In Compact Fold Out Box. Sets include your choice of Wiha precision handle, bit extension and 25 Wiha interchangeable bits.

Item Handle Options for SYSTEM 4

No. Combination Bit Sets

75991 Set with Standard Precision Handle

75992 Set with ESD Safe Precision Handle

Sets include the following bits:

↓ **Slotted:** 1.5, 2.0, 3.0, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1


⬢ **TORX®:** T3, T4, T5,

T6, T7, T8, T9, T10, T15

⬢ **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

○ **100mm Bit Extension**

↔ lbs. .64



27 Pc. Set

75996 SYSTEM 4 Interchangeable Bit Set, 40 Pcs. In Storage Box. Includes Wiha precision handle, bit extension & 38 interchangeable bits.

Item SYSTEM 4

No. Combination Bit Set

75996 Set with ESD Safe Precision Handle

Set includes the following bits:

↓ **Slotted:** 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1



⬢ **TORX®:** T3, T4, T5, T6, T7, T8, T9, T10, T15

⬢ **Hex Metric:** 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm

⬢ **Hex Inch:** .028, .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

○ **100mm Bit Extension**

↔ lbs. 1.04



40 Pc. Set

75994 SYSTEM 4 Slotted/Phillips/Hex Metric/TORX® Precision Interchangeable Bit Set, 27 Pcs. In Compact Fold Out Box.

Set includes Wiha precision handle, bit extension and 25 Wiha interchangeable bits.

Item SYSTEM 4

No. Combination Bit Set

75994 Set with ESD Safe Precision Handle

Set includes the following bits:

↓ **Slotted:** 1.5, 2.0, 3.0, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1


⬢ **TORX®:**

T3, T4, T5, T6, T7, T8, T9, T10, T15

⬢ **Hex Metric:** .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm

○ **100mm Bit Extension**

↔ lbs. .64



27 Pc. Set

Technicians MicroBit Sets

- Micro Precision Bits on 4mm Hex Drive
- Bits of Exclusive CRM-72 Tool Steel
- Handle uses non-magnetic ball retainer
- Use bits in extension only
- Standard extension adds 4" to length
- Non-magnetic bit extension

Rotation cap
Light weight & compact
Handle tapered for precise control
Bits hardened for extreme durability

Surface resistance of handles is $10^6 - 10^9$ Ohms



75093 SYSTEM 4 Slotted, Phillips, TORX® Compact ESD Precision Interchangeable Bit Set, 16 Pcs. Wiha precision handle, bit extension & 14 interchangeable bits.

Item No. Combination Bit Set

75093 Set with ESD Safe Precision Handle

↓ **Slotted:** 1.5, 2.0, 2.5, 3.0mm

⊕ **Phillips:** 00, 0, 1

⊗ **TORX®:** T6, T7, T8, T9, T10, T15, T20

○ **100mm Bit Extension**

↪ **lbs. .17**

[SHOP](#)



75094 SYSTEM 4 Slotted, Phillips, Hex Inch Compact ESD Precision Interchangeable Bit Set, 16 Pcs. Wiha precision handle, bit extension & 14 interchangeable bits.

Item No. Combination Bit Set

75094 Set with ESD Safe Precision Handle

↓ **Slotted:** 1.5, 2.0, 2.5, 3.0mm


⊕ **Phillips:** 00, 0, 1

⊗ **Hex Inch:** .035, .050, 1/16, 5/64, 3/32, 7/64, 1/8"

○ **100mm Bit Extension**

↪ **lbs. .17**

[SHOP](#)



75095 SYSTEM 4 Slotted, Phillips, Hex Metric Compact ESD Precision Interchangeable Bit Set, 16 Pcs. Wiha precision handle, bit extension & 14 interchangeable bits.

Item No. Combination Bit Set

75095 Set with ESD Safe Precision Handle

↓ **Slotted:** 1.5, 2.0, 2.5, 3.0mm

⊕ **Phillips:** 00, 0, 1

⊗ **Hex Metric:** .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm

○ **100mm Bit Extension**

↪ **lbs. .17**

[SHOP](#)



75096 SYSTEM 4 Hex Inch & Metric Compact ESD Precision Interchangeable Bit Set, 16 Pcs. Wiha precision handle, bit extension & 14 interchangeable bits.

Item No. Combination Bit Set

75096 Set with ESD Safe Precision Handle

⊗ **Hex Inch:** 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"


⊗ **Hex Metric:** .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm

○ **100mm Bit Extension**

↪ **lbs. .17**

[SHOP](#)

SYS 4 Interchangeable Bit Sets



75990 SYSTEM 4 Interchangeable Bit Set, 40 Pcs. In Canvas Pouch. Includes Wiha precision handle, bit extension & 38 interchangeable bits.

Item No. SYSTEM 4 Combination Bit Set

No. Set with ESD Safe Precision Handle

75990 Set includes the following bits:

↓ **Slotted:** 0.8, 1.2, 1.5,

1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

⊗ **TORX®:** T3, T4, T5, T6, T7, T8, T9, T10, T15

⊗ **Hex Metric:** 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm

⊗ **Hex Inch:** .028(.7), .035(.9), .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"


○ **100mm Bit Extension**

↪ **lbs. .65**



40 Pc. Set

[SHOP](#)



75965 SYSTEM 4 Master Tech ESD & Ratchet With Micro Bits, 65 Pieces In Storage Box. Includes Wiha precision ESD Safe handle, micro bit extension, 72 tooth ratchet & 62 interchangeable micro bits.

Item No. With ESD Precision Handle, 1/4" Ratchet, Micro Bit Extension

75965 Set includes the following micro bits:

↓ **Slotted:** 0.8, 1.2, 1.5, 1.8, 2.0, 2.5, 3.0, 3.5, 4.0mm

⊕ **Phillips:** 000, 00, 0, 1

⊗ **TORX®:** T3, T4, T5, T6, T7, T8, T9, T10, T15, T20

⊗ **Hex Metric:** .7, .9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0mm

⊗ **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

○ **Nut Drivers Metric:** 2.0, 2.5, 3.0, 3.5, 4.0, 4.5, 5.0, 5.5mm

○ **Nut Drivers Inch:** 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 7/32"

⊗ **Pentalobe:** P1, P2, P3, P4, P5, P6

Magnetic 1/4" to 4mm Adapter

↪ **lbs. 1.16**

[SHOP](#)

Wiha Precision Electronic Pliers & Cutters

Electronics pliers with cutting edges are designed especially for cutting soft to medium hard wires.

C70 tool steel HR60 hardness

Glare free
black finish

Precision ground
cutting edges for
smooth cuts



The Comfortable Precision Pliers & Cutters




Velvet soft ergonomically
designed multi component
handle

Lay-on, riveted
precision joint

Light weight design for maximum
user comfort in production work

Electronic Diagonal Cutters



Full Flush

56818 Precision Electronic Diagonal Cutters, Wide Pointed Head


Cutting edge - full flush. With return spring. C70 special tool steel.

For an absolutely flush cut of copper wire.

#56818	mm	Inch	Cut Capacity	Pkg.	lbs.
	138	5.5	1.3mm/16AWG	1	.22

SHOP

Electronic Diagonal Cutters



Semi Flush

56815 Precision Electronic Diagonal Cutters, Wide Pointed Head


Cutting edge - semi flush. With return spring. C70 special tool steel.

Universal small diagonal cutter for cutting copper wires.

Item No.	Cut		Medium		Pkg.	lbs.
#56815	mm	Inch	Capacity	Hard Wire		
	138	5.5	2.0mm/12AWG	0.8	1	.23

SHOP

Electronic Diagonal Cutters



Full Flush

Wire Holding Spring

56825 Precision Electronic Diagonal Cutters, Wide Shape With


Wire Holding Spring Wide, Pointed head. Cutting edge - full flush.

With return spring & fixture for holding ends of wires that have been cut off. C70 special tool steel. For an absolutely flush cut of copper wire.

#56825	mm	Inch	Cut Capacity	Pkg.	lbs.
	138	5.5	1.3mm/16AWG	1	.23

SHOP

Electronic Diagonal Cutters



Full Flush

56812 Precision Electronic Diagonal Cutters, Narrow Shape

Extra narrow, short head for working in particularly restricted spaces.

Cutting edge - full flush. With return spring. C70 special tool steel. For absolutely flush cutting of copper wires in difficult to access locations.


#56812	mm	Inch	Cut Capacity	Pkg.	lbs.
	118	4.5	0.8mm/20AWG	1	.19

SHOP

Electronic Diagonal Cutters



Wire Holding Spring




Full Flush

56813 Precision Electronic Diagonal Full Flush Cutters With Wire Trapping Spring Extra narrow, short head for working in particularly restricted spaces. Cutting edge - full flush. With return spring. C70 special tool steel. For absolutely flush cutting of copper wires in difficult to access locations.

#56813	mm	Inch	Cut Capacity	Pkg.	lbs.
	128	5.0	1.0mm/18AWG	1	.19

[SHOP](#)

Electronic Oblique 48° Cutter



Full Flush


56833 Electronic Oblique 48° Cutter

Wide pointed head. Cutting edge - full flush. With cutting edge at 48° for cutting obliquely from above or from the side. C70 special tool steel. For absolutely flush cutting of copper wires in difficult to access locations.

#56833	mm	Inch	Cut Capacity	Pkg.	lbs.
	138	5.5	1.3mm/16AWG	1	.22

[SHOP](#)

Narrow Front Cutter/Long Nose Pliers



Full Flush


56830 Electronic Narrow 30° Front Cutter / Long Nose Pliers

Extremely narrow, short head for working in particularly restricted spaces. Cutting edge - full flush. Edge at 30° to face end of pliers for cutting obliquely from above or from the side. C70 special tool steel. For absolutely flush cutting of copper wires in difficult to access locations.

#56830	mm	Inch	Cut Capacity	Pkg.	lbs.
	118	4.5	0.6mm/22AWG	1	.19

[SHOP](#)

Electronic Pointed Pliers




56801 Electronic Short Nose Precision Pliers

Narrow, short head. Smooth jaws. Width at tip is only 1.2mm. C70 special tool steel. For holding small components as well as for holding and angling wires.

#56801	mm	Inch	Pkg.	lbs.
	138	5.5	1	.23

[SHOP](#)

Electronic Stripping Pliers



56871 Electronic Stripping Pliers

Wide long head with ridged gripping surface, shears blade and firm wire stripping stations. With opening spring and locking mechanism. Wire stripping stations 0.81 / 1.0 / 1.3 / 1.6 / 2.0 / 2.59mm, AWG 20 / 18 / 16 / 14 / 12 / 10.

#56871	mm	Inch	Ø	AWG	Pkg.	lbs.
	180	7.0	0.81-2.59	20-10	1	.15

[SHOP](#)

Flush Cutting Diagonal Cutters



- Flush cutting, with return spring

[SHOP](#)

326 Flush Cutting Diagonal Cutters With Return Spring For

Cutting Plastic DIN ISO 5749 Low wear lap joint, riveted and able to withstand high levels of load. Lightweight action, clean cutting. Long life edge is achieved through additional induction hardening to approx. 60 HRC. Special C70 tool steel hardened and tempered. For cutting plastic tie wraps & injection mold components. Soft vinyl grips.

Item				
No.	mm	Inch	Pkg.	lbs.
32607	127	5.0	1	.14
32614	160	6.3	1	.36



Professional Quality ESD Tweezers

ESD SAFE • STATIC DISSIPATIVE • HYPO ALLERGENIC COATED • TEXTURED GRIPPING SURFACE



Universal Fine Point Tweezers

Item No.	Description	wt.
44501	AA SA ESD - 130mm	.09

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)



Fine Round Points For Assembly

Item No.	Description	wt.
44506	3 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)



Sturdy Long, Fine Round Points

Item No.	Description	wt.
44502	GG SA ESD - 130mm	.09

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)



Fine Round Points Shorter

Item No.	Description	wt.
44507	3c SA ESD - 110mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)



Long Narrow Body Low Force

Item No.	Description	wt.
44503	SS SA ESD - 135mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)



Very Fine Points/Tapered To Tip

Item No.	Description	wt.
44508	4 SA ESD - 110mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)



Reduced Body To Medium Point

Item No.	Description	wt.
44504	2 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)



Extra Fine Points/Tapered To Tip

Item No.	Description	wt.
44509	5 SA ESD - 110mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)



Flat Round Tip Smooth Sides

Item No.	Description	wt.
44505	2a SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)



Curved Extra Fine Rounded Tips

Item No.	Description	wt.
44510	7a SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)

Wiha Professional Quality ESD Safe Tweezers



Holds 0.8 to 2mm Diameter

Item No.	Description	wt.
44511	50 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
 Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)


Narrow Rounded Tip Serrated, Guide Pin

Item No.	Description	wt.
44518	22 SA ESD - 150mm	.10

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
 Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)


Holds 1.5 to 3mm Diameter

Item No.	Description	wt.
44512	51 SA ESD - 130mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
 Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)


Universal Blunt Tip Serrated

Item No.	Description	wt.
44520	40 SA ESD - 145mm	.11

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
 Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)


Holds 3.5 to 7mm Diameter

Item No.	Description	wt.
44513	52 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
 Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)


MicroTip 45° Hook 1x1x2mm

Item No.	Description	wt.
44521	12 SA-SMD ESD - 120mm	.09

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
 Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)


Holds 6.5 to 10mm Diameter

Item No.	Description	wt.
44514	53 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
 Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)


MicroTip For Chips Angled 1.6 x 1 x 1mm

Item No.	Description	wt.
44522	13 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
 Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)


Angled 3.5 to 7mm Diameter

Item No.	Description	wt.
44515	54 SA ESD - 120mm	.08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
 Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)


Long Rounded to 1.0mm Wide No Serration

Item No.	Description	wt.
44523	PSF SA ESD - 125mm	.09

Static dissipative, ESD Safe hypo allergenic tweezers made from Vomalloy.
 Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)

Wiha Professional Quality ESD Safe Tweezers



Flat Bent 35°, 3mm Diameter Grip

Item No.	Description	wt.
----------	-------------	-----

44524 58 SA-SMD ESD - 117mm .08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommelloy.
Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)



MicroTip Bent 30° 1.6mm

Item No.	Description	wt.
----------	-------------	-----

44529 8b SA ESD - 120mm .08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommelloy.
Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)



Curved Extra Fine, 3mm Long Straight Tip

Item No.	Description	wt.
----------	-------------	-----

44525 7abb SA ESD - 120mm .08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommelloy.
Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)



Flat Bent 35° - 2mm Diameter Grip Radius

Item No.	Description	wt.
----------	-------------	-----

44530 59 SA-SMD ESD - 117mm .08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommelloy.
Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)



Narrow Body Low Force Bent 35° - 3mm Tip

Item No.	Description	wt.
----------	-------------	-----

44526 SSbb SA ESD - 140mm .08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommelloy.
Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)



ESD Safe General Purpose Fine Point

Item No.	Description	wt.
----------	-------------	-----

44531 1 SA ESD - 120mm .08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommelloy.
Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)



Angled Extra Fine Points Bent 30° - 3mm Long Tips

Item No.	Description	wt.
----------	-------------	-----

44527 5abb SA ESD - 117mm .08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommelloy.
Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)



Heavy Duty Strong Tweezers Tapered To Strong Point

Item No.	Description	wt.
----------	-------------	-----

44532 00 SA ESD - 120mm .09

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommelloy.
Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)



Extra Fine Points Bent 30° - 3mm Long Tips

Item No.	Description	wt.
----------	-------------	-----

44528 5bb SA ESD - 107mm .08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommelloy.
Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)



Angled & Slightly Bent With Extra Fine Tips

Item No.	Description	wt.
----------	-------------	-----

44533 7 SA ESD - 120mm .08

Static dissipative, ESD Safe hypo allergenic tweezers made from Vommelloy.
Special stainless steel, anti-magnetic and acid resistant.

[SHOP](#)


Inspection Mirrors All Stainless Detachable & Boilable

Mirrors-Clean Room Quality

For Visual Checks and Fault
Finding at Inaccessible
Locations


Natural Finish,
Stainless Steel

Magnifying,
Boilable




Inspection Mirror - Stainless 10mm

Item No.	Description	wt.
40410	#0 IM - 185mm	.09




Inspection Mirror - Stainless 22mm Short Stem

Item No.	Description	wt.
40422	#4 IM - 175mm	.10



Inspection Mirror - Stainless 30mm

Item No.	Description	wt.
40430	#8 IM - 215mm	.10



Inspection Mirror - Stainless 14mm

Item No.	Description	wt.
40414	#0 IM - 200mm	.09



Inspection Mirror - Stainless 24mm Short Stem


Item No.	Description	wt.
40424	#5 IM - 175mm	.10



Disposable Inspection Mirrors

Item No.	Description	wt.
40425	5 Pack - Plastic	.10

Set includes: White disposable inspection mirror
#5 Inspection Mirrors - 24mm x 146mm



Inspection Mirror - Stainless 20mm

Item No.	Description	wt.
40420	#3 IM - 205mm	.09



Inspection Mirror - Stainless 26mm

Item No.	Description	wt.
40426	#6 IM - 215mm	.10

PortaCrimp Dies, Frame & Sets

PortaCrimp Tools



One piece dies - held together to prevent mix up and loss

Parallel action mimics applicator type performance



Tested to 50,000 Crimps

Reliable, ratchet controlled, ensures consistent and accurate crimp



- **Top Quality:** 50,000 cycle tested frame for longest life & consistent performance
- **Reliable:** Parallel, full cycle, ratchet controlled action ensures consistent accurate crimps
- **Easy To Use:** Designed to give user full visibility of the crimping process
- **Versatile:** Quickly and easily inter-change crimp dies on the job
- **No More Lost Die Parts!** Practical design uses guide pin to keeps die components together
- **Practical:** Pocket size dies are compact & easy to carry
- **Ergonomic:** Reduced effort ratchet assisted crimping use one hand or two with extended grip
- **Economical:** One tool frame to do the job of many, select only the dies you need

PortaCrimp Tool Sets



[SHOP](#)

43190 4 Piece PortaCrimp Die Set Electrical

Reliable, ratchet controlled, ensures consistent and accurate crimp.

Item				
No.	Set includes: Tool frame &	lbs.	Pkg.	
43190	43129, 43128, 43142	5.0	1	



[SHOP](#)

43191 4 Piece PortaCrimp Die Set Industrial

Reliable, ratchet controlled, ensures consistent and accurate crimp.

Item				
No.	Set includes: Tool Frame &	lbs.	Pkg.	
43191	43129, 43127, 43147	5.0	1	



[SHOP](#)

43192 4 Piece PortaCrimp Die Set Data Com Telco

Reliable, ratchet controlled, ensures consistent and accurate crimp.

Item				
No.	Set includes: Tool Frame &	lbs.	Pkg.	
43192	43144, 43136, 43132	5.0	1	

PortaCrimp Tool Frame



[SHOP](#)

43149 PortaCrimp Tool Frame Parallel action frame gives better performance. Symmetrical pressure with equal force mimics applicator performance. One piece die held together to prevent mix up and loss.

Item No.	mm	Inch	lbs.	Pkg.
43149	234	9.75	1.1	1



Each die includes storage clip

PortaCrimp Dies

One piece die, held together to prevent mix up & loss. Easily interchangeable crimp dies are kept together with a special pin to simplify handling. Reliable crimping performance is consistent and accurate with a parallel action stroke, good to 50,000 cycles.


SHOP


43128 PortaCrimp Die Set For Green & Yellow Insulated Terminals & Splices

Item				
No.	Crimps	AWG	lbs.	Pkg.
43128	4-6 & 0.1-0.4mm ²	26-22 & 12-10	1.2	1

SHOP


43129 PortaCrimp Die Set For Red & Blue Insulated Terminals & Splices

Die set for 22-16 AWG (0.5 - 1.5mm).

Item				
No.	Crimps	AWG	lbs.	Pkg.
43129	1.5-2.5 & 0.5-1.5mm ²	22-16	1.2	1

SHOP


43142 PortaCrimp Die Set For Non-Insulated Terminals, Lugs & Splices

Item				
No.	Crimps	AWG	lbs.	Pkg.
43142	4-6 & 0.5-2.5mm ²	12-10 & 22-14	1.2	1

SHOP


43137 PortaCrimp Die Set For Non-Insulated Terminals, Lugs & Splices

Item				
No.	Crimps	Awg	lbs.	Pkg.
43137	2.5/1.5/0.75mm ²	14/16/20	1.2	1

SHOP


43139 PortaCrimp Die Set For Non-Insulated Terminals, Lugs & Splices

Item				
No.	Crimps	AWG	lbs.	Pkg.
43139	10/6/4mm ²	8/10/12	1.2	1

SHOP


43127 PortaCrimp Wire Ferrules - Insulated & Non-Insulated

Die set for 24-8 AWG (0.25-10mm).


Item				
No.	Crimps	AWG	lbs.	Pkg.
43127	10/6/4/2.5/1-1.5/.25-.75mm ²	8-24	1.2	1

SHOP


43153 PortaCrimp Wire Ferrules - Insulated & Non-Insulated

Die set for 6-4 AWG (16-25mm).

Item				
No.	Crimps	AWG	lbs.	Pkg.
43153	25 & 16mm ²	6 & 4	1.2	1

SHOP


43154 PortaCrimp Wire Ferrules - Insulated & Non-Insulated

Die set for 2-1/0 AWG (35-50mm).

Item				
No.	Crimps	AWG	lbs.	Pkg.
43154	50 & 35mm ²	1/0 & 2	1.2	1

SHOP


43146 PortaCrimp Open Barrel, Non-Insulated Standard Commercial Terminals & Lugs - .250" (6.3mm) Push On Terminals

Item				
No.	Crimp	AWG	lbs.	Pkg.
43146	4-6/1.5-2.5/0.5-1.0mm ²	22-10	1.2	1

PortaCrimp Dies



One piece die, held together to prevent mix up & loss. Easily interchangeable crimp dies are kept together with a special pin to simplify handling. Reliable crimping performance is consistent & accurate with a parallel action stroke, good to 50,000 cycles.



43150 PortaCrimp Open Barrel Non-Insulated Push On Terminals DIN 46247-1 .110" (2.8mm) Tab

Item				
No.	Crimps	AWG	lbs.	Pkg.
43150	0.5-1.0/0.25-0.5/0.1-0.25mm ²	26-18	1.2	1



43151 PortaCrimp Open Barrel Non-Insulated Push On Terminals DIN 46247-2 .187" (4.8mm) Tab

Item				
No.	Crimps	AWG	lbs.	Pkg.
43151	1.5-2.5 & 0.5-1.5mm ²	22-14	1.2	1




43143 PortaCrimp Weather Pack Open Barrel Terminals

Item				
No.	Crimps	AWG	lbs.	Pkg.
43143	3.0-0.5mm ²	12-20	1.2	1



43141 PortaCrimp Fiber Optic Die set for SMA, SMB, SFR, ST, SC fiber optic connectors (.178"/.213"/.151"/.128" hex)

Item				
No.	Crimps		lbs.	Pkg.
43141	4.52/5.41/3.84/3.25mm (.178"/.213"/.151"/.128")		1.2	1



43136 PortaCrimp Coaxial Network & Communications

Die set for RG58, RG59, RG62AU BNC/TNC Coaxial Connectors (.213"/.255"/.068" hex).

Item	Crimps			
No.	1.69/5.41/6.48mm	lbs.	Pkg.	
43136	(.213"/.255"/.068"hex)	1.2	1	



43138 PortaCrimp Coaxial Network & Communications, CATV, HDTV, Video Die set for RG6, Belden 1694A, Twinax BNC, CATV F Coaxial Connectors (.360"/.324" Hex).

Item	Crimps			
No.	9.14 & 8.23mm (.360"/.324")	lbs.	Pkg.	
43138		1.2	1	



43140 PortaCrimp Coaxial Network & Communications

Die set for RG174, RG179 BNC/TNC Coaxial Connectors (.178"/.128"/.068" Hex, .028" (0.7mm) Sq).


Item	Crimps			
No.	4.52/3.25/1.69mm hex 0.7mm sq.	lbs.	Pkg.	
43140	(.178"/.128"/.068" hex, .028" sq.)	1.2	1	



43144 PortaCrimp Datacom/Telecom Modular Plug

Die set for 8-position 8-contact (RJ45).

Item No.	RJ45			
43144		1.2	1	



43132 PortaCrimp Datacom/Telecom Modular Plug

Die set for 6-position 6-contact (RJ11).

Item No.	RJ11			
43132		1.2	1	

PortaCrimp Dies



One piece die, held together to prevent mix up & loss. Easily interchangeable crimp dies are kept together with a special pin to simplify handling. Reliable crimping performance is consistent & accurate with a parallel action stroke, good to 50,000 cycles.


[SHOP](#)

43147 PortaCrimp Power Contacts

Item No.	Crimps	AWG	↔ lbs.	▬ Pkg.
43147	4 / .14-1 / 2.5 / 1.5mm	26-12	1.2	1


[SHOP](#)

43148 PortaCrimp Power Contacts

Item No.	Crimps	AWG	↔ lbs.	▬ Pkg.
43148	6 & 10mm	10-8	1.2	1


[SHOP](#)

43158 PortaCrimp Die set for heat shrink connectors: 0.5-1.5mm² red & 1.5-2.5mm² blue.

Item	Crimps	↔ lbs.	▬ Pkg.
No.	0.5-1.5mm² (22-16AWG) red	lbs.	Pkg.
43158	1.5-2.5mm² (16-14 AWG) blue	1.2	1


[SHOP](#)

43162 PortaCrimp Die set for heat shrink connectors: 4-6mm² yellow & 0.32-0.75mm² green.

Item	Crimps	↔ lbs.	▬ Pkg.
No.	4-6mm² (12-10AWG) yellow	lbs.	Pkg.
43162	0.32-0.75mm² (22-18AWG) green	1.2	1

Ratchet End Sleeve Crimper



5 die nests side entry crimp

[SHOP](#)

43612 Ratchet End Sleeve Crimper

Crimps Insulated & non-insulated end sleeves. 6 crimp positions range AWG 26-18, 18-16, 14, 12, 10, 8. Soft grip non-slip handles. Factory set auto release at end of crimp cycle.

Item	Inch	AWG	↔ lbs.	▬ Pkg.
No.	Length	Range	lbs.	Pkg.
43612	220mm/8.6"	26-8	1.18	1

Ratchet Crimper For Standard Connectors



Crimp Profile

[SHOP](#)

43618 Ratchet Crimper For Standard Connectors

Crimps Insulated & non-insulated connectors. 3 crimp positions range AWG 20-18 red, 16-14 blue, 12-10 yellow. Soft grip non-slip handles. Factory set auto release at end of crimp cycle.

Item	Inch	AWG	↔ lbs.	▬ Pkg.
No.	Length	Range	lbs.	Pkg.
43618	220mm/8.6"	20-10	1.06	1

Ratchet Crimper Push On Terminals


 Crimp Profile
"F"/"B"

[SHOP](#)

43624 Ratchet Crimper Push On Terminals

Crimps Insulated & non-insulated terminals. 4 crimp positions range AWG 24-20, 20-18, 16-14, 12-10. Soft grip non-slip handles. Factory set auto release at end of crimp cycle.

Item	Inch	AWG	↔ lbs.	▬ Pkg.
No.	Length	Range	lbs.	Pkg.
43624	220mm/8.6"	24-10	1.06	1

Ratchet Crimper For Eye Terminals


 Self adjusting
side entry crimp

[SHOP](#)

43643 Ratchet Crimper For Eye Terminals

Crimps Insulated & non-insulated terminals. 4 crimp positions range AWG 26-22, 20-18, 12-10, 8-6. Soft grip non-slip handles. Factory set auto release at end of crimp cycle.

Item	Inch	AWG	↔ lbs.	▬ Pkg.
No.	Length	Range	lbs.	Pkg.
43643	220mm/8.6"	26-6	1.02	1

Automatic Stripping Tool



Interchangeable stripping blade cassettes



Cuts & strips up to 10mm²/8 AWG - Strips PVC, THHW, TEFLON insulations



Ergonomic design with non-slip two component handles



Easy/snag free wire removal from tool - jaws stay open after strip

Self Adjusting Cut & Strip Tool



Straight Blade Cassette Stripping Range
0.02 - 10.0mm²



Cables: Conduit wire, Flex mains cable, Equipment wire, Flat modplug cable etc.

34-8 AWG

44212 Self Adjusting Cutting & Stripping Tool

Easily interchangeable stripping cassettes enables a wide range of insulations from PVC to PTFE. Light weight soft grip handle qualified for high volume production and portable/field usage.

Item No.	mm	Inch	AWG	Strip Dim.	lbs.	Pkg.
44212	191	7.5	34 - 8	0.02-10mm²	.30	1

[SHOP](#)

Replaceable Cassette - Straight Blade



Straight Blade Cassette Stripping Range
0.02 - 10.0mm²



Straight

34-8 AWG

44214 Straight Blade Cassette, PVC Insulations

Fine adjustability ensures that thin insulations can be stripped without damage to conductors. At the end of the stripping function, the stripping blades open and remain open during the return phase of the strip cycle facilitating easy/snag free wire removal from the tool.

Item No.	AWG	Strip Range	lbs.	Pkg.
44214	34 - 8	0.02-10mm²	.02	1

[SHOP](#)

Replaceable Cassette - 4-16mm²



Stripping Range
4-16mm²



Radius Blade

10-5 AWG

44269 Replaceable Cassette, 4-16mm Stripping Range

Fine adjustability ensures that thin insulations can be stripped without damage to conductors. At the end of the stripping function, the stripping blades open and remain open during the return phase of the strip cycle facilitating easy/snag free wire removal from the tool.


Item No.	AWG	Strip Range	lbs.	Pkg.
44269	10 - 5	4-16mm²	.02	1

[SHOP](#)

Replaceable Cassette - "V" Blade



"V" Blade Stripping Range
0.1 - 4mm²



VBC for PTFE

28-12 AWG

44213 Replaceable VBC or PTFE Cassette, "V" Blade

Fine adjustability ensures that thin insulations can be stripped without damage to conductors. At the end of the stripping function, the stripping blades open and remain open during the return phase of the strip cycle facilitating easy/snag free wire removal from the tool.

Item No.	AWG	Strip Range	lbs.	Pkg.
44213	28 - 12	0.1-4mm²	.02	1

[SHOP](#)

Heavy Duty Adjustable Cable Stripper



Circular + Straight Window Strip
Circular + Spiral Strip



Cables: Power cable. Multi-conductor control, fiber optic and copper trunk cables

44217 Jacket Stripper - Heavy Duty Adjustable

Professional stripping tool for cables of all insulations types. Positive locking positions for circular, lengthways and spiral strips. Interchangeable cable retention hooks give cable stripping capacity of up to 40mm/1.57 inch diameter. Replacement cutting blades can be stored within the tool.

Item No.	mm	Inch	Strip Range	Strip Dim.	lbs.	Pkg.
44217	168	6.6	4.5-40mm ²	0-4.5mm	.26	1

SHOP

Replacement Blade



Replacement cutting blades can be stored within the tool

44218 Replacement Blade For 44217 Stripper

Interchangeable cable retention hooks give cable stripping capacity of up to 40mm/1.57 inch diameter. Replacement cutting blades can be stored within the tool.

Item No.	Replacement Blade For	lbs.	Pkg.
44218	44217 Stripper	.01	1

SHOP

Precision Adjustable Stripping Tool



Replaceable Blade



Cables: Multi core cable, Modplug cable. Fiber optic cable etc.



44220 Precision Adjustable Stripping Tool

Professional stripping tool removes the outer cable jacket from signal, telephone, audiovisual, instrumentation and data transmission copper and fiber optic cables up to 11mm/0.43" diameter. The tool features a 9 position indexed blade height adjustment wheel ensuring accurate & repeatable stripping results. Simply squeeze together to open the stripping cavity - insert cable, rotate once and pull off the scrap insulation. Smooth, Lightweight and pocket size. No open blade, replacement blades encased within cassette.

Item No.	mm	Inch	Strip Range	Strip Range	lbs.	Pkg.
44220	90.5	3.6	2.5-11mm	.10"/0.43"	.06	1

SHOP

Replacement Blade



Replacement Blade



44221 Replacement Blade For 44220 Stripper

Stripping capacity of up to 2.5-11mm/0.43" diameter.

Item No.	Strip Range	Strip Dim.	lbs.	Pkg.
44221	2.5-11mm	11mm/0.43"	.01	1

SHOP

CATV/Satellite Stripper



Strips: RG59 & RG6 CATV coaxial cables



44206 CATV/Satellite Stripper

Quickly & simply strips RG59 & RG6 coaxial cables for CATV "F" type connectors giving industry standard strip lengths of 6.35mm/.25" for both the braid and the conductor. Patented spring-like action and built-in stop eliminates the need for manual adjustment for different cables.

Item No.	mm	Inch	Strip Length	lbs.	Pkg.
44206	83	3.3"	6.35mm/.25" Braid/Conductor	.05	1

SHOP



Adjustable Screw
For Precise Blade
Positioning



4 Cable V-blocks




Reversible
Cassettes
Long Life



Stepped Stripping
Depth For
Reduced Friction

2 Step



	44237	44238	44239	44240
	Blue	Red	Yellow	Orange
"B" mm	6.8	6.0	12.0	9.2
"B" Inch	0.27"	0.24"	0.47"	0.36"
"A"	User adjusted			

Blue Cassette Stripping Tool Kit



2 Step

Cables: RG
58/59/62/174/180/188/
195/316/6/ Belden 8281

2 Step Red Cassette Stripping Tool Kit



2 Step

Cables: RG
58/59/62/174/180/188/
195/316/6/ Belden 8281

2 Step Yellow Cassette Stripping Tool Kit




2 Step

Cables: RG
58/59/62/174/180/188/
195/316/6/ Belden 8281

2 Step Replacement Stripping Cassettes



Cables: RG
58/59/62/174/180/
188/195/316/6/
Belden 8281



SHOP

Stripping Tool - No Cassette



44200 Cassette Hand-Stripping Tool Accurate & versatile coaxial hand-stripping tool. Holds all 2 or 3 step cassettes.

Item No.	lbs.	Pkg.
44200	.07	1

SHOP

44227 Blue Cassette Hand-Stripping Tool Kit

Accurate & versatile coaxial hand-stripping tool, designed to provide 2 strip steps on chosen cable. Enclosed V-blocks make stripper useful for cables in range of 2.5-7.6mm. Universal tool body accepts all cassettes. High quality steel blade cassettes with razor sharp edges for long, effective use.

Item No.	mm	Inch	Strip Range	Strip Dim.	lbs.	Pkg.
44227	90	3.54	1.87-7.6mm	6.8mm	.09	1
			0.10"-0.30"	0.27"		

SHOP

44222 2 Step Red Cassette Hand-Stripping Tool Kit

Accurate & versatile coaxial hand-stripping tool, designed to provide 2 strip steps on chosen cable. Enclosed V-blocks make stripper useful for cables in range of 6.0mm/.24". Universal tool body accepts all cassettes. High quality steel blade cassettes with razor sharp edges for long, effective use.

Item No.	mm	Inch	Strip Range	Strip Dim.	lbs.	Pkg.
44222	90	3.54	1.87-7.6mm	6.0mm	.09	1
			0.10"-0.30"	0.24"		

SHOP

44224 2 Step Yellow Cassette Hand-Stripping Tool Kit

Accurate & versatile coaxial hand-stripping tool, designed to provide 2 strip steps on chosen cable. Enclosed V-blocks make stripper useful for cables in range of 12.0mm/.47". Universal tool body accepts all cassettes. High quality steel blade cassettes with razor sharp edges for long, effective use.

Item No.	mm	Inch	Strip Range	Strip Dim.	lbs.	Pkg.
44224	90	3.54	1.87-7.6mm	12.0mm	.09	1
			0.10"-0.30"	0.47"		

SHOP

442 2 Step Replacement Stripping Cassettes High quality steel blade cassettes with razor sharp edges for long, effective use.

Item No.	Color	Strip Range	Strip Dim.	lbs.	Pkg.
44237	Blue	1.87-7.6mm	6.8(0.27")	.01	1
44238	Red	1.87-7.6mm	6.0(0.24")	.01	1
44239	Yellow	1.87-7.6mm	12.0(0.47")	.01	1
44240	Orange	1.87-7.6mm	9.2(0.36")	.01	1

Stripping Tool Set



44290 10 Piece Set, Cassette Hand-Stripping Tool

Accurate & versatile coaxial hand-stripping tool, designed to provide 2 strip steps on chosen cable. Universal tool body accepts all cassettes.

Item No.	Set includes: Stripping Tool, L-key,	lbs.	Pkg.
44290	4 Cable V-blocks & 4 Stripping Cassettes	.10	1

SHOP



Adjustable Screw
For Precise Blade
Positioning



4 Cable V-blocks




Reversible
Cassettes
Long Life



Stepped Stripping
Depth For Reduce
Friction

3 Step



	44251	44255	44259	44260	44261
	Brown	Green	White	Dk. Brown	Black
"C" mm	8.3	6.0	6.8	7.5	5.5
"B" mm	2.7	6.0	2.5	3.5	5.5
"A"	User adjusted				

3 Step Brown Cassette Kit



Cables: RG
58/59/62/174/180/188/
195/316/6/ Belden 8282



44241 3 Step Brown Cassette Kit

Accurate & versatile coaxial hand-stripping tool, designed to provide 3 strip steps on chosen cable. Enclosed V-blocks make stripper useful for cables in range of 2.5-7.6mm. Universal tool body accepts all cassettes. High quality steel blade cassettes with razor sharp edges for long, effective use.

Item No.	mm	Inch	Strip Range	Strip Dim.	lbs.	Pkg.
44241	90	3.54	1.87-7.6mm 0.10"-0.30"	8.3mm(B) 2.7mm(C)	.08	1

[SHOP](#)

3 Step Green Cassette Kit



Cables: RG
58/59/62/174/180/188/
195/316/6/ Belden 8283



44245 3 Step Green Cassette Kit

Accurate & versatile coaxial hand-stripping tool, designed to provide 3 strip steps on chosen cable. Enclosed V-blocks make stripper useful for cables in range of 2.5-7.6mm. Universal tool body accepts all cassettes. High quality steel blade cassettes with razor sharp edges for long, effective use.

Item No.	mm	Inch	Strip Range	Strip Dim.	lbs.	Pkg.
44245	90	3.54	1.87-7.6mm 0.10"-0.30"	6.0mm(B) 6.0mm(C)	.08	1

[SHOP](#)

3 Step White Cassette Kit



Cables: RG
58/59/62/174/180/188/
195/316/6/ Belden 8284



44249 3 Step White Cassette Kit

Accurate & versatile coaxial hand-stripping tool, designed to provide 3 strip steps on chosen cable. Enclosed V-blocks make stripper useful for cables in range of 2.5-7.6mm. Universal tool body accepts all cassettes. High quality steel blade cassettes with razor sharp edges for long, effective use.


Item No.	mm	Inch	Strip Range	Strip Dim.	lbs.	Pkg.
44249	90	3.54	1.87-7.6mm 0.10"-0.30"	6.8mm(B) 2.5mm(C)	.08	1

[SHOP](#)

3 Step Replacement Stripping Cassettes



Cables: RG
58/59/62/174/180/188/
195/316/6




[SHOP](#)

442 3 Step Replacement Stripping Cassettes

Accurate & versatile coaxial hand-stripping tool, designed to provide 3 strip steps on chosen cable. High quality steel blade cassettes with razor sharp edges for long, effective use.

Item No.	Color	Strip B	Strip C	lbs.	Pkg.
44251	Brown	2.7mm/.11"	8.3mm/.33"	.01	1
44255	Green	6.0mm/.24"	6.0mm/.24"	.01	1
44259	White	2.5mm/.10"	6.8mm/.27"	.01	1
44260	Dk.Brown	3.5mm/.14"	7.5mm/.30"	.01	1
44261	Black	5.5mm/.22"	5.5mm/.22"	.01	1

Stripping Tool Set



44292 11 Piece Set, Cassette Hand-Stripping Tool

Accurate & versatile coaxial hand-stripping tool, designed to provide 3 strip steps on chosen cable. Universal tool body accepts all cassettes.

Item No.	Set includes: Stripping Tool, L-key,	lbs.	Pkg.
44292	4 Cable V-blocks, 5 Stripping Cassettes	.11	1

[SHOP](#)

Item No. Page	Item No. Page	Item No. Page	Item No. Page	Item No. Page	Item No. Page
26000 4	26135 10	26449 12	26702 9	26920 16	26982 17
26001 4	26136 10	26455 12	26703 9	26921 16	26985 17
26008 4	26140 10	26457 12	26704 9	26922 15	26987 19
26010 4	26142 10	26459 12	26705 9	26923 16	26989 19
26012 4	26145 10	26461 12	26706 9	26924 16	26990 18
26015 4	26190 5	26463 12	26707 9	26925 16	26991 18
26018 4	26192 5	26465 12	26708 9	26926 16	26992 18
26020 4	26193 10	26467 12	26709 9	26927 16	26993 18
26022 4	26194 5	26490 7	26710 9	26928 16	26995 19
26023 4	26199 5	26491 7	26715 9	26929 16	26996 19
26025 4	26205 6	26493 12	26720 9	26932 16	26997 19
26027 4	26210 6	26499 7	26721 11	26933 16	26999 19
26028 4	26307 6	26510 8	26723 11	26934 16	28000 15
26030 4	26309 6	26515 8	26725 11	26935 16	28001 15
26032 4	26313 6	26520 8	26727 11	26936 16	28002 17
26033 4	26315 6	26523 8	26729 11	26937 16	28003 17
26034 4	26316 6	26525 8	26731 11	26938 16	28004 17
26035 4	26320 6	26527 8	26732 11	26939 16	28005 17
26040 4	26323 6	26530 8	26733 11	26940 16	28006 17
26041 4	26325 6	26531 8	26735 11	26941 16	28007 17
26042 4	26327 6	26532 8	26736 11	26942 16	28008 17
26050 10	26330 6	26535 8	26737 11	26943 16	28009 17
26051 10	26331 6	26536 8	26739 11	26944 16	28010 17
26052 10	26333 6	26539 8	26741 11	26945 16	28011 17
26053 10	26336 6	26540 8	26743 11	26946 16	28012 17
26054 10	26340 6	26545 8	26745 11	26947 16	28013 17
26055 10	26341 12	26547 8	26747 11	26948 16	28014 17
26056 10	26343 12	26550 8	26749 11	26949 16	28015 17
26060 10	26345 12	26555 8	26751 11	26950 16	28016 17
26061 10	26347 12	26556 8	26761 9	26951 15	28017 17
26063 10	26349 12	26560 8	26762 9	26952 15	28021 16
26065 10	26351 12	26563 8	26763 9	26953 15	28023 16
26066 10	26353 12	26570 8	26764 9	26954 15	28024 16
26068 10	26363 12	26571 13	26765 9	26955 15	28025 16
26070 10	26367 12	26572 13	26766 9	26956 15	28026 16
26072 10	26369 12	26573 13	26790 9	26957 15	28027 16
26073 10	26371 12	26574 13	26791 9	26958 17	28028 16
26074 10	26390 6	26575 13	26792 9	26959 17	28029 16
26076 10	26391 6	26576 13	26793 11	26960 17	28033 16
26079 10	26392 12	26577 13	26794 9	26961 17	28034 16
26080 10	26393 12	26578 13	26796 11	26962 16	28035 16
26090 4	26399 6	26579 13	26798 11	26963 16	28036 16
26092 5	26413 7	26581 13	26799 9	26964 16	28037 16
26093 10	26415 7	26582 13	26810 4	26965 16	28080 18
26099 4	26416 7	26583 13	26815 11	26966 16	28084 19
26100 5	26419 7	26584 13	26900 15	26967 16	28087 19
26101 5	26420 7	26585 13	26901 15	26968 16	28091 19
26102 5	26423 7	26586 13	26903 15	26969 16	28094 18
26105 5	26425 7	26587 13	26904 15	26971 15	28097 19
26107 5	26427 7	26588 13	26905 15	26972 15	28552 7
26108 5	26430 7	26589 13	26911 15	26973 15	28620 7
26109 5	26431 7	26590 8	26912 15	26974 15	28622 7
26110 5	26436 7	26591 8	26913 16	26975 17	28624 7
26113 5	26439 7	26592 8	26914 16	26976 17	28626 7
26114 5	26440 7	26593 13	26915 16	26977 17	28627 7
26115 5	26441 12	26596 13	26916 16	26978 17	28629 7
26130 10	26443 12	26598 8	26917 16	26979 17	28632 7
26132 10	26445 12	26599 8	26918 16	26980 17	28633 7
26133 10	26447 12	26701 9	26919 16	26981 17	28637 7

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Notes:
28638	7	44241	37	75018	20	75747	21	
28644	7	44245	37	75020	20	75748	21	
32607	25	44249	37	75025	20	75792	22	
32614	25	44251	37	75030	20	75800	20	
40010	13	44255	37	75035	20	75801	20	
40410	29	44259	37	75040	20	75802	21	
40414	29	44260	37	75093	23	75803	21	
40420	29	44261	37	75094	23	75810	21	
40422	29	44269	34	75095	23	75811	21	
40424	29	44290	36	75096	23	75812	21	
40425	29	44292	37	75105	20	75813	21	
40426	29	44501	26	75110	20	75814	21	
40430	29	44502	26	75115	20	75815	21	
43127	31	44503	26	75120	20	75816	21	
43128	31	44504	26	75307	20	75817	21	
43129	31	44505	26	75309	20	75820	21	
43132	32	44506	26	75313	20	75821	21	
43136	32	44507	26	75315	20	75822	21	
43137	31	44508	26	75320	20	75823	21	
43138	32	44509	26	75322	20	75824	21	
43139	31	44510	26	75325	20	75825	21	
43140	32	44511	27	75327	20	75826	21	
43141	32	44512	27	75330	20	75827	21	
43142	31	44513	27	75332	20	75900	20	
43143	32	44514	27	75340	20	75901	20	
43144	32	44515	27	75342	20	75902	20	
43146	31	44518	27	75350	20	75965	23	
43147	33	44520	27	75352	20	75981	21	
43148	33	44521	27	75354	20	75983	21	
43149	30	44522	27	75356	20	75985	21	
43150	32	44523	27	75358	20	75989	21	
43151	32	44524	28	75360	20	75990	23	
43153	31	44525	28	75362	20	75991	22	
43154	31	44526	28	75364	20	75992	22	
43158	33	44527	28	75366	20	75994	22	
43162	33	44528	28	75368	20	75996	22	
43190	30	44529	28	75370	20	75999	22	
43191	30	44530	28	75372	20	91118	11,13	
43192	30	44531	28	75395	22	92190	9	
43612	33	44532	28	75703	20	92191	8	
43618	33	44533	28	75704	20	95190	14	
43624	33	44590	18	75705	20	96800	14	
43643	33	56801	25	75706	20			
44200	36	56812	24	75707	20			
44206	35	56813	25	75708	20			
44212	34	56815	24	75709	20			
44213	34	56818	24	75710	20			
44214	34	56825	24	75715	20			
44217	35	56830	25	75720	20			
44218	35	56833	25	75727	20			
44220	35	56871	25	75728	20			
44221	35	62990	14	75729	20			
44222	36	62993	14	75735	20			
44224	36	62994	14	75739	20			
44227	36	62995	14	75742	20			
44237	36	65090	14	75743	21			
44238	36	75008	20	75744	21			
44239	36	75012	20	75745	21			
44240	36	75015	20	75746	21			

(800) 494-6104
 fax: (800) 494-7456
 email: cservice@wiha.com
 www.wihatools.com

**SEE OUR GREAT
 WEB SPECIALS!**



Wiha Quality Tools

1348 Dundas Circle
 Monticello, MN 55362
 tel: 763.295.6591
 fax: 763.295.6598

Wiha Tools Canada Ltd.

www.wihatools.ca
 Brampton, ONT L6T 4X4
 tel: 866.494.0096 or 763.295.6591
 fax: 763.295.6598

To:

Catalog Item No. 99006.wo
 version - 5/15/14

Subject to change without notice

©2014 Willi Hahn Corporation

®Torx is a registered trademark of
 Acument Intellectual Properties LLC.




91330.wo - Tooling Catalog



99004.wo - Shop Tools Catalog



99914.wo - TORX Catalog



99002.wo - Screwdrivers Catalog



99919.wo - Insulated Catalog



99001.wo - TorqueControl Catalog



99934.wo - Hex Tools Catalog



99951.wo - Bits Catalog



99945.wo - ESD Catalog



99977.wo - Pliers/Crimpers Catalog