



Home> Products > Stainless Steel Media Isolated> BL > Product Page

BLH100PSBG



Actual product appearance may vary.

BL Series Flush Mount Stainless Steel Pressure Sensor, 4 mA to 20 mA Output, Sealed Gage, 0 psi to 100 psi, Item Number 9243201

Features

- Accuracies to 0.25%
- Flush diaphragm
- Wide choice of pressures ranges available
- Absolute models available
- For critical applications
- Easily cleaned/adaptable
- Wide range of application
- Can measure vacuum

Potential Applications

- Depth sensing
- Water resource management
- Process control
- Marine instrumentation
- Chemical manufacture
- Paint spraying
- Tank/liquid level

Description

The BL pressure transmitter has a conventional 4 mA to 20 mA output and is available with accuracies to 0.25%. It has Factory Mutual approval as an intrinsically safe device* for use in hazardous areas Class I, Division I, Groups A through G. All PSIS or PSIA BL's are hermetically sealed. The pressure sensitive diaphragm is either 316L or 15-5 stainless steel, depending on the pressure range selected. The BL's flush diaphragm is especially suited to measuring viscous fluids, slurries, and media where system flushing is necessary. It may also be mounted in an adapter for more conventional installations. The overall price/performance ratio makes this an ideal choice for many process environments.

**When used with approved barriers.*

Supporting Documentation

- [Dimensions and Circuitry](#)
- [Documentation](#)

Product Specifications	
Measurement Type	Sealed Gage
Signal Conditioning	Amplified
Pressure Range	0 psi to 100 psi
Supply Voltage	12.0 Vdc to 30.0 Vdc
Maximum Overpressure	200 psi
Burst Pressure	500 psi
Port Style	Flush Diaphragm
Temperature Compensation	Yes
Output Type	4 mA to 20 mA
Protection Circuitry	Reverse Polarity
Accuracy	0.25% full scale BFSL
Response Time	less than 0.5 ms
Insulation Resistance	1000 Mohms @ 50 Vdc max.
Output Calibration	Yes
Termination Type	Bendix Connector
Weight	70 grams [2.5 ounces]
Full Scale Span	16 mA ± 0.16 mA
Operating Temperature Range	-40 °C to 82 °C [-40 °F to 180 °F]
Compensated Temperature Range	-1 °C to 54 °C [30 °F to 130 °F]
Storage Temperature Range	NO IDEA SHARED FORMULA EXP PTG
Media Compatibility	Limited only to those media which will not attack 15 - 5PH stainless steel
Approvals	FM IS with Appropriate Barriers
UNSPSC Code	411121
UNSPSC Commodity	411121 Transducers
Availability	Global
Series Name	BL

My Links

- Login to iCOM
- Login as Rep/AD
- Login as Guest
- Login to Digital University

Keyword Search

Search for product and support information.

All Sensing and Control▼

Product Search

Part number search:

Use (*) to expand search

Specification Search