

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [31402-3100](#)
Status: **Active**
Overview: MX64 Sealed Single Row Connectors
Description: 2.54mm MX64™ Sealed Single Row Crimp Housing, GET Terminal, Black, 3 Circuits, Mating Part: Keying A, without CPA Lock

Documents:
[3D Model](#) [Product Specification PS-31402-000 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)


General
Product Family Crimp Housings
Series [31402](#)
Application Power
More Detailed Tech Information <http://ewcap.uscarteams.org>
Overview [MX64 Sealed Single Row Connectors](#)
Product Name MX64™, USCAR
UPC 822348285723

Physical
Circuits (maximum) 3
Color - Resin Black, Natural
Gender Female
Glow-Wire Compliant No
Keying to Mating Part Yes
Lock to Mating Part None
Material - Resin Modified Polystyrene Alloy, Polyester
Net Weight 4.882/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.54mm
Temperature Range - Operating -40°C to +125°C

Electrical
Current - Maximum per Contact 9A

Material Info
Old Part Number CVP31402-3100

Reference - Drawing Numbers
Product Specification PS-31402-000
Sales Drawing SD-31402-211



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[31402Series](#)

Mates With
Sensors, Other USCAR Interfaces

Use With
[34230](#) Molex GET Terminals

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[31402-3100](#)