


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT<br>PART NUMBER | PKG.     | STUD<br>SIZE | DIMENSIONS in.    |                   |                   |                   |                   |
|------------------------|----------|--------------|-------------------|-------------------|-------------------|-------------------|-------------------|
|                        |          |              | A <sup>±.03</sup> | W <sup>±.01</sup> | C <sup>±.02</sup> | M <sup>±.03</sup> | H <sup>±.01</sup> |
| P2-10R                 | -X<br>-T | #10          | 1.46<br>(.37,1)   | .68<br>(.17,3)    | .58<br>(.14,7)    | 1.12<br>(.28,5)   | .20<br>(5,1)      |
| P2-14R                 | -X<br>-T | 1/4"         | 1.46<br>(.37,1)   | .68<br>(.17,3)    | .58<br>(.14,7)    | 1.12<br>(.28,5)   | .27<br>(6,9)      |
| P2-56R                 | -X<br>-T | 5/16"        | 1.46<br>(.37,1)   | .68<br>(.17,3)    | .58<br>(.14,7)    | 1.12<br>(.28,5)   | .33<br>(8,4)      |
| P2-38R                 | -X<br>-T | 3/8"         | 1.46<br>(.37,1)   | .68<br>(.17,3)    | .58<br>(.14,7)    | 1.12<br>(.28,5)   | .39<br>(9,9)      |
| P2-12R *               | -X<br>-T | 1/2"         | 1.55<br>(.39,4)   | .86<br>(.21,8)    | .58<br>(.14,7)    | 1.12<br>(.28,5)   | .52<br>(13,2)     |

**NOTES:**

1. UL LISTED AND CERTIFIED FOR:  
A. 347° F (175° C) MAX OPERATING TEMP  
B. #2 AWG STRANDED COPPER WIRE
2. PACKAGE QTY: STD. PKG.-X=10  
BULK PKG.-T=200
3. MATERIAL: .060" (1,52) THK COPPER, TIN PLATED
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
5. INSTALLATION TOOL: CT-700 (OBSOLETE), CT-1701
6. WIRE STRIP LENGTH: 7/16 <sup>+1/32</sup><sub>-0</sub> (11,11 <sup>+8</sup><sub>-0</sub>)



LISTED  
587H  
E52164



CERTIFIED  
LR31212

- P2-12R NOT CSA CERTIFIED

A41212\_03

|     |       |     |     |                                                                                                                                  |       |      |      |                                                                                                            |              |               |                       |
|-----|-------|-----|-----|----------------------------------------------------------------------------------------------------------------------------------|-------|------|------|------------------------------------------------------------------------------------------------------------|--------------|---------------|-----------------------|
|     |       |     |     |                                                                                                                                  |       |      |      |  <b>PANDUIT CORP.</b> |              |               |                       |
| 03  | 3/01  | EJS |     | ADDED PACKAGE CODE TO CHART, ADDED CT-1701, ADDED "OBSOLETE" TO NOTE 5, FILE SPEC WAS N41212AA_PCD_02, METRIC DIM. WERE 2 PLACES |       |      |      | TINLEY PARK, ILLINOIS                                                                                      |              |               |                       |
| 02  | 11/94 | TH  | RLS | UPDATED NOTES AND DIMENSIONS                                                                                                     | 02669 | LA   | TFKE | #2 BARREL NON-INSULATED RING TONGUE                                                                        |              |               |                       |
| 1   | 7-88  | DW  |     | REDRAWN WITH REVISIONS                                                                                                           |       |      |      |                                                                                                            |              |               |                       |
| REV | DATE  | BY  | CHK | DESCRIPTION                                                                                                                      | ECN # | CUST | PM   | DRAWN BY<br>DAW                                                                                            | CHK'D<br>RLS | SCALE<br>NONE | DRAWING NO.<br>A41212 |