


Female Header Right Angled 2,54 mm

Series

095



Rated current	3,0 A
Rated voltage	250 V _{RMS} / V _{DC}
	Please consider air- and creepage distances
Withstand voltage	500 V _{RMS} for one minute
Material contact	Phosphor bronze
Material insulator	High temp. thermoplast UL94V-0
Operating temperature	-40°C to +105°C
Max. processing temper.	260°C for 10 seconds

All dimensions in mm.

pitch
2,54



termination

mating pin
size



☐ 0.64

max.
pincount
040 / 080

Variation



PCB Layout



Plating:

$$T = S_n$$
$$F = Au$$

S = Selective Au

* No. of contacts:

Variation 1 = 001 - 040

Variation 2 = 002 - 080

Variation (1,2)

No. of contacts
(001,... - 080) *

Plating contact (T,F,S)



www.mpe-connector.de

00170644 V2

Order code:

0	9	5	-	?	-	?	?	?	-	0	-	N	?	X	-	B	S	0
---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---

[illegible]