


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19
© COPYRIGHT — BY —

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
			K1	REVISED PER ECO-11-005294	08APR11
					HMR



- 1 WIRE INSULATION DIA: SEE TABLE.
2 TONGUE MATERIAL THK.: .031 ± .002

OBSOLETE OBSOLETE OBSOLETE OBSOLETE	.115-.170	100	LOOSE PC, BOX	8-328281-1
	.115-.170	100	ON TAPE, SM. BOX	1-328281-4
	.115-.170	1000	ON TAPE, LG. BOX	1-328281-3
	.105-.170	5000	ON TAPE, REEL	1-328281-2
	.115-.170	5000	ON TAPE, REEL	1-328281-1
	.105-.170	—	LOOSE PIECE	1-328281-0
	.115-.170	—	LOOSE PIECE	328281

	WIRE INS. DIA.	QUANTITY	DESCRIPTION	PART NO
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .008 ANGLES ± —				
CONTRACT NO. DR UTA/RFB 10-4-85				
CHK P. Mutyala 2-13-86				
APPD C. Maiti 12-13-86				
APPD				
MATERIAL INSULATION: NYLON - BLUE BODY & SLEEVE: COPPER (CG-C-376) FINISH BODY & SLEEVE TIN PL (MIL-T-10727) .000100 MIN. THK.				
DSGN APPD				
OTHER APPD				
		SIZE B	FSCM NO 00779	DRAWING NO 328281
		SCALE NTS	SHEET 1 OF 1	



NAME
TERMINAL
P.I.D.G., SPADE
WIRE SIZE: 16-14