

Quick Reference

Search by part #

Check distributor
part inventory

Products

Browse Products

-By Device - 6

-By Product Line- 6

-Attachment Methods 6

-Interface Materials - 6

-Accessories - 6


























Useful Links

[MSDS Safety Sheets](#)[How to Order?](#)[Find Sales Rep](#)[Find Distributor](#)[Sample Request](#)[Quote Request](#)[Catalog Request](#)[Building a Part #](#)[Part # Cross Ref](#)

Accessories

Standard Mounting Pads

The following Mounting Pads are for use with T-6

7717-167DAPG (DAP) Leads: 3 Outside Diameter mm (in): 8.71 (0.343) Thickness: 3.18 (0.125) RoHS Compliant	
7717-167NG (nylon) Leads: 3 Outside Diameter mm (in): 8.71 (0.343) Thickness: 3.18 (0.125) RoHS Compliant	
7717-161DAPG (DAP) Leads: 4-Mar Outside Diameter mm (in): 8.64 (0.340) Thickness: 1.91 (0.075) RoHS Compliant	
7717-161NG (nylon) Leads: 4-Mar Outside Diameter mm (in): 8.64 (0.340) Thickness: 1.91 (0.075) RoHS Compliant	
7717-159NG (nylon) Leads: 5 Outside Diameter mm (in): 9.53 (0.375) Thickness: 5.59 (0.220) RoHS Compliant	
7717-158TG (Teflon) Leads: 4 Outside Diameter mm (in): 9.91 (0.390) Thickness: 0.25 (0.010) RoHS Compliant	
7717-131DAPG (DAP) Leads: 4 Outside Diameter mm (in): 8.89 (0.350) Thickness: 0.97 (0.038) RoHS Compliant	
7717-131NG (nylon) Leads: 4 Outside Diameter mm (in): 8.89 (0.350) Thickness: 0.97 (0.038) RoHS Compliant	
7717-114NG (nylon) Leads: 4 Outside Diameter mm (in): 9.02 (0.355) Thickness: 1.17 (0.046) RoHS Compliant	
7717-4DAPG (DAP) Leads: 4 Outside Diameter mm (in): 9.53 (0.375) Thickness: 1.91 (0.075) RoHS Compliant	
7717-4NG (nylon) Leads: 4 Outside Diameter mm (in): 9.53 (0.375) Thickness: 1.91 (0.075) RoHS Compliant	
7717-5DAPG (DAP) Leads: 4 Outside Diameter mm (in): 8.89 (0.350) Thickness: 3.18 (0.125) RoHS Compliant	
7717-5NG (nylon) Leads: 4 Outside Diameter mm (in): 8.89 (0.350) Thickness: 3.18 (0.125) RoHS Compliant	
7717-15DAPG (DAP) Leads: 4 Outside Diameter mm (in): 8.89 (0.350) Thickness: 0.51 (0.020) RoHS Compliant	
7717-15NG (nylon) Leads: 4 Outside Diameter mm (in): 8.89 (0.350) Thickness: 0.51 (0.020) RoHS Compliant	
7717-3DAPG (DAP) Leads: 4-Mar Outside Diameter mm (in): 8.71 (0.343) Thickness: 1.91 (0.075) RoHS Compliant	
7717-3NG (nylon) Leads: 4-Mar Outside Diameter mm (in): 8.71 (0.343) Thickness: 1.91 (0.075) RoHS Compliant	
7717-79DAPG (DAP) Leads: 3 Outside Diameter mm (in): 9.02 (0.355) Thickness: 0.97 (0.038) RoHS Compliant	
7717-79NG (nylon) Leads: 3 Outside Diameter mm (in): 9.02 (0.355) Thickness: 0.97 (0.038) RoHS Compliant	
7717-178DAPG (DAP) Leads: 3 Outside Diameter mm (in): 8.89 (0.350) Thickness: 0.53 (0.021) RoHS Compliant	
7717-178NG (nylon) Leads: 3 Outside Diameter mm (in): 8.89 (0.350) Thickness: 0.53 (0.021) RoHS Compliant	
7717-86DAPG (DAP) Leads: 3 Outside Diameter mm (in): 8.71 (0.343) Thickness: 1.91 (0.075) RoHS Compliant	
7717-86NG (nylon) Leads: 3 Outside Diameter mm (in): 8.71 (0.343) Thickness: 1.91 (0.075) RoHS Compliant	
7717-22NG (nylon) Leads: 3 Outside Diameter mm (in): 8.71 (0.343) Thickness: 1.91 (0.075) RoHS Compliant	
7717-22DAPG (DAP) Leads: 3 Outside Diameter mm (in): 8.71 (0.343) Thickness: 1.91 (0.075) RoHS Compliant	
7717-238NG (nylon) Leads: 4-Mar Outside Diameter mm (in): 10.16 (0.400) Thickness: 4.06 (0.160) RoHS Compliant	
7717-300NG (nylon) Leads: Universal Outside Diameter mm (in): 11.18 (0.440) Thickness: 9.65 (0.380) RoHS Compliant	
7717-94NG (nylon) Leads: 4-Mar Outside Diameter mm (in): 8.89 (0.350) Thickness: 0.97 (0.038) RoHS Compliant	