




8 7 6 5 4 3 2 1



TOP VIEW



SIDE VIEW



ISOMETRIC VIEW

DNMF100AC230

Finish - Housing - Black Painted Aluminum

- Fan - Black Painted Steel

Rated - 230 VAC, 50/60 Hz, 0.09 Amps

Free Flow Air Delivery - 105 CFM

Hardware

4 Screws - Panhead Self-tapping 10-32 x 1/2"

8 Screws - Type F 10-24 x 3/8"

4 Bolts - 8-32 x 2"

4 Hex Nuts - 8-32 Thread

4 External Tooth Washers



**HAMMOND
MANUFACTURING™**

DNMF100AC230

www.hammondmfg.com

8 7 6 5 4 3 2 1