



MODEL: BU-P2249-C-XX

Test Lead, BNC (M) on Each End, RG-58C/U



- **Materials:**
 - Cable: Cable is RG 58C/U, complies to Mil-M17/155-00001
Jacket is non-contaminating PVC
Center conductor is 20 AWG (19x33) tinned copper
Shield is tinned copper braid (95% coverage)
 - Male BNC: Body is tarnish resistant nickel plated brass
Center Contact is Gold plated brass
Insulator is PTFE
 - Strain Relief is Molded PVC that is bonded to the BNC.
- **Ratings:** Impedance: 50 Ohms
Capacitance per foot: 30.8 pf
Power Loss/100 Ft. @ 1 MHz: .40 dB
Hands free testing to 1400 VRMS
Operating Temperature: -40°C to 85°C
- **Ordering:** The “XX” in the part number represents the length in Inches. Standard lengths are:
6”, 12”, 24”, 36”, 48”, 60”, 72”, 120”, 144”, 180”, 240”, 300”, and 600”
- **RoHS Compliant, CE Compliant**