

## Nut - A-INL-NPT3/4-P-BK - 1411238

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Nut, PA 6 GF 30, Connecting thread: 3/4 inch NPT, For threads 3/4 inch NPT, Color: jet black



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	5 pc
Weight per Piece (excluding packing)	4.0 g
Custom tariff number	39269097
Country of origin	Turkey

### Technical data

#### Dimensions

Length	5 mm
Connecting thread diameter	25.9 mm
Wrench size, counter nut	33 mm
Hexagon angular dimension GRP	37.5 mm

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 100 °C
---------------------------------	-------------------

#### General

Material	PA 6 GF 30
Thread type on connection side	3/4 inch NPT
Flammability rating according to UL 94	V2
Color	jet black RAL 9005
	jet black

#### Standards and Regulations

## Nut - A-INL-NPT3/4-P-BK - 1411238

### Technical data

#### Standards and Regulations

Flammability rating according to UL 94	V2
--	----

#### Classifications

##### eCl@ss

eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 8.0	23110701

#### ETIM

ETIM 4.0	EC000032
ETIM 5.0	EC000129

#### Drawings

Dimensional drawing

