





RMQ 22 Surface Mounting Enclosures

Control Circuit Devices

	Number of locations	Cable entry knockouts		Max. number of lamps in simultaneous operation	Type	Price See Price List	Std.. pack
		Bottom	Sides:				
	Quantity	Quantity × PG...		Max.	Colour 1)		
Surface mounting enclosure IP 65 totally insulated							
With moulded cover fixing screws Cannot be used to mount: EC..., BFT..., BCE(L) 24							
Emergency-stop button	1	1×13.5	3×16	—	IGE1M 081696		1 off
	1	1×13.5	3×16	1	I1M 038834		
	2	2×13.5	3×16	2	I2M 041207		
	3	2×13.5	4×16	2	I3M 043580		
	4	2×13.5	4×16	3	I4M 045953		
	5	2×13.5	4×16	4	I5M 048326		

One-way screws


For securing enclosure against tampering



ES-IM 050699	4 off
ES-IGE 060244	4 off

Surface mounting enclosure IP 65 totally insulated



With quick-release fastener for cover and base plate for EK...C
Enclosure pebble grey
Cannot be used to mount: EC..., BFT..., BCE(L) 24



12 ²⁾	—	1×21/16 ²⁾ 4 2×29/16 ²⁾	I12M 053072	1 off
------------------	---	--	----------------	-------

Notes

- ¹⁾ Colour: Yellow RAL 1004, enclosure cover light grey RAL 7032, enclosure base anthracite RAL 7016
²⁾ Cable entry at top and bottom

Style: flush mounting**Style: surface mounting**

Accessories	Page
1 Actuator	03/014
2 Fixing adapter	03/036
3 Contact element	03/036
4 Contact element	03/037
5 Fixing adapter	03/037
Button plate	03/044
Legend plate	03/052
Accessories	03/057

For networking

AS interface	01/046
--------------	--------