





RECOMMEND PC BOARD HOLE PATTERN



PART NO.	CODE NO.	A	B
A2-1PA-2.54DSA(71)	CL620-0051-5-71	1 2.24	—
A2-2PA-2.54DSA(71)	CL620-0052-8-71	2 4.78	2.54
A2-3PA-2.54DSA(71)	CL620-0053-0-71	3 7.32	5.08
A2-4PA-2.54DSA(71)	CL620-0054-3-71	4 9.86	7.62
A2-5PA-2.54DSA(71)	CL620-0055-6-71	5 12.40	10.16
A2-6PA-2.54DSA(71)	CL620-0056-9-71	6 14.94	12.70
A2-7PA-2.54DSA(71)	CL620-0057-1-71	7 17.48	15.24
A2-8PA-2.54DSA(71)	CL620-0058-4-71	8 20.02	17.78
A2-9PA-2.54DSA(71)	CL620-0059-7-71	9 22.56	20.32
A2-10PA-2.54DSA(71)	CL620-0060-6-71	10 25.10	22.86
A2-11PA-2.54DSA(71)	CL620-0061-9-71	11 27.64	25.40
A2-12PA-2.54DSA(71)	CL620-0062-1-71	12 30.18	27.94
A2-13PA-2.54DSA(71)	CL620-0063-4-71	13 32.72	30.48
A2-14PA-2.54DSA(71)	CL620-0064-7-71	14 35.26	33.02
A2-15PA-2.54DSA(71)	CL620-0065-0-71	15 37.80	35.56
A2-16PA-2.54DSA(71)	CL620-0066-2-71	16 40.34	38.10
A2-17PA-2.54DSA(71)	CL620-0067-5-71	17 42.88	40.64
A2-18PA-2.54DSA(71)	CL620-0068-8-71	18 45.42	43.18
A2-19PA-2.54DSA(71)	CL620-0069-0-71	19 47.96	45.72
A2-20PA-2.54DSA(71)	CL620-0070-0-71	20 50.50	48.26

NOTES 1. THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.
2. NUMBER OF CONTACTS.

1	POLYBUTYLENE TEREPHTHALATE	BLACK	UL94V-0	2	BRASS	CONTACT AREA : GOLD 0.2μ m min. DIP AREA : TIN-PLATING 2μ m min. UNDER PLATING : NICKEL 2.5μ m min.
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS	
CODE NO. (OLD) CL						

DESIGNED A. SUZUKAWA 05.10.07	CHECKED H. Ogasawara 05.10.07	APPROVED H. Ogasawara 05.10.11	RELEASED
DRAWING NO. EDC3-018389-21			
PART NO. A2-20PA-2.54DSA(71)			
CODE NO. CL620			

SCALE FREE	UNITS mm	1
HIROSE ELECTRIC CO., LTD.		
CL620		
1/1		

TO
PCK