





# **FEMALE PLUG WITH LOCKING LEVER PIN SPACING 3.5 MM / 0.138 IN 100% PROTECTED AGAINST MISMATING**

733-102/037-000 TO 733-112/037-000

|                                                      |                                  |
|------------------------------------------------------|----------------------------------|
| ITEM-NO. (ITEM-NO.)                                  | 733-103/037-000                  |
| Cross section1 (Cross section / mm <sup>2</sup> )    | 0.08 - 0.5                       |
| Cross section2 (Cross section / AWG)                 | 28 - 20                          |
| Strip length (Strip length / mm)                     | 5 - 6                            |
| Measured voltage (Measured voltage / V)              | 160                              |
| Measured shock voltage (Measured shock voltage / kV) | 2.5                              |
| Pollution degree (Pollution degree)                  | 2                                |
| Current intensity (Current intensity / A)            | 6                                |
| RM (PIN SPACING / mm)                                | 2.5                              |
| P (NO. OF POLES)                                     | 3                                |
| Height (Height / mm)                                 | 11.8                             |
| Width (Width / mm)                                   | 19.3                             |
| Depth (Depth / mm)                                   | 17.1                             |
| No. of connection Points (No. of connection Points)  | 3                                |
| No. of potentials (No. of potentials)                | 3                                |
| COLOR (COLOR)                                        | lichtgrau                        |
| Comment (Comment)                                    | L = (No. of poles x Pin Spacing) |