

[Home](#)[Products](#)[Search](#)[Support](#)[About Us](#)
[Home](#) > [Search Engine](#) > Catalog: PKM17EWH4000

Piezoelectric Sound Components > Piezoelectric Sounders > External-Drive

Specification

Global Part Number	PKM17EWH4000
Previous Part Number	PKM17EWH4000
Sound Pressure Level	75dB min.
Measure Condition of Sound Pressure Level	[3Vp-p,4kHz,square wave,10cm]
Oscillating Frequency	
Measure Condition of Oscillation Frequency	
Current Consumption	
Measure Condition of Current Consumption	
Min. of Operating Voltage Range	
Max. of Operating Voltage Range	25.0 Vp-p max.
Capacitance	9.5nF ±30%
Measure Condition of Capacitance	[1kHz]
Type	Lead Wire Type
Operating Temperature Range	-20 to +70°C
Storage Temperature Range	-30 to +80°C

Details

-  [Part Numbering](#)
-  [Appearance](#)
-  [Dimensions](#)
-  [Features and Applications](#)
-  [Frequency Response](#)
-  [Frequency Response](#)
-  [Recommended Circuit](#)
-  [Notice \(storage and operating condition\)](#)
-  [Notice \(soldering and mounting\)](#)
-  [Notice \(handling\)](#)

Minimum Quantity

180mm Paper Tape	
180mm Embossed Tape	
330mm Paper Tape	
330mm Embossed Tape	
Bulk Case	
Bulk(Bag)	
Ammo Pack	
320Reel	

Magazine	
Box	500

**Product specifications in this catalog are as of November 2006,
and are subject to change or obsolescence without notice.
Please approve our product specifications or transact the approval sheet before ordering.
Please read rating and !Cautions first.**

All products and company names herein are trademarks or registered trademarks of their respective owners.

UP 

| [Site Map](#) | [History](#) | [Terms of use](#) | [Privacy Policy](#) |

All Rights Reserved, Copyright© Murata Manufacturing Co., Ltd. 2006