

Terminal blocks

to Type 189

ASP043 page 44

Type 339 page 86

Accessories

for Type 189

Coding set
720293 page 204

Note for Type 189

Packaging for automated processing is available on demand. Please do not hesitate to contact us.

Type 189

Header, centerline 3.5 mm / 0.138 inches, vertical mounting, designed for THR, optional Tape on Reel packaging for automated processing, square contact pins 0.8 mm / 0.031 inches, closed ends, codable

Technical Data


V / A 300 / 10

130 V / 2.5 kV / 10 A

Insulation co-ordination according to EN 60664-1			
Clearance and creepage distances	min. 2.7 mm		
Insulating material class	CTI 600		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	200	500	500
Rated test voltage	2.5	4	2.5
Protection category according to IEC 529	IP00		
Solder pin dimension	0.8 x 0.8 mm		
Recommended pc board hole dia.	Ø 1.3 mm		
Solder pin length	3.2 mm		
Pole size	2 - 18		
Color	black		

Dimensions in mm

1 mm = 0.0394 in.



$L = (\text{pole size} - 1) \times \text{centerline} + 5.35 \text{ mm} / 0.211 \text{ inches}$

Part numbers (P/N)

(information: page 110)
Complete the part number by adding the pole size.

Type 189

centerline 3.5 mm / 0.138 inches

P/N 311891

	02	03	04	05	06	07	08
	09	10	11	12	13	14	15
	17	18					

Standard pole sizes

Available on demand. Minimum order quantity 5000 pieces per item.