






注記
 NOTES

1. 嵌合相手 : 5557-NR-210
MATES WITH : 5557-NR-210
2. 一般公差 : ± 0.38
GENERAL TOLERANCE : ± 0.38

材料 MATERIAL	 中参照 SEE DRAWING
仕上げ FINISH	 中参照 SEE DRAWING

RELEASED	EC NO: J2007-1208	2006/10/27	2006/10/31	2006/10/31	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
						10 UNDER ± ---		MM ONLY		2:1	METRIC		
						10 OVER 30 UNDER ± ---		DRAWN BY DATE		TITLE MINI-FIT JR R/A HEADER ASSY WITH MOUTING PEGS			
						30 OVER ± ---		K.SAITO 2006/10/24					
						ANGULAR ± --- °		CHECKED BY DATE		MOLEX MOLEX INCORPORATED			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		K.TOYODA 2006/10/24											
0	REV					APPROVED BY DATE		DOCUMENT NO.		SHEET NO.			
						N.UKITA 2006/10/24		SD-5569-001		1 OF 1			
SEE CHART												THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	

BULK PACKAGED PER PK-5569-002										
PART NUMBER	ENG. NUMBER	CKT. SIZE	PLATING (NOTE 2)	HSG MAT'L	PART NUMBER	ENG. NUMBER	CKT. SIZE	PLATING (NOTE 2)	HSG MAT'L	
39-30-1020	5569-02A2	2	TIN OVER COPPER SEE NOTE 2 OPTION "BLANK"	94V-2	39-30-0020	5569-02A2-210	2	TIN OVER COPPER SEE NOTE 2 OPTION "BLANK"	94V-0	
39-30-1040	5569-04A2	4			39-30-0040	5569-04A2-210	4			
39-30-1060	5569-06A2	6			39-30-0060	5569-06A2-210	6			
39-30-1080	5569-08A2	8			39-30-0080	5569-08A2-210	8			
39-30-1100	5569-10A2	10			39-30-0100	5569-10A2-210	10			
39-30-1120	5569-12A2	12			39-30-0120	5569-12A2-210	12			
39-30-1140	5569-14A2	14			39-30-0140	5569-14A2-210	14			
39-30-1160	5569-16A2	16			39-30-0160	5569-16A2-210	16			
39-30-1180	5569-18A2	18			39-30-0180	5569-18A2-210	18			
39-30-1200	5569-20A2	20			39-30-0200	5569-20A2-210	20			
39-30-1220	5569-22A2	22	39-30-0220	5569-22A2-210	22					
39-30-1240	5569-24A2	24			39-30-0240	5569-24A2-210	24			
39-30-1021	5569-02A2G	2	30 μ" GOLD SEE NOTE 2 OPTION "G"	94V-2	39-30-1022	5569-02A2G-210	2	30 μ" GOLD SEE NOTE 2 OPTION "G"	94V-0	
39-30-1041	5569-04A2G	4			39-30-1042	5569-04A2G-210	4			
39-30-1061	5569-06A2G	6			39-30-1062	5569-06A2G-210	6			
39-30-1081	5569-08A2G	8			39-30-1082	5569-08A2G-210	8			
39-30-1101	5569-10A2G	10			39-30-1102	5569-10A2G-210	10			
39-30-1121	5569-12A2G	12			39-30-1122	5569-12A2G-210	12			
39-30-1141	5569-14A2G	14			39-30-1142	5569-14A2G-210	14			
39-30-1161	5569-16A2G	16			39-30-1162	5569-16A2G-210	16			
39-30-1181	5569-18A2G	18			39-30-1182	5569-18A2G-210	18			
39-30-1201	5569-20A2G	20			39-30-1202	5569-20A2G-210	20			
39-30-1221	5569-22A2G	22	39-30-1222	5569-22A2G-210	22					
39-30-1241	5569-24A2G	24			39-30-1242	5569-24A2G-210	24			
39-30-0021	5569-02A2G2	2	15 μ" GOLD SEE NOTE 2 OPTION "G2"	94V-2	39-30-0022	5569-02A2G2-210	2	15 μ" GOLD SEE NOTE 2 OPTION "G2"	94V-0	
39-30-0041	5569-04A2G2	4			39-30-0042	5569-04A2G2-210	4			
39-30-0061	5569-06A2G2	6			39-30-0062	5569-06A2G2-210	6			
39-30-0081	5569-08A2G2	8			39-30-0082	5569-08A2G2-210	8			
39-30-0101	5569-10A2G2	10			39-30-0102	5569-10A2G2-210	10			
39-30-0121	5569-12A2G2	12			39-30-0122	5569-12A2G2-210	12			
39-30-0141	5569-14A2G2	14			39-30-0142	5569-14A2G2-210	14			
39-30-0161	5569-16A2G2	16			39-30-0162	5569-16A2G2-210	16			
39-30-0181	5569-18A2G2	18			39-30-0182	5569-18A2G2-210	18			
39-30-0201	5569-20A2G2	20			39-30-0202	5569-20A2G2-210	20			
39-30-0221	5569-22A2G2	22	39-30-0222	5569-22A2G2-210	22					
39-30-0241	5569-24A2G2	24			39-30-0242	5569-24A2G2-210	24			
NOT TOOLED	5569-02A2G3	2	50 μ" GOLD SEE NOTE 2 OPTION "G3"	94V-2	NOT TOOLED	5569-02A2G3-210	2	50 μ" GOLD SEE NOTE 2 OPTION "G3"	94V-0	
15-27-1514	5569-04A2G3	4			NOT TOOLED	5569-04A2G3-210	4			
15-27-1511	5569-06A2G3	6			NOT TOOLED	5569-06A2G3-210	6			
15-27-1512	5569-08A2G3	8			NOT TOOLED	5569-08A2G3-210	8			
15-27-1503	5569-10A2G3	10			15-27-1504	5569-10A2G3-210	10			
NOT TOOLED	5569-12A2G3	12			NOT TOOLED	5569-12A2G3-210	12			
NOT TOOLED	5569-14A2G3	14			NOT TOOLED	5569-14A2G3-210	14			
15-27-1513	5569-16A2G3	16			NOT TOOLED	5569-16A2G3-210	16			
NOT TOOLED	5569-18A2G3	18			NOT TOOLED	5569-18A2G3-210	18			
NOT TOOLED	5569-20A2G3	20			NOT TOOLED	5569-20A2G3-210	20			
NOT TOOLED	5569-22A2G3	22	NOT TOOLED	5569-22A2G3-210	22					
NOT TOOLED	5569-24A2G3	24			NOT TOOLED	5569-24A2G3-210	24			
REVISION:	ECR/ECN INFORMATION:		TITLE:					SHEET No.		
L2	EC No: UCP2009-2779		MINI-FIT JR.® RIGHT ANGLE HEADER ASSEMBLIES WITH MOUNTING PEGS					- 2 -		
	DATE: 2009/05/13									
DOCUMENT NUMBER:			Drawn By:		Checked By:		Approved By:			
SDA-5569-NA2*-*			TRBENES		JBELL		FSMITH			
Filename: SPOMASTER.DOC			Revision: 1			Location: Workmanager General Docs Class.			Date: 4-15-2002	

BULK PACKAGED PER PK-5569-002										
PART NUMBER	ENG. NUMBER	CKT. SIZE	PLATING (NOTE 2)	HSG MAT'L	PART NUMBER	ENG. NUMBER	CKT. SIZE	PLATING (NOTE 2)	HSG MAT'L	
39-34-9022	5569-02A2-100	2	TIN OVER COPPER SEE NOTE 2 OPTION "BLANK"	94V-2	39-31-1021	5569-02A2-BL	2	TIN OVER COPPER SEE NOTE 2 OPTION "BLANK"	94V-2	
39-34-9042	5569-04A2-100	4			39-31-1041	5569-04A2-BL	4			
39-34-9064	5569-06A2-100	6			39-31-1061	5569-06A2-BL	6			
39-34-9084	5569-08A2-100	8			39-31-1081	5569-08A2-BL	8			
39-34-9104	5569-10A2-100	10			39-31-1101	5569-10A2-BL	10			
39-34-9124	5569-12A2-100	12			39-31-1121	5569-12A2-BL	12			
39-34-9144	5569-14A2-100	14			39-31-1141	5569-14A2-BL	14			
39-34-9164	5569-16A2-100	16			39-31-1161	5569-16A2-BL	16			
39-34-9184	5569-18A2-100	18			39-31-1181	5569-18A2-BL	18			
39-34-9204	5569-20A2-100	20			39-31-1201	5569-20A2-BL	20			
39-34-9224	5569-22A2-100	22			39-31-1221	5569-22A2-BL	22			
39-34-9244	5569-24A2-100	24			39-31-1241	5569-24A2-BL	24			
39-34-9023	5569-02A2S-100	2	TIN OVER NICKEL SEE NOTE 2 OPTION "S"	94V-2	39-31-6029	5569-02A2G-BL	2	30 μ" GOLD SEE NOTE 2 OPTION "G"	94V-2	
39-34-9043	5569-04A2S-100	4			39-31-6049	5569-04A2G-BL	4			
39-34-9063	5569-06A2S-100	6			39-31-6069	5569-06A2G-BL	6			
39-34-9083	5569-08A2S-100	8			39-31-6089	5569-08A2G-BL	8			
39-34-9103	5569-10A2S-100	10			39-31-6109	5569-10A2G-BL	10			
39-34-9123	5569-12A2S-100	12			39-31-6129	5569-12A2G-BL	12			
39-34-9143	5569-14A2S-100	14			39-31-6149	5569-14A2G-BL	14			
39-34-9163	5569-16A2S-100	16			39-31-6169	5569-16A2G-BL	16			
39-34-9183	5569-18A2S-100	18			39-31-6189	5569-18A2G-BL	18			
39-34-9203	5569-20A2S-100	20			39-31-6209	5569-20A2G-BL	20			
39-34-9223	5569-22A2S-100	22			39-31-6229	5569-22A2G-BL	22			
39-34-9243	5569-24A2S-100	24			39-31-6249	5569-24A2G-BL	24			
39-34-9020	5569-02A2-400	2	TIN OVER COPPER SEE NOTE 2 OPTION "BLANK"	94V-0	39-31-7020	5569-02A2G2-BL	2	15 μ" GOLD SEE NOTE 2 OPTION "G2"	94V-2	
39-34-9040	5569-04A2-400	4			39-31-7040	5569-04A2G2-BL	4			
39-34-9060	5569-06A2-400	6			39-31-7060	5569-06A2G2-BL	6			
39-34-9080	5569-08A2-400	8			39-31-7080	5569-08A2G2-BL	8			
39-34-9100	5569-10A2-400	10			39-31-7100	5569-10A2G2-BL	10			
39-34-9120	5569-12A2-400	12			39-31-7120	5569-12A2G2-BL	12			
39-34-9140	5569-14A2-400	14			39-31-7140	5569-14A2G2-BL	14			
39-34-9160	5569-16A2-400	16			39-31-7160	5569-16A2G2-BL	16			
39-34-9180	5569-18A2-400	18			39-31-7180	5569-18A2G2-BL	18			
39-34-9200	5569-20A2-400	20			39-31-7200	5569-20A2G2-BL	20			
39-34-9220	5569-22A2-400	22			39-31-7220	5569-22A2G2-BL	22			
39-34-9240	5569-24A2-400	24			39-31-7240	5569-24A2G2-BL	24			
39-34-9021	5569-02A2S-400	2	TIN OVER NICKEL SEE NOTE 2 OPTION "S"	94V-0	39-31-7021	5569-02A2G3-BL	2	50 μ" GOLD SEE NOTE 2 OPTION "G3"	94V-2	
39-34-9041	5569-04A2S-400	4			39-31-7041	5569-04A2G3-BL	4			
39-34-9061	5569-06A2S-400	6			39-31-7061	5569-06A2G3-BL	6			
39-34-9081	5569-08A2S-400	8			39-31-7081	5569-08A2G3-BL	8			
39-34-9101	5569-10A2S-400	10			39-31-7101	5569-10A2G3-BL	10			
39-34-9121	5569-12A2S-400	12			39-31-7121	5569-12A2G3-BL	12			
39-34-9141	5569-14A2S-400	14			39-31-7141	5569-14A2G3-BL	14			
39-34-9161	5569-16A2S-400	16			39-31-7161	5569-16A2G3-BL	16			
39-34-9181	5569-18A2S-400	18			39-31-7181	5569-18A2G3-BL	18			
39-34-9201	5569-20A2S-400	20			39-31-7201	5569-20A2G3-BL	20			
39-34-9221	5569-22A2S-400	22			39-31-7221	5569-22A2G3-BL	22			
39-34-9241	5569-24A2S-400	24			39-31-7241	5569-24A2G3-BL	24			
REVISION: L2	ECR/ECN INFORMATION: EC No: UCP2009-2779 DATE: 2009/05/13		TITLE: MINI-FIT JR.® RIGHT ANGLE HEADER ASSEMBLIES WITH MOUNTING PEGS						SHEET No. - 4 -	
DOCUMENT NUMBER: SDA-5569-NA2*-*			Drawn By: TRBENES		Checked By: JBELL		Approved By: FSMITH			
Filename: SPOMASTER.DOC			Revision: 1		Location: Workmanager General Docs Class.			Date: 4-15-2002		

TRAY PACKAGED PER PK-5569-003									
PART NUMBER	ENG. NUMBER	CKT. SIZE	PLATING (NOTE 2)	HSG MAT'L	PART NUMBER	ENG. NUMBER	CKT. SIZE	PLATING (NOTE 2)	HSG MAT'L
50-36-1757	5569-02A2S-T	2	TIN OVER NICKEL SEE NOTE 2 OPTION "S"	94V-2	50-36-1758	5569-02A2S-210-T	2	TIN OVER NICKEL SEE NOTE 2 OPTION "S"	94V-0
50-36-1767	5569-04A2S-T	4			50-36-1768	5569-04A2S-210-T	4		
50-36-1777	5569-06A2S-T	6			50-36-1778	5569-06A2S-210-T	6		
50-36-1787	5569-08A2S-T	8			50-36-1788	5569-08A2S-210-T	8		
50-36-1797	5569-10A2S-T	10			50-36-1798	5569-10A2S-210-T	10		
50-36-1807	5569-12A2S-T	12			50-36-1808	5569-12A2S-210-T	12		
50-36-1817	5569-14A2S-T	14			50-36-1818	5569-14A2S-210-T	14		
50-36-1827	5569-16A2S-T	16			50-36-1828	5569-16A2S-210-T	16		
50-36-1837	5569-18A2S-T	18			50-36-1838	5569-18A2S-210-T	18		
50-36-1847	5569-20A2S-T	20			50-36-1848	5569-20A2S-210-T	20		
50-36-1857	5569-22A2S-T	22			50-36-1858	5569-22A2S-210-T	22		
50-36-1867	5569-24A2S-T	24			50-36-1868	5569-24A2S-210-T	24		
50-36-1755	5569-02A2GS-T	2	30 μ" SELECT GOLD SEE NOTE 2 OPTION "GS"	94V-2	50-36-1756	5569-02A2GS-210-T	2	30 μ" SELECT GOLD SEE NOTE 2 OPTION "GS"	94V-0
50-36-1765	5569-04A2GS-T	4			50-36-1766	5569-04A2GS-210-T	4		
50-36-1775	5569-06A2GS-T	6			50-36-1776	5569-06A2GS-210-T	6		
50-36-1785	5569-08A2GS-T	8			50-36-1786	5569-08A2GS-210-T	8		
50-36-1795	5569-10A2GS-T	10			50-36-1796	5569-10A2GS-210-T	10		
50-36-1805	5569-12A2GS-T	12			50-36-1806	5569-12A2GS-210-T	12		
50-36-1815	5569-14A2GS-T	14			50-36-1816	5569-14A2GS-210-T	14		
50-36-1825	5569-16A2GS-T	16			50-36-1826	5569-16A2GS-210-T	16		
50-36-1835	5569-18A2GS-T	18			50-36-1836	5569-18A2GS-210-T	18		
50-36-1845	5569-20A2GS-T	20			50-36-1846	5569-20A2GS-210-T	20		
50-36-1855	5569-22A2GS-T	22			50-36-1856	5569-22A2GS-210-T	22		
50-36-1865	5569-24A2GS-T	24			50-36-1866	5569-24A2GS-210-T	24		
		2					2		
		4					4		
		6					6		
		8					8		
		10					10		
		12					12		
		14					14		
		16					16		
		18					18		
		20					20		
		22					22		
		24					24		
		2					2		
		4					4		
		6					6		
		8					8		
		10					10		
		12					12		
		14					14		
		16					16		
		18					18		
		20					20		
		22					22		
		24					24		
REVISION:	ECR/ECN INFORMATION:		TITLE:						SHEET No.
L2	EC No: UCP2009-2779		MINI-FIT JR.® RIGHT ANGLE HEADER ASSEMBLIES WITH MOUNTING PEGS						- 6 -
	DATE: 2009/05/13								
DOCUMENT NUMBER:			Drawn By:		Checked By:		Approved By:		
SDA-5569-NA2*-*			TRBENES		JBELL		FSMITH		
Filename: SPOMASTER.DOC			Revision: 1		Location: Workmanager General Docs Class.		Date: 4-15-2002		