

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [98267-0270](#)
Status: **Active**
Overview: [Premo-Flex™ FFC and Etched Polyimide Jumpers](#)
Description: 1.00mm Pitch Premo-Flex™ FFC Jumper, Opposite Side Contacts (Type D), 12 Circuits, 0.051m Cable Length, 0.22mm Cable Thickness, Tin(Sn) Plating

Documents:

Drawing (PDF)	Packaging Specification PK-98267-001 (PDF)
Product Specification PS-98267-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Cable
Series	98267
Comments	Contacts on opposite sides, Type D
Crimp Quality Equipment	Yes
Overview	Premo-Flex™ FFC and Etched Polyimide Jumpers
Product Name	Premo-Flex™ FFC Jumper
UPC	756054771006

Physical

Cable Length	0.051m
Circuits (Loaded)	12
Net Weight	0.483/g
Packaging Type	Bag
Pitch - Termination Interface	1.00mm
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	1.2A
Voltage - Maximum	60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-98267-001
Product Specification	PS-98267-001
Sales Drawing	SD-98267-001



Series

image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[98267Series](#)

Use With

52207 , 52271 , 52852 , 52793 , 52808 ,
52610 , 52807 , 52030 , 52806 See [http://
www.molex.com/product/ffcfpc_th.html](http://www.molex.com/product/ffcfpc_th.html)