

APPLIANCE COUPLERS

Cordsets

IEC / EN 60320-1 / C13,
protection class I, pin
temperature 70 °C (cold
condition)



**Medical Grade
Standard
NEMA 5-15P**


IEC/EN 60320-1/C19



**North America
Standard
NEMA 5-15**




C7 Non-Polarized



C7 Polarized



C5 Polarized



**North America, Europlug, United Kingdom, Schuko
Standards
NEMA 1-15P, 5-15P, CEE 7/7, 7/16, BS 1363**



Cord Type SJT	Cord Type SJT	CS01.0221.150	C7 Non-Polarized Nema 1-15P	standard SPT2	2.5 A / 250 V
		CS02.0221.150	C7 Polarized Nema 1-15P	standard AWG18	7 A / 250 V
Conductor 3 x 18 AWG	Conductor 3 x 14 AWG	CS01.0121.150	C7 Non-Polarized Europlug CEE 7/16	H03VVH2-F	2.5 A / 250 V
Rated 10 A / 125, 250 V 15 A / 125 V	Rated 16 A / 250 V	CS01.0421.150	C7 Non-Polarized UK BS 1363	H03VVH2-F	2.5 A / 250 V
		CS03.0421.150	C5 Polarized UK BS 1363	H03VV-F	2.5 A / 250 V
Color clear	Color black	CS03.0521.150	C5 Polarized Schuko Plug	H03VV-F	2.5 A / 250 V
	Length 2,5 meters	CS03.0621.150	C5 Polarized North America Nema 5-15P	standard SPT2	2.5 A / 250 V
		Color black, Length 1500 mm			
4300	6016	CS			

Approvals / Cordsets supplied by SCHURTER carry the country specific approvals

4300.0920	6009.5195	CS01.0121.150 - CS03.0621.150
-----------	-----------	-------------------------------