



Federleisten, von oben steckbar





Raster 2,5 mm/Centerline 2.5 mm			
Polzahl No. of Positions	Best.-Nr./Part No.		L _{max.} mm
	grau grey	grün green	
2	163833-1	164821-1	5,1
3	163680-1	164516-1	7,6
4	163680-2	164516-2	10,1
5	163680-3	164516-3	12,6
6	163680-4	164516-4	15,1
7	163680-5	164516-5	17,6
8	163680-6	164516-6	20,1
9	163680-7	164516-7	22,6
10	163680-8	164516-8	25,1
11	163680-9	164516-9	27,6
12	1-163680-1	1-164516-1	30,1
13	1-163680-2	1-164516-2	32,6
14	1-163680-3	1-164516-3	35,1
15	1-163680-4	1-164516-4	37,6
16	1-163680-5	1-164516-5	40,1
17	1-163680-6	1-164516-6	42,6
18	1-163680-7	1-164516-7	45,1
19	1-163680-8	1-164516-8	47,6
20	1-163680-9	1-164516-9	50,1

Raster 5,0 mm/Centerline 5.0 mm		
Polzahl No. of Positions	Best.-Nr./Part No.	
	grau grey	L _{max.} mm
2	163986-1	7,6
3	163685-1	12,6
4	163685-2	17,6
5	163685-3	22,6
6	163685-4	27,6
7	163685-5	32,6
8	163685-6	37,6
9	163685-7	42,6
10	163685-8	47,6
11	163685-9	52,6
12	1-163685-1	57,6
13	1-163685-2	62,6
14	1-163685-3	67,6
15	1-163685-4	72,6

Female Connectors, Top Entry

Federleisten, von unten steckbar



Raster 2,5 mm/Centerline 2.5 mm			
Polzahl No. of Positions	Best.-Nr./Part No.		L _{max.} mm
	grau grey	grün green	
2	164254-1	—	5,1
3	163681-1	164517-1	7,6
4	163681-2	164517-2	10,1
5	163681-3	164517-3	12,6
6	163681-4	164517-4	15,1
7	163681-5	164517-5	17,6
8	163681-6	164517-6	20,1
9	163681-7	164517-7	22,6
10	163681-8	164517-8	25,1
11	163681-9	164517-9	27,6
12	1-163681-1	1-164517-1	30,1
13	1-163681-2	1-164517-2	32,6
14	1-163681-3	1-164517-3	35,1
15	1-163681-4	1-164517-4	37,6
16	1-163681-5	1-164517-5	40,1
17	1-163681-6	1-164517-6	42,6
18	1-163681-7	1-164517-7	45,1
19	1-163681-8	1-164517-8	47,6
20	1-163681-9	1-164517-9	50,1

Raster 5,0 mm/Centerline 5.0 mm		
Polzahl No. of Positions	Best.-Nr./Part No.	
	grau grey	L _{max.} mm
2	163996-1	7,6
3	163686-1	12,6
4	163686-2	17,6
5	163686-3	22,6
6	163686-4	27,6
7	163686-5	32,6
8	163686-6	37,6
9	163686-7	42,6
10	163686-8	47,6
11	163686-9	52,6
12	1-163686-1	57,6
13	1-163686-2	62,6
14	1-163686-3	67,6
15	1-163686-4	72,6

Female Connectors, Bottom Entry