



SVS ECO LED VALVE PLUG FORM C 8MM LED VDR 24V


2+PE field-wireable M12

Form C (8 mm)
24 V AC/DC with LED and VDR
metric

[Link to Product](#)

Illustration





Height: 26 mm

Product may differ from Image

Approvals



Form

Form 30105

Technical Data

Operating voltage	24 V AC/DC $\pm 10\%$
Operating current per contact	max. 1.5 A
Connection cross section	0.34...0.5 mm ²
Sealing range (cable Ø)	4...6 mm
Locking of ports	M2.5 (recommended torque 0.4 Nm)
Compression gland	M12 × 1.75 mm
Contact figure	Cable outlet can be turned in 90° steps
Protection	IP65 inserted and tightened

General data

Temperature range -40...+60 °C

Commercial data

country of origin	HU
customs tariff number	85369010
minimum order quantity	1