





Recommended P.C.Board
Hole Layout



Specifications

Current Rating: 3Amp

Insulation Resistance: 1000MΩ Min.

Dielectric Withstanding: 600V AC/DC

Contact Resistance: 20mΩ Max.

Operating Temperature: -40°C to +105°C

Materials

Contact Material: Copper Alloy

Insulation Material: Polyester, UL 94V-0

P.B.T

Contact plating: Glod Flash

All materials must be GP materials

NUMBER	Dimensions		
OF POSITION	A	B	C
10	32.00	21.84	10.16
14	37.08	26.92	15.24
16	39.62	29.46	17.78
20	44.70	34.54	22.86
26	52.32	42.16	30.48
30	57.40	47.24	35.56
34	62.48	52.32	40.64
40	70.10	59.94	48.26
50	82.80	72.64	60.96
60	95.50	85.34	73.66
64	100.58	90.42	78.74

CnC Tech, LLC

Industrial Cable and Connector Technology

DESIGN *lumayl*

DATE 2011. 12. 05

CHECKED

PART NO.

REV
A

UNIT
mm

3010-XX-002-12-00

SIZE

UNLESS OTHERWISE SPECIFIED TOLERANCE
ANG ±5°
0 ±0.3
.0 ±0.15
.00 ±0.10

