




REV. 0

DCO 141310


COIL: @ 25°C
 RESISTANCE 1130 OHMS ±10%
 NOMINAL VOLTAGE 26.5 VDC
 MUST OPERATE 18.0 VDC
 MUST RELEASE 1.23 VDC MIN.

ENVIRONMENT:

VIBRATION 140 CPS TO 2000 CPS @ 100 g's
 SHOCK 150 g's 11 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 6.0 MS MAX
RELEASE TIME 2.0 MS MAX
CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO
1A 28 VDC RESISTIVE 100,000
OPERATIONS

DR. B.D. 8/26/99 CKX ERRY 8/26/99

COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. C. I. I.
 CUST. NO. STD REV.

"MAV" RELAY

MAVC-26S2