


MPD Series	Flange Recess	Clearance Hole	Recommended Flange Diameter	Typical Stimpson P/N
	0.180" wide x 0.040" deep	0.093"	0.150"	GS-3 Series, 0.089 O.D.

Date	SYM	REVISION RECORD	AUTH	DR.	CK.
4/29/06	A	Added dimensions Updated notes	T.B.	B.S.	
4/26/08	B	Added dimension 0.51	T.B.	B.S.	
8/01/14	C	Updated to ROHS 2 Compliant	T.B.	B.S.	



- NOTES:
- MATERIAL:
HOUSING : BLACK POLYPROPYLENE, PP4410
FLAMMABILITY RATING -UL94V-0, UL FILE NO. E107536
TEMPERATURE RANGE: -20°C TO +110°C
SPRING: STAINLESS STEEL, NICKEL PLATED
TERMINAL: BRASS, NICKEL PLATED, FAST ON TABS OR SOLDER LUGS
 - ROHS 2 COMPLIANT

Tolerance (Except as noted)	MPD Memory Protection Devices, Inc 200 Broad Hollow Road, Farmingdale, New York 11735		
decimal ±.5 (.020)		Scale	Drawn By B.S.
Fractional ± .8 (.030)			Approved By T.B.
Angular ± 3°	Title 6V BATTERY HOLDER		
	Date 8/01/14	Drawing Number BH223-L	