

TK Polystyrene

- **Flame-resistant**
- **Impact-resistant**
- **Temperature-resistant to 70°C**



Base grey lid grey						
with Pg knockouts		with metric knockouts		with smooth walls		
Type	Order N°	Type	Order N°	Type	Order N°	Dimensions
PS 77 - 6	115 401 01	PS 77 - 6-m	105 401 01	PS 77 - 6-o	110 401 01	65 x 65 x 57
PS 77 - 8	115 901 01	PS 77 - 8-m	105 901 01	PS 77 - 8-o	110 901 01	65 x 65 x 81
PS 97 - 6	115 402 01	PS 97 - 6-m	105 402 01	PS 97 - 6-o	110 402 01	94 x 65 x 57
PS 97 - 8	115 902 01	PS 97 - 8-m	105 902 01	PS 97 - 8-o	110 902 01	94 x 65 x 81
PS 99 - 6	115 403 01	PS 99 - 6-m	105 403 01	PS 99 - 6-o	110 403 01	94 x 94 x 57
PS 99 - 8	115 903 01	PS 99 - 8-m	105 903 01	PS 99 - 8-o	110 903 01	94 x 94 x 81
PS 1111 - 7	115 404 01	PS 1111 - 7-m	105 404 01	PS 1111 - 7-o	110 404 01	110x 110 x 66
PS 1111 - 9	115 904 01	PS 1111 - 9-m	105 904 01	PS 1111 - 9-o	110 904 01	110x 110 x 90
PS 1309 - 6	115 409 01	PS 1309 - 6-m	105 409 01	PS 1309 - 6-o	110 409 01	130 x 94 x 57
PS 1309 - 8	115 909 01	PS 1309 - 8-m	105 909 01	PS 1309 - 8-o	110 909 01	130 x 94 x 81
PS 1313 - 7	115 405 01	PS 1313 - 7-m	105 405 01	PS 1313 - 7-o	110 405 01	130 x 130 x 75
PS 1313 -10	115 905 01	PS 1313 -10-m	105 905 01	PS 1313 -10-o	110 905 01	130 x 130 x 99
PS 1809 - 6	115 410 01	PS 1809 - 6-m	105 410 01	PS 1809 - 6-o	110 410 01	180 x 94 x 57
PS 1809 - 8	115 910 01	PS 1809 - 8-m	105 910 01	PS 1809 - 8-o	110 910 01	180 x 94 x 81
PS 1811 - 9	115 406 01	PS 1811 - 9-m	105 406 01	PS 1811 - 9-o	110 406 01	180 x 110 x 90
PS 1811 -11	115 906 01	PS 1811 -11-m	105 906 01	PS 1811 -11-o	110 906 01	180 x 110 x 111
PS 1811 -16	114 406 01	PS 1811 -16-m	104 406 01	PS 1811 -16-o	109 406 01	180 x 110 x 165
PS 1818 - 9	115 407 01	PS 1818 - 9-m	105 407 01	PS 1818 - 9-o	110 407 01	182 x 180 x 90
PS 1818 -11	115 907 01	PS 1818 -11-m	105 907 01	PS 1818 -11-o	110 907 01	182 x 180 x 111
PS 1818 -16	114 407 01	PS 1818 -16-m	104 407 01	PS 1818 -16-o	109 407 01	182 x 180 x 165
PS 1818 -21	114 907 01	PS 1818 -21-m	104 907 01	PS 1818 -21-o	109 907 01	182 x 180 x 215
PS 2518 - 9	115 408 01	PS 2518 - 9-m	105 408 01	PS 2518 - 9-o	110 408 01	254 x 180 x 90
PS 2518 -11	115 908 01	PS 2518 -11-m	105 908 01	PS 2518 -11-o	110 908 01	254 x 180 x 111
PS 2518 -16	114 408 01	PS 2518 -16-m	104 408 01	PS 2518 -16-o	109 408 01	254 x 180 x 165
PS 2518 -21	114 908 01	PS 2518 -21-m	104 908 01	PS 2518 -21-o	109 908 01	254 x 180 x 215
PS 3625 -11	115 412 01	PS 3625 -11-m	105 412 01	PS 3625 -11-o	110 412 01	360 x 254 x 111
PS 3625 -16	115 912 01	PS 3625 -16-m	105 912 01	PS 3625 -16-o	110 912 01	360 x 254 x 165
PS 3625 -21	114 412 01	PS 3625 -21-m	104 412 01	PS 3625 -21-o	109 412 01	360 x 254 x 215



Base grey lid transparent										
with Pg knockouts			with metric knockouts			with smooth walls				
Type	Order N°		Type	Order N°		Type	Order N°		Dimensions	
PS 77 - 6 -t	116 001 01		PS 77 - 6 -tm	106 001 01		PS 77 - 6 -to	111 001 01		65 x 65 x 57	
PS 77 - 8 -t	116 501 01		PS 77 - 8 -tm	106 501 01		PS 77 - 8 -to	111 501 01		65 x 65 x 81	
PS 97 - 6 -t	116 002 01		PS 97 - 6 -tm	106 002 01		PS 97 - 6 -to	111 002 01		94 x 65 x 57	
PS 97 - 8 -t	116 502 01		PS 97 - 8 -tm	106 502 01		PS 97 - 8 -to	111 502 01		94 x 65 x 81	
PS 99 - 6 -t	116 003 01		PS 99 - 6 -tm	106 003 01		PS 99 - 6 -to	111 003 01		94 x 94 x 57	
PS 99 - 8 -t	116 503 01		PS 99 - 8 -tm	106 503 01		PS 99 - 8 -to	111 503 01		94 x 94 x 81	
PS 1111 - 7 -t	116 004 01		PS 1111 - 7 -tm	106 004 01		PS 1111 - 7 -to	111 004 01		110x 110 x 66	
PS 1111 - 9 -t	116 504 01		PS 1111 - 9 -tm	106 504 01		PS 1111 - 9 -to	111 504 01		110x 110 x 90	
PS 1309 - 6 -t	116 009 01		PS 1309 - 6 -tm	106 009 01		PS 1309 - 6 -to	111 009 01		130 x 94 x 57	
PS 1309 - 8 -t	116 509 01		PS 1309 - 8 -tm	106 509 01		PS 1309 - 8 -to	111 509 01		130 x 94 x 81	
PS 1313 - 7 -t	116 005 01		PS 1313 - 7 -tm	106 005 01		PS 1313 - 7 -to	111 005 01		130 x 130 x 75	
PS 1313 -10 -t	116 505 01		PS 1313 -10 -tm	106 505 01		PS 1313 -10 -to	111 505 01		130 x 130 x 99	
PS 1809 - 6 -t	116 010 01		PS 1809 - 6 -tm	106 010 01		PS 1809 - 6 -to	111 010 01		180 x 94 x 57	
PS 1809 - 8 -t	116 510 01		PS 1809 - 8 -tm	106 510 01		PS 1809 - 8 -to	111 510 01		180 x 94 x 81	
PS 1811 - 9 -t	116 006 01		PS 1811 - 9 -tm	106 006 01		PS 1811 - 9 -to	111 006 01		180 x 110 x 90	
PS 1811 -11 -t	116 506 01		PS 1811 -11 -tm	106 506 01		PS 1811 -11 -to	111 506 01		180 x 110 x 111	
PS 1811 -16 -t	117 006 01		PS 1811 -16 -tm	107 006 01		PS 1811 -16 -to	112 006 01		180 x 110 x 165	
PS 1818 - 9 -t	116 007 01		PS 1818 - 9 -tm	106 007 01		PS 1818 - 9 -to	111 007 01		182 x 180 x 90	
PS 1818 -11 -t	116 507 01		PS 1818 -11 -tm	106 507 01		PS 1818 -11 -to	111 507 01		182 x 180 x 111	
PS 1818 -16 -t	117 007 01		PS 1818 -16 -tm	107 007 01		PS 1818 -16 -to	112 007 01		182 x 180 x 165	
PS 1818 -21 -t	117 507 01		PS 1818 -21 -tm	107 507 01		PS 1818 -21 -to	112 507 01		182 x 180 x 215	
PS 2518 - 9 -t	116 008 01		PS 2518 - 9 -tm	106 008 01		PS 2518 - 9 -to	111 008 01		254 x 180 x 90	
PS 2518 -11 -t	116 508 01		PS 2518 -11 -tm	106 508 01		PS 2518 -11 -to	111 508 01		254 x 180 x 111	
PS 2518 -16 -t	117 008 01		PS 2518 -16 -tm	107 008 01		PS 2518 -16 -to	112 008 01		254 x 180 x 165	
PS 2518 -21 -t	117 508 01		PS 2518 -21 -tm	107 508 01		PS 2518 -21 -to	112 508 01		254 x 180 x 215	
PS 3625 -11 -t	116 012 01		PS 3625 -11 -tm	106 012 01		PS 3625 -11 -to	111 012 01		360 x 254 x 111	
PS 3625 -16 -t	116 512 01		PS 3625 -16 -tm	106 512 01		PS 3625 -16 -to	111 512 01		360 x 254 x 165	
PS 3625 -21 -t	117 012 01		PS 3625 -21 -tm	107 012 01		PS 3625 -21 -to	112 012 01		360 x 254 x 215	

- glass-fibre reinforced
- flame-resistant
- UV-resistant
- temperature-resistant to 120°C



Base grey lid grey						
with Pg knockouts		with metric knockouts		with smooth walls*		
Type	Order N°	Type	Order N°	Type	Order N°	Dimensions
PC 77 - 6	125 401 01	PC 77 - 6-m	127 401 01	PC 77 - 6-o	120 401 01	65 x 65 x 57
PC 77 - 8	125 901 01	PC 77 - 8-m	127 901 01	PC 77 - 8-o	120 901 01	65 x 65 x 81
PC 97 - 6	125 402 01	PC 97 - 6-m	127 402 01	PC 97 - 6-o	120 402 01	94 x 65 x 57
PC 97 - 8	125 902 01	PC 97 - 8-m	127 902 01	PC 97 - 8-o	120 902 01	94 x 65 x 81
PC 99 - 6	125 403 01	PC 99 - 6-m	127 403 01	PC 99 - 6-o	120 403 01	94 x 94 x 57
PC 99 - 8	125 903 01	PC 99 - 8-m	127 903 01	PC 99 - 8-o	120 903 01	94 x 94 x 81
PC 1111 - 7	125 404 01	PC 1111 - 7-m	127 404 01	PC 1111 - 7-o	120 404 01	110x 110 x 66
PC 1111 - 9	125 904 01	PC 1111 - 9-m	127 904 01	PC 1111 - 9-o	120 904 01	110x 110 x 90
PC 1309 - 6	125 409 01	PC 1309 - 6-m	127 409 01	PC 1309 - 6-o	120 409 01	130 x 94 x 57
PC 1309 - 8	125 909 01	PC 1309 - 8-m	127 909 01	PC 1309 - 8-o	120 909 01	130 x 94 x 81
PC 1313 - 7	125 405 01	PC 1313 - 7-m	127 405 01	PC 1313 - 7-o	120 405 01	130 x 130 x 75
PC 1313 -10	125 905 01	PC 1313 -10-m	127 905 01	PC 1313 -10-o	120 905 01	130 x 130 x 99
PC 1809 - 6	125 410 01	PC 1809 - 6-m	127 410 01	PC 1809 - 6-o	120 410 01	180 x 94 x 57
PC 1809 - 8	125 910 01	PC 1809 - 8-m	127 910 01	PC 1809 - 8-o	120 910 01	180 x 94 x 81
PC 1811 - 9	125 406 01	PC 1811 - 9-m	127 406 01	PC 1811 - 9-o	120 406 01	180 x 110 x 90
PC 1811 -11	125 906 01	PC 1811 -11-m	127 906 01	PC 1811 -11-o	120 906 01	180 x 110 x 111
PC 1811 -16	126 406 01	PC 1811 -16-m	128 406 01	PC 1811 -16-o	121 406 01	180 x 110 x 165
PC 1818 - 9	125 407 01	PC 1818 - 9-m	127 407 01	PC 1818 - 9-o	120 407 01	182 x 180 x 90
PC 1818 -11	125 907 01	PC 1818 -11-m	127 907 01	PC 1818 -11-o	120 907 01	182 x 180 x 111
PC 1818 -16	126 407 01	PC 1818 -16-m	128 407 01	PC 1818 -16-o	121 407 01	182 x 180 x 165
PC 1818 -21	126 907 01	PC 1818 -21-m	128 907 01	PC 1818 -21-o	121 907 01	182 x 180 x 215
PC 2518 - 9	125 408 01	PC 2518 - 9-m	127 408 01	PC 2518 - 9-o	120 408 01	254 x 180 x 90
PC 2518 -11	125 908 01	PC 2518 -11-m	127 908 01	PC 2518 -11-o	120 908 01	254 x 180 x 111
PC 2518 -16	126 408 01	PC 2518 -16-m	128 408 01	PC 2518 -16-o	121 408 01	254 x 180 x 165
PC 2518 -21	126 908 01	PC 2518 -21-m	128 908 01	PC 2518 -21-o	121 908 01	254 x 180 x 215
PC 3625 -11	125 412 01	PC 3625 -11-m	127 412 01	PC 3625 -11-o	120 412 01	360 x 254 x 111
PC 3625 -16	125 912 01	PC 3625 -16-m	127 912 01	PC 3625 -16-o	120 912 01	360 x 254 x 165
PC 3625 -21	126 412 01	PC 3625 -21-m	128 412 01	PC 3625 -21-o	121 412 01	360 x 254 x 215

* only available in UK



Base grey lid transparent						
with Pg knockouts		with metric knockouts		with smooth walls*		
Type	Order N°	Type	Order N°	Type	Order N°	Dimensions
PC 77- 6-t	135 001 01	PC 77- 6-tm	137 001 01	PC 77- 6-to	130 001 01	65 x 65 x 57
PC 77- 8-t	135 501 01	PC 77- 8-tm	137 501 01	PC 77- 8-to	130 501 01	65 x 65 x 81
PC 97- 6-t	135 002 01	PC 97- 6-tm	137 002 01	PC 97- 6-to	130 002 01	94 x 65 x 57
PC 97- 8-t	135 502 01	PC 97- 8-tm	137 502 01	PC 97- 8-to	130 502 01	94 x 65 x 81
PC 99- 6-t	135 003 01	PC 99- 6-tm	137 003 01	PC 99- 6-to	130 003 01	94 x 94 x 57
PC 99- 8-t	135 503 01	PC 99- 8-tm	137 503 01	PC 99- 8-to	130 503 01	94 x 94 x 81
PC 1111- 7-t	135 004 01	PC 1111- 7-tm	137 004 01	PC 1111- 7-to	130 004 01	110x 110 x 66
PC 1111- 9-t	135 504 01	PC 1111- 9-tm	137 504 01	PC 1111- 9-to	130 504 01	110x 110 x 90
PC 1309- 6-t	135 009 01	PC 1309- 6-tm	137 009 01	PC 1309- 6-to	130 009 01	130 x 94 x 57
PC 1309- 8-t	135 509 01	PC 1309- 8-tm	137 509 01	PC 1309- 8-to	130 509 01	130 x 94 x 81
PC 1313- 7-t	135 005 01	PC 1313- 7-tm	137 005 01	PC 1313- 7-to	130 005 01	130 x 130 x 75
PC 1313-10-t	135 505 01	PC 1313-10-tm	137 505 01	PC 1313-10-to	130 505 01	130 x 130 x 99
PC 1809- 6-t	135 010 01	PC 1809- 6-tm	137 010 01	PC 1809- 6-to	130 010 01	180 x 94 x 57
PC 1809- 8-t	135 510 01	PC 1809- 8-tm	135 510 01	PC 1809- 8-to	130 510 01	180 x 94 x 81
PC 1811- 9-t	135 006 01	PC 1811- 9-tm	137 006 01	PC 1811- 9-to	130 006 01	180 x 110 x 90
PC 1811-11-t	135 506 01	PC 1811-11-tm	137 506 01	PC 1811-11-to	130 506 01	180 x 110 x 111
PC 1811-16-t	136 006 01	PC 1811-16-tm	138 006 01	PC 1811-16-to	131 006 01	180 x 110 x 165
PC 1818- 9-t	135 007 01	PC 1818- 9-tm	137 007 01	PC 1818- 9-to	130 007 01	182 x 180 x 90
PC 1818-11-t	135 507 01	PC 1818-11-tm	137 507 01	PC 1818-11-to	130 507 01	182 x 180 x 111
PC 1818-16-t	136 007 01	PC 1818-16-tm	138 007 01	PC 1818-16-to	131 007 01	182 x 180 x 165
PC 1818-21-t	136 507 01	PC 1818-21-tm	138 507 01	PC 1818-21-to	131 507 01	182 x 180 x 215
PC 2518- 9-t	135 008 01	PC 2518- 9-tm	137 008 01	PC 2518- 9-to	130 008 01	254 x 180 x 90
PC 2518-11-t	135 508 01	PC 2518-11-tm	137 508 01	PC 2518-11-to	130 508 01	254 x 180 x 111
PC 2518-16-t	136 008 01	PC 2518-16-tm	138 008 01	PC 2518-16-to	131 008 01	254 x 180 x 165
PC 2518-21-t	136 508 01	PC 2518-21-tm	138 508 01	PC 2518-21-to	131 508 01	254 x 180 x 215
PC 3625-11-t	135 012 01	PC 3625-11-tm	137 012 01	PC 3625-11-to	130 012 01	360 x 254 x 111
PC 3625-16-t	135 512 01	PC 3625-16-tm	137 512 01	PC 3625-16-to	130 512 01	360 x 254 x 165
PC 3625-21-t	136 012 01	PC 3625-21-tm	138 012 01	PC 3625-21-to	131 012 01	360 x 254 x 215

* only available in UK

TK Polycarbonate

with  Certification

- glass-fibre reinforced
- flame-resistant
- UV-resistant
- temperature-resistant to 120°C



Base grey lid grey				Base grey lid transparent				
with Pg knockouts		with metric knockouts		with Pg knockouts		with metric knockouts		
Type	Order N°	Type	Order N°	Type	Order N°	Type	Order N°	Dimensions
PC 77 - 6	125 401 52	PC 77 - 6-m	127 401 52	PC 77 - 6-t	135 001 52	PC 77 - 6-tm	137 001 52	65 x 65 x 57
PC 77 - 8	125 901 52	PC 77 - 8-m	127 901 52	PC 77 - 8-t	135 501 52	PC 77 - 8-tm	137 501 52	65 x 65 x 81
PC 97 - 6	125 402 52	PC 97 - 6-m	127 402 52	PC 97 - 6-t	135 002 52	PC 97 - 6-tm	137 002 52	94 x 65 x 57
PC 97 - 8	125 902 52	PC 97 - 8-m	127 902 52	PC 97 - 8-t	135 502 52	PC 97 - 8-tm	137 502 52	94 x 65 x 81
PC 99 - 6	125 403 52	PC 99 - 6-m	127 403 52	PC 99 - 6-t	135 003 52	PC 99 - 6-tm	137 003 52	94 x 94 x 57
PC 99 - 8	125 903 52	PC 99 - 8-m	127 903 52	PC 99 - 8-t	135 503 52	PC 99 - 8-tm	137 503 52	94 x 94 x 81
PC 1111 - 7	125 404 52	PC 1111 - 7-m	127 404 52	PC 1111 - 7-t	135 004 52	PC 1111 - 7-tm	137 004 52	110x 110 x 66
PC 1111 - 9	125 904 52	PC 1111 - 9-m	127 904 52	PC 1111 - 9-t	135 504 52	PC 1111 - 9-tm	137 504 52	110x 110 x 90
PC 1309 - 6	125 409 52	PC 1309 - 6-m	127 409 52	PC 1309 - 6-t	135 009 52	PC 1309 - 6-tm	137 009 52	130 x 94 x 57
PC 1309 - 8	125 909 52	PC 1309 - 8-m	127 909 52	PC 1309 - 8-t	135 509 52	PC 1309 - 8-tm	137 509 52	130 x 94 x 81
PC 1313 - 7	125 405 52	PC 1313 - 7-m	127 405 52	PC 1313 - 7-t	135 005 52	PC 1313 - 7-tm	137 005 52	130 x 130 x 75
PC 1313 -10	125 905 52	PC 1313 -10-m	127 905 52	PC 1313 -10-t	135 505 52	PC 1313 -10-tm	137 505 52	130 x 130 x 99
PC 1809 - 6	125 410 52	PC 1809 - 6-m	127 410 52	PC 1809 - 6-t	135 010 52	PC 1809 - 6-tm	137 010 52	180 x 94 x 57
PC 1809 - 8	125 910 52	PC 1809 - 8-m	127 910 52	PC 1809 - 8-t	135 510 52	PC 1809 - 8-tm	137 510 52	180 x 94 x 81
PC 1811 - 9	125 406 52	PC 1811 - 9-m	127 406 52	PC 1811 - 9-t	135 006 52	PC 1811 - 9-tm	137 006 52	180 x 110 x 90
PC 1811 -11	125 906 52	PC 1811 -11-m	127 906 52	PC 1811 -11-t	135 506 52	PC 1811 -11-tm	137 506 52	180 x 110 x 111
PC 1811 -16	126 406 52	PC 1811 -16-m	128 406 52	PC 1811 -16-t	136 006 52	PC 1811 -16-tm	138 006 52	180 x 110 x 165
PC 1818 - 9	125 407 52	PC 1818 - 9-m	127 407 52	PC 1818 - 9-t	135 007 52	PC 1818 - 9-tm	137 007 52	182 x 180 x 90
PC 1818 -11	125 907 52	PC 1818 -11-m	127 907 52	PC 1818 -11-t	135 507 52	PC 1818 -11-tm	137 507 52	182 x 180 x 111
PC 1818 -16	126 407 52	PC 1818 -16-m	128 407 52	PC 1818 -16-t	136 007 52	PC 1818 -16-tm	138 007 52	182 x 180 x 165
PC 1818 -21	126 907 52	PC 1818 -21-m	128 907 52	PC 1818 -21-t	136 507 52	PC 1818 -21-tm	138 507 52	182 x 180 x 215
PC 2518 - 9	125 408 52	PC 2518 - 9-m	127 408 52	PC 2518 - 9-t	135 008 52	PC 2518 - 9-tm	137 008 52	254 x 180 x 90
PC 2518 -11	125 908 52	PC 2518 -11-m	127 908 52	PC 2518 -11-t	135 508 52	PC 2518 -11-tm	137 508 52	254 x 180 x 111
PC 2518 -16	126 408 52	PC 2518 -16-m	128 408 52	PC 2518 -16-t	136 008 52	PC 2518 -16-tm	138 008 52	254 x 180 x 165
PC 2518 -21	126 908 52	PC 2518 -21-m	128 908 52	PC 2518 -21-t	136 508 52	PC 2518 -21-tm	138 508 52	254 x 180 x 215
PC 3625 -11	125 412 52	PC 3625 -11-m	127 412 52	PC 3625 -11-t	135 012 52	PC 3625 -11-tm	137 012 52	360 x 254 x 111
PC 3625 -16	125 912 52	PC 3625 -16-m	127 912 52	PC 3625 -16-t	135 512 52	PC 3625 -16-tm	137 512 52	360 x 254 x 165
PC 3625 -21	126 412 52	PC 3625 -21-m	128 412 52	PC 3625 -21-t	136 012 52	PC 3625 -21-tm	138 012 52	360 x 254 x 215