


Dimensions: mm (In.)**Electrical Specifications:**

- Rating: 50mA/12VDC
- Contact Resistance: 100mΩ max. initial
- Insulation Resistance: 100MΩ min. @ 100VDC
- Dielectric Strength: 250 VAC for 1 minute.
- LED: Voltage - 4.2 typ, 6V max.;
- Current - 15mA, Max.20mA

Mechanical Specifications:

- Bounce: 10m sec. max
- Operating Temperature: +10°C~+60°C
- Storage Temperature: -20°C~+70°C
- Operating Force: 250gf max.
- Travel: 0.3±0.1mm
- Life: 300,000 cycles min.

Mouser Stock No.	Illuminated Button Color
107-LP12-3	Yellow
107-LP12-5	Red
107-LP12-7	Green

Solder Process:

- Temperature: 260°±5°C, 3 sec

Illuminated Pushbutton Switches
 107-LP12-3, 107-LP12-5, 107-LP12-7

Mountain
Switch

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[107-LP12-7](#)