


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -


ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14						
			C	REVISED PER ECO-10-012870	27APR11	HMR	DR



AMP
WIRE RANGE

12-10 AWG
SOLID OR STRANDED



- 1
- STAMP AMP 12-10* APPROX AS SHOWN

2

MAXIMUM LENGTH DOES NOT INCLUDE
MANUFACTURING TABS

3

COPPER PER ASTM B152, ANNEALED

4

GOLD PLATE 0.00127[.000050] MIN THK
PER ASTM B488 TYPE 1, CPDE C, OVER
NICKEL PLATE 0.00127[0.000050] MIN
EXT THK PER SAE AMS QQ-N-290 OVER
Cu FLASH PER SAE AMS 2418

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING
TEMPERATURE:
260° C MAX

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

VOLTAGE RATING:
NOT APPLICABLE

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

WIRE CROSS SECTIONAL AREA RANGE:
2.62-6.64mm²[5,180-13,100] CIR MILS
SOLID OR STRANDED

FOR ORDER ENTRY

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
TA BRINKMAN
4-14-93

CHK
DA PATTERSON
4-14-93

APVD
DE MILLER
4-14-93

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

—

CUSTOMER DRAWING

SCALE
10:1

SHEET
1 OF 1

REV
C

500

LOOSE PIECE

328600

QTY

PACKAGING

PART NO

TE TE Connectivity

NAME

SPLICE, BUTT,
STRAP, SOLISTRAND,TM
HEAT RESISTANT STRATO-THERM

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=328600

—