




-	6.71±0.13 [.265±.005]	1/4	BODY: COPPER ASTM-B187 ANNEALED TIN PL MIL-T-10727 0.00381[.000150] MIN THK INSERT & FUNNEL: BRASS ASTM B36 NICKEL PL SAE AMS QQ-N-290A, DATED JULY 2000, 0.00254 [.000100] MIN THK	277149-8
-	5.00±0.08 [.197±.003]	#10		277149-7
-	4.34±0.08 [.171±.003]	#8		277149-6
-	4.34±0.08 [.171±.003]	#8		277149-5
18.5 GRAMS	9.91±0.13 [.390±.005]	3/8		277149-4
18.9 GRAMS	8.33±0.13 [.328±.005]	5/16	MATERIAL & FINISH	277149-3
19.4 GRAMS	6.71±0.13 [.265±.005]	1/4		277149-2
19.8 GRAMS	5.00±0.08 [.197±.003]	#10		277149-1
WEIGHT	'A'	'B'		PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 6/23/89	TE Connectivity	
DIMENSIONS: MM [INCHES]		CHK MS FEHER 10/16/90		
		APVD WJ VOCKROTH 10/16/90	NAME WIRE TERMINAL, COPALUM SEALED, RING TONGUE, WIRE SIZE [4] AL OR [6] COPPER	
		PRODUCT SPEC 108-11011		
MATERIAL SEE TABLE		APPLICATION SPEC 114-2134	SIZE A2	CAGE CODE 00779
FINISH SEE TABLE		WEIGHT SEE TABLE	DRAWING NO. C-277149	RESTRICTED TO -
		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 of 1
			REV K	